

## Product Change Notifications

Ref.	PCN-FLS-200415001	Date	2020/04/15
Supplier	HANGZHOU HPWINNER OPTO CORPORATION		
Add.	No.18 Kangzhong Road, Gongshu District, Hangzhou 310015, China		

To:	
Company	Future Electronics



### 1. Product Change Statement:

HPWINNER has moved the factory from location of its headquarters to one of its subsidiaries, thus information about owner of UL product certifications has been updated. Therefore, information about name and address of manufacturer on labels has to change accordingly. There will be changes on both product label and carton label for all products. The content of change is listed below and presented with examples. The change starts from May 15th, 2020.

Although, invoices will still be issued by HANGZHOU HPWINNER LIGHTING EQUIPMENTS CO., LTD.

### 2. Content of Change:

#### 2.1 Product Label (with UL)

Item of Change:	Manufacturer	
	Before Change	After Change
Content	<u>HANGZHOU HPWINNER OPTO CORPORATION</u>	<u>Zhejiang Hpwinner Wisdom Opto Co., Ltd.</u>
Example (marked in red)	 <p><b>Recognized Component</b>            Conforms to            UL Std.8750            Certified to            CSA Std. C22.2 No.250.13            Date Code:2009            Lot #: VZ00120002J            SN: Q2292020 02            For Use in Lighting Products</p> <p><b>LED Module</b>            Model M1H-H            Part Number: M9HHT3MLT030            Input Voltage:45.0-58.5VDC            Working Current:DC 350-1050mA            Wattage Range:Max.60W            CRI&gt;80 CCT3000K            Ambient temperature:-40~+50°C            Vi+ -WH/RED Vi- BLK            Beam Angle: Type II Medium            IP Rating: IP68            SUITABLE FOR WET LOCATIONS</p> <p>MANUFACTURER:HANGZHOU HPWINNER OPTO CORPORATION Made In China</p>	 <p><b>Recognized Component</b>            Conforms to            UL Std.8750            Certified to            CSA Std. C22.2 No.250.13            Date Code:2016            Lot #: VZ00310008J            SN: 041520201001            For Use in Lighting Products</p> <p><b>LED Module</b>            Model M9H-H            Part Number: M9H60DL3080 L300            Input Voltage:45.0-58.5VDC            Working Current:DC 350-1050mA            Wattage Range:Max.60W            CRI&gt;80 CCT4000K            Ambient temperature:-40~+50°C            Vi+ -WH/RED Vi- BLK            Beam Angle: 60DEG            IP Rating: IP68            SUITABLE FOR WET LOCATIONS</p> <p>Manufacturer: Zhejiang Hpwinner Wisdom Opto Co., Ltd. Made In China</p>

#### 2.2 Carton Label

Item of Change:	Ship From Address	
	Before Change	After Change
Content	<u>HANGZHOU HPWINNER LIGHTING EQUIPMENTS CO., LTD</u> <u>18th, Kangzhong Road, Gongshu Dist., Hangzhou, Zhejiang, China. 310015</u>	<u>Zhejiang Hpwinner Wisdom Opto Co., Ltd.</u> <u>No.9-1, Baixi Avenue, Changxing Economic Development Zone, Huzhou City 313100, Zhejiang Province, China.</u>



### 3. Part Number of Products in Changing:

#### 3.1 LED modules for both product and carton labels

M1HHT1SLTX730	M2HH12DLTX730	M8HH25DL30730	M8HL25DL30730	M16HH25DL50730
M1HHT1SLTX740	M2HH12DLTX740	M8HH25DL30740	M8HL25DL30740	M16HH25DL50740
M1HHT1SLTX750	M2HH12DLTX750	M8HH25DL30750	M8HL25DL30750	M16HH25DL50750
M1HHT1SLTX757	M2HH12DLTX757	M8HH25DL30757	M8HL25DL30757	M16HH25DL50757
M1HHT2MLTX730	M2HH25DLTX730	M8HH40DL30730	M8HL40DL30730	M16HH40DL50730
M1HHT2MLTX740	M2HH25DLTX740	M8HH40DL30740	M8HL40DL30740	M16HH40DL50740
M1HHT2MLTX750	M2HH25DLTX750	M8HH40DL30750	M8HL40DL30750	M16HH40DL50750
M1HHT2MLTX757	M2HH25DLTX757	M8HH40DL30757	M8HL40DL30757	M16HH40DL50757
M1HHT3MLTX730	M2HH40DLTX730	M8HH60DL30730	M8HL60DL30730	M16HH60DL50730
M1HHT3MLTX740	M2HH40DLTX740	M8HH60DL30740	M8HL60DL30740	M16HH60DL50740
M1HHT3MLTX750	M2HH40DLTX750	M8HH60DL30750	M8HL60DL30750	M16HH60DL50750
M1HHT3MLTX757	M2HH40DLTX757	M8HH60DL30757	M8HL60DL30757	M16HH60DL50757
M1HHT4MLTX730	M2HH60DLTX730	M8HH90DL30730	M8HL90DL30730	M16HH90DL50730
M1HHT4MLTX740	M2HH60DLTX740	M8HH90DL30740	M8HL90DL30740	M16HH90DL50740
M1HHT4MLTX750	M2HH60DLTX750	M8HH90DL30750	M8HL90DL30750	M16HH90DL50750
M1HHT4MLTX757	M2HH60DLTX757	M8HH90DL30757	M8HL90DL30757	M16HH90DL50757
M1HHT5MLTX730	M2HH90DLTX730	M8HHLBNL30730	M8HLLBNL30730	M16HHT1SL50730
M1HHT5MLTX740	M2HH90DLTX740	M8HHLBNL30740	M8HLLBNL30740	M16HHT1SL50740
M1HHT5MLTX750	M2HH90DLTX750	M8HHLBNL30750	M8HLLBNL30750	M16HHT1SL50750
M1HHT5MLTX757	M2HH90DLTX757	M8HHLBNL30757	M8HLLBNL30757	M16HHT1SL50757
M1HHT1SVLTX730	M2HH34DLTX730	M8HHT1SL30730	M8HLT1SL30730	M16HHT2SL50730
M1HHT1SVLTX740	M2HH34DLTX740	M8HHT1SL30740	M8HLT1SL30740	M16HHT2SL50740
M1HHT1SVLTX750	M2HH34DLTX750	M8HHT1SL30750	M8HLT1SL30750	M16HHT2SL50750
M1HHT1SVLTX757	M2HH34DLTX757	M8HHT1SL30757	M8HLT1SL30757	M16HHT2SL50757

M1HHT3MVLTX730	M2HH12DLTX830	M8HHT2SL30730	M8HLT2SL30730	M16HHT2ML50730
M1HHT3MVLTX740	M2HH12DLTX840	M8HHT2SL30740	M8HLT2SL30740	M16HHT2ML50740
M1HHT3MVLTX750	M2HH12DLTX850	M8HHT2SL30750	M8HLT2SL30750	M16HHT2ML50750
M1HHT3MVLTX757	M2HH25DLTX830	M8HHT2SL30757	M8HLT2SL30757	M16HHT2ML50757
M1HHT1SLTX830	M2HH25DLTX840	M8HHT3ML30730	M8HLT3ML30730	M16HHT3ML50730
M1HHT1SLTX840	M2HH25DLTX850	M8HHT3ML30740	M8HLT3ML30740	M16HHT3ML50740
M1HHT1SLTX850	M2HH40DLTX830	M8HHT3ML30750	M8HLT3ML30750	M16HHT3ML50750
M1HHT2MLTX830	M2HH40DLTX840	M8HHT3ML30757	M8HLT3ML30757	M16HHT3ML50757
M1HHT2MLTX840	M2HH40DLTX850	M8HH25DL30830	M8HL25DL30830	M16HHT5SL50730
M1HHT2MLTX850	M2HH60DLTX830	M8HH25DL30840	M8HL25DL30840	M16HHT5SL50740
M1HHT3MLTX830	M2HH60DLTX840	M8HH25DL30850	M8HL25DL30850	M16HHT5SL50750
M1HHT3MLTX840	M2HH60DLTX850	M8HH25DL30857	M8HL25DL30857	M16HHT5SL50757
M1HHT3MLTX850	M2HH90DLTX830	M8HH40DL30830	M8HL40DL30830	
M1HHT4MLTX830	M2HH90DLTX840	M8HH40DL30840	M8HL40DL30840	
M1HHT4MLTX840	M2HH90DLTX850	M8HH40DL30850	M8HL40DL30850	
M1HHT4MLTX850	M2HH34DLTX830	M8HH40DL30857	M8HL40DL30857	
M1HHT5MLTX830	M2HH34DLTX840	M8HH60DL30830	M8HL60DL30830	
M1HHT5MLTX840	M2HH34DLTX850	M8HH60DL30840	M8HL60DL30840	
M1HHT5MLTX850		M8HH60DL30850	M8HL60DL30850	
M1HHT1SVLTX830	M6HHT2SLTX730	M8HH60DL30857	M8HL60DL30857	
M1HHT1SVLTX840	M6HHT2SLTX740	M8HH90DL30830	M8HL90DL30830	
M1HHT1SVLTX850	M6HHT2SLTX750	M8HH90DL30840	M8HL90DL30840	
M1HHT3MVLTX830	M6HHT2SLTX757	M8HH90DL30850	M8HL90DL30850	
M1HHT3MVLTX840	M6HHLBNLTX730	M8HH90DL30857	M8HL90DL30857	
M1HHT3MVLTX850	M6HHLBNLTX740	M8HHLBNL30830	M8HLLBNL30830	
	M6HHLBNLTX750	M8HHLBNL30840	M8HLLBNL30840	
	M6HHLBNLTX757	M8HHLBNL30850	M8HLLBNL30850	
	M6HHT2SLTX830	M8HHLBNL30857	M8HLLBNL30857	
	M6HHT2SLTX840	M8HHT1SL30830	M8HLT1SL30830	
	M6HHT2SLTX850	M8HHT1SL30840	M8HLT1SL30840	
	M6HHLBNLTX830	M8HHT1SL30850	M8HLT1SL30850	
	M6HHLBNLTX840	M8HHT1SL30857	M8HLT1SL30857	
	M6HHLBNLTX850	M8HHT2SL30830	M8HLT2SL30830	
		M8HHT2SL30840	M8HLT2SL30840	
		M8HHT2SL30850	M8HLT2SL30850	
		M8HHT2SL30857	M8HLT2SL30857	
		M8HHT3ML30830	M8HLT3ML30830	
		M8HHT3ML30840	M8HLT3ML30840	
		M8HHT3ML30850	M8HLT3ML30850	
		M8HHT3ML30857	M8HLT3ML30857	
		M8HH60DL30830-L300		
		M8HH60DL30835-L300		
		M8HH60DL30840-L300		

		M8HH60DL30850-L300		
		M8HH60DL30857-L300		

### 3.2 Cable connectors for carton labels

C2A-01M500	C2A-01F500	C2A-S2M200F	C2A-P2M500
C2A-S2M500	C2A-1FS1M	C2A-S3M200F	C2A-P3M500
C2A-S3M500		C2A-S4M200F	C2A-P4M500
C2A-S4M500			
C2A-S5M620			

#### Contact 1:

Attn: Claire Tang                      Email: [claire@hpwin.com](mailto:claire@hpwin.com)                      Tel: +86-571-88061966  
 Add: Building 1, No.18 Kangzhong Road, Gongshu District, Hangzhou 310015, Zhejiang Province, P.R.C.

#### Contact 2:

Attn: Christine Cheung                      Email: [christine@hpwin.com](mailto:christine@hpwin.com)                      Tel: +86-571-56532729  
 Add: Building 1, No.18 Kangzhong Road, Gongshu District, Hangzhou 310015, Zhejiang Province, P.R.C.