



8755 W. Higgins Road
Suite 500
Chicago, Illinois USA 60631

Apr 1st, 2021

Notification of Schottky Barrier and Ultrafast Recovery Rectifier MOQ Change _Apr 1st, 2021

To whom it may concern,

This is a declaration letter to state that Littelfuse will change the MOQ for Schottky Barrier and Ultrafast Recovery Rectifier products aligning to manufacture requirement. Detail affected part number list refer to Appendix.

There will be no change on product fit, form, function, and no change to MPQ/Packing Mode.

We value your business and look forward to assisting you whenever possible. Thank you!

Sincerely and Best Regards,

Sophia Lv
Global Product Manager
Thyristor and Rectifier Diode
Semiconductor Business Unit, Wuxi, China
+86 510 85277701 - 7967
slv@littelfuse.com

Appendix --- MOQ change table for Affected Products

Part ID	Original MOQ	Updated MOQ	Part ID	Original MOQ	Updated MOQ
DST10100S	5000	20000	DSTF40150C	1000	20000
DST10100S-A	5000	20000	DSTF40150C-T	1000	20000
DST10100S-T	5000	20000	DSTF4045C	1000	20000
DST1040S	5000	20000	DSTF4050C	1000	20000
DST1040S-A	5000	20000	DSTF4050C-T	1000	20000
DST1040S-T	5000	20000	DSTF4060C	1000	20000
DST1045S	5000	20000	DSTF4060C-T	1000	20000
DST1045S-A	5000	20000	DSTF60100C	1000	20000
DST1045S-T	5000	20000	DSTF60100C-T	1000	20000
DST1050S	5000	20000	DUR1040CT	1000	20000
DST1050S-A	5000	20000	DUR1040CT-T	1000	20000
DST12100S	5000	20000	DUR2030CT	1000	20000
DST12100S-T	5000	20000	DUR2030CT-T	1000	20000
DST1545S	5000	20000	DUR30120	1000	20000
DST1545S-T	5000	20000	DUR30120-T	1000	20000
DST1550S	5000	20000	DUR3060CT	1000	20000
DST1550S-T	5000	20000	DUR3060CT-T	1000	20000
DST20100C	1000	20000	DUR60120W	300	20000
DST20100C-T	1000	20000	DUR60120W-T	300	20000
DST20150C	1000	20000	DUR6030WT	300	20000
DST20150C-T	1000	20000	DUR6040WT	300	20000
DST2045AX	2500	20000	DUR6060W	300	20000
DST2045C	1000	20000	DUR75120W	300	20000
DST2045C-T	1000	20000	DURB1640CT	800	20000
DST2050S	5000	20000	DURB2020CT	800	20000
DST2050S-T	5000	20000	DURD560A	2500	20000
DST2060C	1000	20000	DURD560A-T	2500	20000
DST2060C-T	1000	20000	DURF1030CT	1000	20000
DST2060DJF	3000	20000	DURF1030CTR	1000	20000
DST2080C	1000	20000	DURF1040CT	1000	20000
DST2080C-T	1000	20000	DURF1040CTR	1000	20000
DST2080S	5000	20000	DURF1040CT-T	1000	20000
DST2080S-T	5000	20000	DURF1060	1000	20000
DST30100C	1000	20000	DURF1060CT	1000	20000
DST30100C-T	1000	20000	DURF1060CT-T	1000	20000
DST3060DJF	3000	20000	DURF1060-T	1000	20000
DST3060LC	1000	20000	DURF2040CT	1000	20000
DST3060LC-T	1000	20000	DURF2040CT-T	1000	20000
DST3080C	1000	20000	DURF3060CT	1000	20000
DST40100C	1000	20000	DURF3060CT-T	1000	20000
DST40100C-T	1000	20000	DURF840	1000	20000
DST5100S	5000	20000	MBR10100CT	1000	20000
DST5100S-A	5000	20000	MBR10100CT-T	1000	20000
DST5200	1000	20000	MBR10150CT	1000	20000
DST560S	5000	20000	MBR10150CT-T	1000	20000
DST560S-A	5000	20000	MBR10200CT	1000	20000
DST580S	5000	20000	MBR10200CT-T	1000	20000

DST580S-A	5000	20000	MBR1045	1000	20000
DST8100S	5000	20000	MBR1045-T	1000	20000
DST8100S-A	5000	20000	MBR1060CTL	1000	20000
DST860S	5000	20000	MBR1060CTL-T	1000	20000
DST860S-A	5000	20000	MBR20100CTP	1000	20000
DSTB2045C	800	20000	MBR20100CTP-T	1000	20000
DSTB2045C-T	800	20000	MBR20150CT	1000	20000
DSTB30200C	800	20000	MBR20150CT-T	1000	20000
DSTB30200C-T	800	20000	MBR2060CT	1000	20000
DSTB60100C	800	20000	MBR2060CT-T	1000	20000
DSTB60100C-T	800	20000	MBR40100WT	1500	20000
DSTD5200	2500	20000	MBR6045WT	1500	20000
DSTF10200C	1000	20000	MBRB10100CT	800	20000
DSTF10200C-T	1000	20000	MBRB1060CT	800	20000
DSTF20100C	1000	20000	MBRB20100CT	800	20000
DSTF20100C-T	1000	20000	MBRB2060CT	800	20000
DSTF20120C	1000	20000	MBRD10100CT	2500	20000
DSTF20120CR	1000	20000	MBRD10150CT	2500	20000
DSTF20120CR-T	1000	20000	MBRD10200CT	2500	20000
DSTF20150CR	1000	20000	MBRF10100CTL	1000	20000
DSTF2045C	1000	20000	MBRF10100CTL-T	1000	20000
DSTF2045C-T	1000	20000	MBRF10100CTR	1000	20000
DSTF2050C	1000	20000	MBRF10100CTR-T	1000	20000
DSTF2060C	1000	20000	MBRF10150CTL	1000	20000
DSTF2060C-T	1000	20000	MBRF10150CTL-T	1000	20000
DSTF2080C	1000	20000	MBRF10200CT	1000	20000
DSTF30100C	1000	20000	MBRF10200CT-T	1000	20000
DSTF30100C-T	1000	20000	MBRF1060CTL	1000	20000
DSTF30100S	1000	20000	MBRF20100CTP	1000	20000
DSTF30120C	1000	20000	MBRF20100CTP-T	1000	20000
DSTF30120CR	1000	20000	MBRF20150CT	1000	20000
DSTF30120C-T	1000	20000	MBRF20150CT-T	1000	20000
DSTF30150C	1000	20000	MBRF20200CT	1000	20000
DSTF30150C-T	1000	20000	MBRF20200CTR	1000	20000
DSTF30200C	1000	20000	MBRF20200CT-T	1000	20000
DSTF30200C-T	1000	20000	MBRF2045CT	1000	20000
DSTF3045C	1000	20000	MBRF2045CT-T	1000	20000
DSTF3045C-T	1000	20000	MBRF2060CT	1000	20000
DSTF3060C	1000	20000	MBRF30100CTP	1000	20000
DSTF3060CR	1000	20000	MBRF30100CTP-T	1000	20000
DSTF3060C-T	1000	20000	MBRF30150CT	1000	20000
DSTF3080C	1000	20000	MBRF30150CT-T	1000	20000
DSTF40100C	1000	20000	MBRF30200CT	1000	20000
DSTF40100C-T	1000	20000	MBRF30200CT-T	1000	20000
DSTF40120C	1000	20000	MBRF3060CT	1000	20000
DSTF40120C-T	1000	20000			