

## Product Change Notification - KSRA-20KRVB706

**Date:** 24 Oct 2017  
**Product Category:** Memory; Sigma - Delta A/D Converters; 8-bit PIC Microcontrollers  
**Notification subject:** CCB 2845 Final Notice: Qualification of ASSH as an additional assembly site for selected products of 160K wafer technology available in 8L SOIC package using CuPdAu bond wire  
**Notification text:** **PCN Status:**  
 Final notification.

**Microchip Parts Affected:**

Please open the attachments found in the attachments field below labeled as PCN\_#\_Affected\_CPN.

NOTE: For your convenience Microchip includes identical files in two formats (.pdf and .xls).

**Description of Change:**

Qualification of ASSH as an additional assembly site for selected products of 160K wafer technology available in 8L SOIC package using palladium coated copper with gold flash (CuPdAu) bond wire.

**Pre Change:**

Assembled at ANAP and NSEB Assembly site

**Post Change:**

Assembled at ANAP, NSEB and ASSH Assembly site

**Pre and Post Change Summary:**

	Pre Change		Post Change		
<b>Assembly Site</b>	Amkor Technology Philippine (P1/P2), INC. (ANAP)	UTAC Thai Limited (NSEB)	Amkor Technology Philippine (P1/P2), INC. (ANAP)	UTAC Thai Limited (NSEB)	ASE- Shanghai (ASSH)
<b>Wire material</b>	Au Wire	Au Wire	Au Wire	Au Wire	CuPdAu Wire
<b>Die attach material</b>	8290	2200D	8290	2200D	EN4900G
<b>Molding compound material</b>	G600	G600	G600	G600	CEL- 9240HF10AK
<b>Lead frame material</b>	C194	C194	C194	C194	C194

**Impacts to Data Sheet:**  
None

**Change Impact:**  
None

**Reason for Change:**  
To improve productivity by qualifying ASSH as an additional assembly site.

**Change Implementation Status:**  
In Progress

**Estimated First Ship Date:**  
November 24, 2017 (date code: 1747)

NOTE: Please be advised that after the estimated first ship date customers may receive pre and post change parts.

**Time Table Summary:**

	March 2017					-->	October 2017				November 2017			
	09	10	11	12	13		40	41	42	43	44	45	46	47
Workweek														
Initial PCN Issue Date			X											
Qual Report Availability									X					
Final PCN Issue Date									X					
Estimated Implementation Date													X	

**Method to Identify Change:**  
Traceability code

**Qualification Report:**  
Please open the attachments included with this PCN labeled as PCN\_#\_Qual Report.

**Revision History:**

**March 23, 2017:** Issued initial notification.  
**October 24, 2017:** Issued final notification. Attached the Qualification Report. Revised the affected parts list. Provided estimated first ship date on November 24, 2017.

The change described in this PCN does not alter Microchip's current regulatory compliance regarding the material content of the applicable products.

**Attachment(s):**  
[PCN\\_KSRA-20KRVB706\\_Affected CPN.pdf](#)  
[PCN\\_KSRA-20KRVB706\\_Qual Report.pdf](#)  
[PCN\\_KSRA-20KRVB706\\_Affected CPN.xlsx](#)

Please contact your local [Microchip sales office](#) with questions or concerns regarding this notification.

**Terms and Conditions:**

If you wish to change your product/process change notification (PCN) profile please log on to our website at <http://www.microchip.com/PCN> sign into myMICROCHIP to open the myMICROCHIP home page, then select a profile option from the left navigation bar.

To opt out of future offer or information emails (other than product change notification emails), click here to go to [microchipDIRECT](#) and login, then click on the "My account" link, click on "Update profile" and un-check the box that states "Future offers or information about Microchip's products or services."



**MICROCHIP**

**QUALIFICATION REPORT SUMMARY**  
RELIABILITY LABORATORY

**PCN#: KSRA-20KRVB706**

**Date**

**September 11, 2017**

**Qualification of ASSH as an additional assembly site for selected products of 160K wafer technology available in 8L SOIC package using palladium coated copper with gold flash (CuPdAu) bond wire**



## MICROCHIP PACKAGE QUALIFICATION REPORT

**Purpose** Qualification of ASSH as an additional assembly site for selected products of 160K wafer technology available in 8L SOIC package using palladium coated copper with gold flash (CuPdAu) bond wire

**CN** ES096352

**QUAL ID** Q17106

**MP CODE** DE0244C2XB04

**Part No.** PIC12F683-E/SN

**Bonding No.** BDM-001172 Rev.C

**CCB No.** 2845

### Package

**Type** 8L SOIC

**Package size** 150 mils

**Die thickness** 11 mils

**Die size** 77.50 x 86.20 mils

### Lead Frame

**Paddle size** 98 x 130 mils

**Material** C194

**Surface** Double Ring

**Process** Stamped

**Lead Lock** No

**Part Number** LI-WSO000008-07

**Treatment** None

### Material

**Epoxy** EN 4900G conductive

**Wire** CuPdAu wire

**Mold Compound** CEL-9240HF10AK

**Plating Composition** Matte Tin



## MICROCHIP PACKAGE QUALIFICATION REPORT

### Manufacturing Information

Assembly Lot No.	Wafer Lot No.	Date Code
ASSH175000069.000	TMPE217387152.110	1710WUE
ASSH175100001.000	TMPE217387152.110	1711WUM
ASSH175100002.000	TMPE217387152.110	1711WUU

### Result

Pass     Fail     \_\_\_\_\_

8L SOIC (.150") assembled by ASSH pass reliability test per QCI-39000. This package was qualified the Moisture/Reflow Sensitivity Classification Level 1 at 260°C reflow temperature per IPC/JEDEC J-STD-020D standard.

# PACKAGE QUALIFICATION REPORT

Qual Report : Q17106

Test Number (Reference)	Test Condition	Standard/ Method	Qty. (Acc.)	Def/SS	Result	Remarks
<b>Moisture/Reflow Sensitivity Classification Test (At MSL Level 1)</b>	85°C/ 85%RH Moisture Soak 168 hrs. System: TABAI ESPEC Model PR-3SPH 3x Convection-Reflow 265°C max System: Vitronics Soltec MR1243  ( IPC/JEDEC J-STD-020D)	IPC/JEDEC C J-STD- 020D	198	0/198	Pass	
<b><u>Precondition</u> <u>Prior Perform</u> <u>Reliability Tests</u> (At MSL Level 1)</b>	<b>Electrical Test</b> :+25°C and 125°C System: J750  Bake 150°C, 24 hrs System: CHINEE  85°C/85%RH Moisture Soak 168 hrs. System: TABAI ESPEC Model PR-3SPH  3x Convection-Reflow 265°C max System: Vitronics Soltec MR1243  <b>Electrical Test</b> :+25°C and 125°C System: J750	JESD22- A113	693(0)	693  693  693  0/693	       Pass	Good Devices

# PACKAGE QUALIFICATION REPORT

Test Number (Reference)	Test Condition	Standard/ Method	Qty. (Acc.)	Def/SS.	Result	Remarks	
<b>Temp Cycle</b>	<b>Stress Condition:</b> (Standard) -65°C to +150°C, 500 Cycles System : TABAI ESPEC TSA-70H <b>Electrical Test:</b> + 125°C System: TTS1000 <b>Bond Strength:</b> Wire Pull (>4.0 grams) Bond Shear (>18.00 grams)	JESD22- A104		231		Parts had been pre-conditioned at 260°C	
			231(0)	0/231	Pass		
			45 (0)	0/45	Pass		
	<b>Cross section</b>		3(0) Wires	0/3	Pass		
<b>HAST</b>	<b>Stress Condition:</b> (Standard) +130°C/85%RH, 96 hrs. System: HAST 6000X <b>Electrical Test:</b> + 25°C and 125°C System: TTS10000 <b>Bond Strength:</b> Wire Pull (>4.0 grams) Bond Shear (>18.00 grams)	<b>Bias</b> JESD22- A110		231		Parts had been pre-conditioned at 260°C	
			231(0)	0/231	Pass		77 units / lot
			45 (0)	0/45	Pass		
	<b>Cross section</b>		3(0) Wires	0/3	Pass		
<b>UNBIASED-HAST</b>	<b>Stress Condition:</b> (Standard) +130°C/85%RH, 96 hrs. System: HAST 6000X <b>Electrical Test:</b> +25°C System: TTS1000	JESD22- A118		231		Parts had been pre-conditioned at 260°C	
			231(0)	0/231	Pass		77 units / lot



# PACKAGE QUALIFICATION REPORT

Qual Report : Q17106

Test Number (Reference)	Test Condition	Standard/ Method	Qty. (Acc.)	Def/SS.	Result	Remarks
<b>High Temperature Storage Life</b>	<b>Stress Condition:</b> Bake 175°C, 504 hrs System: SHEL LAB	JESD22- A103		45		
	<b>Electrical Test</b> :+25°C and 125°C System: TTS1000		45(0)	0/45	Pass	
<b>Solderability Temp 215°C</b>	<b>Steam Aging:</b> Temp 93°C,8Hrs System: SAS-3000 Solder Dipping: Solder Temp.215°C Solder material: SnPb Sn63,Pb37 System: ERSA RA 2200D Visual Inspection: External Visual Inspection	JESD22 B-102E	22 (0)	22  22  0/22	Pass	
<b>Solderability Temp 245°C</b>	<b>Steam Aging:</b> Temp 93°C,8Hrs System: SAS-3000 Solder Dipping:Solder Temp.245°C Solder material:Pb Free Sn 95.5Ag3.9 Cu0.6 System: ERSA RA 2200D Visual Inspection: External Visual Inspection	JESD22 B-102E	22 (0)	22  22  0/22	Pass	
<b>Physical Dimensions</b>	Physical Dimension, 30 units from 1 lot	JESD22 - B100/B 108	30(0) Units	0/30	Pass	
<b>Bond Strength</b>	Wire Pull (>4.0 grams)	M2011	30 (0) Wires	0/30	Pass	
<b>Data Assembly</b>	Bond Shear (>18.00 grams)	JESD22 -B116	30 (0) bonds	0/30	Pass	

KSRA-20KRVB706-CCB 2845: Initial Notice: Qualification of ASSH as an additional assembly site for selected products of 160K wafer technology available in 8L SOIC package using CuPdAu bond wire

Affected Catalog Part Number (CPN)

<b>PCN_KSRA-20KRVB706</b>
<b>CATALOG_PART_NBR</b>
24AA128-I/SN
24AA128T-I/SN
24AA128T-I/SNRVF
24FC128-E/SN
24FC128-I/SN
24FC128T-E/SN
24FC128T-I/SN
24FC256-E/SN
24FC256-I/SN
24FC256T-E/SN
24FC256T-I/SN
25AA320A-I/SN
25AA320A-I/SNB22
25AA320AT-I/SN
25AA320AT-I/SNB22
25AA640A-E/SN
25AA640A-I/SN
25AA640AT-E/SN
25AA640AT-I/SN
25AA640AT-I/SNB23
25LC320A-E/SN
25LC320A-I/SN
25LC320AT-E/SN
25LC320AT-I/SN
25LC640A-E/SN
25LC640A-I/SN
25LC640AT-E/SN
25LC640AT-I/SN
HA7600-I/SN
HA7600T-I/SN
MCP3550-50E/SN
MCP3550-60E/SN
MCP3550T-50E/SN
MCP3550T-60E/SN
MCP3551-E/SN
MCP3551T-E/SN
MCP3553-E/SN
MCP3553T-E/SN
MCP6N11-001E/SN
MCP6N11-002E/SN
MCP6N11-005E/SN
MCP6N11-010E/SN
MCP6N11-100E/SN

KSRA-20KRVB706-CCB 2845: Initial Notice: Qualification of ASSH as an additional assembly site for selected products of 160K wafer technology available in 8L SOIC package using CuPdAu bond wire

Affected Catalog Part Number (CPN)

<b>PCN_KSRA-20KRVB706</b>
<b>CATALOG_PART_NBR</b>
MCP6N11T-001E/SN
MCP6N11T-002E/SN
MCP6N11T-005E/SN
MCP6N11T-010E/SN
MCP6N11T-100E/SN
PIC12F609-E/SN
PIC12F609-I/SN
PIC12F609T-E/SN
PIC12F609T-I/SN
PIC12F609T-I/SN027
PIC12F615-E/SN
PIC12F615-I/SN
PIC12F615-I/SN083
PIC12F615T-E/SN
PIC12F615T-I/SN
PIC12F615T-I/SN020
PIC12F615T-I/SN043
PIC12F615T-I/SN051
PIC12F615T-I/SN057
PIC12F615T-I/SN058
PIC12F615T-I/SN071
PIC12F615T-I/SN076
PIC12F615T-I/SN079
PIC12F615T-I/SN083
PIC12F617-E/SN
PIC12F617-E/SN020
PIC12F617-E/SN031
PIC12F617-E/SN033
PIC12F617-E/SN034
PIC12F617-I/SN
PIC12F617-I/SN020
PIC12F617-I/SN021
PIC12F617-I/SN030
PIC12F617-I/SN032
PIC12F617-I/SN053
PIC12F617-I/SNAU
PIC12F617-I/SNC15
PIC12F617T-E/SN
PIC12F617T-E/SN020
PIC12F617T-E/SN024
PIC12F617T-E/SN026
PIC12F617T-E/SN027
PIC12F617T-E/SN031

KSRA-20KRVB706-CCB 2845: Initial Notice: Qualification of ASSH as an additional assembly site for selected products of 160K wafer technology available in 8L SOIC package using CuPdAu bond wire

Affected Catalog Part Number (CPN)

<b>PCN_KSRA-20KRVB706</b>
<b>CATALOG_PART_NBR</b>
PIC12F617T-E/SN033
PIC12F617T-E/SN034
PIC12F617T-E/SN036
PIC12F617T-E/SN037
PIC12F617T-E/SN050
PIC12F617T-E/SN051
PIC12F617T-E/SN052
PIC12F617T-E/SN055
PIC12F617T-E/SN067
PIC12F617T-E/SN071
PIC12F617T-I/SN
PIC12F617T-I/SN020
PIC12F617T-I/SN021
PIC12F617T-I/SN022
PIC12F617T-I/SN023
PIC12F617T-I/SN025
PIC12F617T-I/SN028
PIC12F617T-I/SN030
PIC12F617T-I/SN032
PIC12F617T-I/SN038
PIC12F617T-I/SN043
PIC12F617T-I/SN044
PIC12F617T-I/SN045
PIC12F617T-I/SN048
PIC12F617T-I/SN053
PIC12F617T-I/SN059
PIC12F617T-I/SNAU
PIC12F617T-I/SNC15
PIC12F635-E/SN
PIC12F635-I/SN
PIC12F635-I/SN057
PIC12F635T-I/SN
PIC12F635T-I/SN041
PIC12F635T-I/SN043
PIC12F635T-I/SN047
PIC12F635T-I/SN050
PIC12F635T-I/SN058
PIC12F635T-I/SN066
PIC12F683-E/SN
PIC12F683-E/SN084
PIC12F683-I/SN
PIC12F683-I/SN075
PIC12F683-I/SNAU

KSRA-20KRVB706-CCB 2845: Initial Notice: Qualification of ASSH as an additional assembly site for selected products of 160K wafer technology available in 8L SOIC package using CuPdAu bond wire

Affected Catalog Part Number (CPN)

<b>PCN_KSRA-20KRVB706</b>
<b>CATALOG_PART_NBR</b>
PIC12F683T-E/SN
PIC12F683T-E/SN040
PIC12F683T-E/SN079
PIC12F683T-E/SN084
PIC12F683T-E/SN092
PIC12F683T-E/SN097
PIC12F683T-E/SN098
PIC12F683T-I/SN
PIC12F683T-I/SN061
PIC12F683T-I/SN062
PIC12F683T-I/SN072
PIC12F683T-I/SN091
PIC12F683T-I/SNAU
PIC12HV609-E/SN
PIC12HV609-I/SN
PIC12HV609T-I/SN
PIC12HV615-E/SN
PIC12HV615-I/SN
PIC12HV615T-E/SN
PIC12HV615T-E/SN035
PIC12HV615T-E/SN043
PIC12HV615T-E/SN044
PIC12HV615T-I/SN
PIC12HV615T-I/SN022