



Product Change Notification - GBNG-10GPNP631

Date:

16 Apr 2018

Product Category:

32-bit PIC Microcontrollers; Touchscreen Controllers

Affected CPNs:



Notification subject:

CCB 3265 Initial Notice: Qualification of UMC Fab 8N (U08N) as an additional fabrication site for selected Atmel products manufactured with the 66.11K process technology.

Notification text:

PCN Status:

Initial notification

PCN Type:

Manufacturing Change

Microchip Parts Affected:

Please open one of the icons found in the Affected CPNs section above.

NOTE: For your convenience Microchip includes identical files in two formats (.pdf and .xls).

Description of Change:

Qualification of UMC Fab 8N (U08N) as an additional fabrication site for selected Atmel products manufactured with the 66.11K process technology.

Pre Change:

Fabricated at United Microelectronics Corporation - UMC Fab 8D (U08D) or Fab 8S (U08S) site.

Post Change:

Fabricated at United Microelectronics Corporation - UMC Fab 8D (U08D), Fab 8S (U08S) or Fab 8N (U08N) site.

Pre and Post Change Summary:

	Pre Change		Post Change		
Fabrication Supplier and Location	United Microelectronics Corporation – Fab 8D Hsin-Chu Taiwan (U08D)	United Microelectronics Corporation – Fab 8S Hsin-Chu Taiwan (U08S)	United Microelectronics Corporation – Fab 8D Hsin-Chu Taiwan (U08D)	United Microelectronics Corporation – Fab 8S Hsin-Chu Taiwan (U08S)	United Microelectronics Corporation – Fab 8N ZuZhou China (U08N)
Technology	ISO/TS16949	ISO/TS16949	ISO/TS16949	ISO/TS16949	ISO/TS16949
Die Size	No change	No change	No change	No change	No change



Wafer Diameter	8 inches	8 inches	8 inches	8 inches	8 inches
-----------------------	----------	----------	----------	----------	----------

Impacts to Data Sheet:

None

Change Impact:

None

Reason for Change:

To improve manufacturability and on-time delivery performance by qualifying UMC Fab 8N (U08N) as an additional fabrication site.

Change Implementation Status:

In Progress

Estimated Qualification Completion Date:

July 2018

Note: Please be advised the qualification completion times may be extended because of unforeseen business conditions however implementation will not occur until after qualification has completed and a final PCN has been issued. The final PCN will include the qualification report and estimated first ship date. Also note that after the estimated first ship date guided in the final PCN customers may receive pre and post change parts.

Time Table Summary:

2018	April 2018					->	July 2018
	14	15	16	17	18		
Initial PCN Issue Date			X				
Qualification Report Available							X
Final PCN Issue Date							X

Method to Identify Change:

Traceability code

Qualification Plan:

Please open the attachments included with this PCN labeled as PCN_#_Qual Plan.

Revision History:

April 16, 2018: Issued initial notification.

The change described in this PCN does not alter Microchip’s current regulatory compliance regarding the material content of the applicable products.

Attachment(s):

[PCN_GBNG-10GPNP631_Qual_Plan.pdf](#)

Please contact your local **Microchip sales office** with questions or concerns regarding this notification.

Terms and Conditions:



If you wish to change your product/process change notification (PCN) profile please log on to our website at <http://www.microchip.com/PCN> sign into myMICROCHIP to open the myMICROCHIP home page, then select a profile option from the left navigation bar.

To opt out of future offer or information emails (other than product change notification emails), click here to go to [microchipDIRECT](#) and login, then click on the "My account" link, click on "Update profile" and un-check the box that states "Future offers or information about Microchip's products or services."



MICROCHIP

QUALIFICATION PLAN SUMMARY

PCN #: GBNG-10GPNP631

Date

November 08, 2017

**Qualification of UMC Fab 8N (U08N) as an additional
fabrication site for selected Atmel products manufactured
with the 66.11K process technology.**

Purpose: Qualification of UMC Fab 8N (U08N) as an additional fabrication site for selected Atmel products manufactured with the 66.11K process technology.

CCB NO.: 3265

Qualification	Test	Sampling	
		Lots	Wafers/Lot
WLR Qualification Test			
HCI Reliability (low voltage, all devices)	Hot Carrier Induced Degradation (HCI)	3	1
NBTI Reliability	Negative Bias Temperature Instability (NBTI)	3	3
Dielectric Reliability (GOI)	FEOL Ramped Voltage (V-ramp) - Area	3	25+(2*10)
	FEOL Ramped Voltage (V-ramp) - Edge	3	25+(2*10)
	FEOL Time Dependent Dielectric Breakdown (TDDB)	3	4
Electromigration	Metal ½ & TM	1	3
Passivation Integrity	Passivation pinhole test	1	3
Characterization Tests using PCMs			
High Voltage SOA for embedded NVM	Safe Operating Area (SOA)	1	3
NVM	Data Retention	1	2
	Endurance	1	1
	Characterization vs VM & prg time	1	1
SPICE Validation for 2nd sourcing			
SPICE Model Check (2 nd source projects only)	Device scaling curves: 10xL & Wx10	1	1
	Room and High temperature leakage behavior	1	1
	Special device characterization	1	1
Wafer Level Data Retention			
Wafer sort (cp1 +cp2)			4
Pre-cycling (2cycles) @RT Write CKB			4
Bake at 25°C/150°C/250°C/300°C			4
Read-out @RT T=0/48H/168H/500H/1000H			4

Test Name / Test Conditions	Method	Qty of Lots	Sample Size/Lot
Packaged Die Product Qualification			
Early Failure Rate 24h 150°C	AEC-Q100-008	3	800
Precycling 1k flash HTOL 150°C 168h 500h 1000h	JESD22 A108	3	80
Precycling 1k flash Data-Ret 175°C - 500h		3	80
Precycling 10k Flash Data-Ret 25°C - 1000h		3	80
UNL Endurance Flash 25°C - 25K		3	80
UNL Endurance Flash 85°C - 25K		3	80
UNL Endurance Flash 105°C - 25K *		3	80
UNL Endurance Flash 125°C - 25K *		3	80
UNL Endurance Flash -40°C - 25K		3	80
Electrostatic Discharge, Human Body Model (ESD HBM)		AEC-Q100-002	1
Electrostatic Discharge, Charged Device Model (ESD CDM)	AEC-Q100-011	1	3
Latch up (LU)	AEC-Q100-004	1	6
High temperature storage 175°C – 500H	JESD22 A103	3	80
Moisture sensitivity MSL3	J-STD-020	3	320
HAST 131°C/85%RH biased 96h / 198h	JESD22 A110	3	80
UHAST 131°C / 85% RH no bias 96h	JESD22 A118	3	80
TC –65°C/150°C (500 cycles)	JESD22 A104	3	80
Humidity 85°C, 85%RH, 3.7V bias 1000h	JESD22-A101	3	80

GBNG-10GPNP631 - CCB 3265 Initial Notice: Qualification of UMC Fab 8N (U08N) as an additional fabric

Affected Catalog Part Numbers(CPN)

ATSAMC21E15A-MNT
ATSAMC21E15A-MUT
ATSAMC21E15A-MUTDY
ATSAMC21E16A-ANT
ATSAMC21E16A-AUT
ATSAMC21E16A-MNT
ATSAMC21E16A-MUT
ATSAMC21E16A-MUTDY
ATSAMC21E17A-ANT
ATSAMC21E17A-AUT
ATSAMC21E17A-MNT
ATSAMC21E17A-MUT
ATSAMC21E18A-ANT
ATSAMC21E18A-AUT
ATSAMC21E18A-MNT
ATSAMC21E18A-MUT
ATSAMC21E18A-MUTDY
ATSAMC21G15A-ANT
ATSAMC21G15A-AUT
ATSAMC21G15A-MNT
ATSAMC21G15A-MUT
ATSAMC21G16A-ANT
ATSAMC21G16A-AUT
ATSAMC21G16A-MNT
ATSAMC21G16A-MUT
ATSAMC21G17A-ANT
ATSAMC21G17A-AUT
ATSAMC21G17A-MNT
ATSAMC21G17A-MUT
ATSAMC21G18A-ANT
ATSAMC21G18A-AUT
ATSAMC21G18A-MNT
ATSAMC21G18A-MUT
ATSAMC21J15A-ANT
ATSAMC21J15A-AUT
ATSAMC21J15A-MNT
ATSAMC21J15A-MUT
ATSAMC21J16A-ANT
ATSAMC21J16A-AUT
ATSAMC21J16A-MNT
ATSAMC21J16A-MUT
ATSAMC21J17A-ANT

ATSAMC21J17A-AUT
ATSAMC21J17A-MNT
ATSAMC21J17A-MUT
ATSAMC21J17A-MUTB2
ATSAMC21J18A-ANT
ATSAMC21J18A-AUT
ATSAMC21J18A-MNT
ATSAMC21J18A-MUT
ATSAMC21N17A-ANT
ATSAMC21N18A-ANT
ATSAMD09C13A-SSUT
ATSAMD09D14A-MUT
ATSAMD10C13A-SSNT
ATSAMD10C13A-SSUT
ATSAMD10C14A-SSNT
ATSAMD10C14A-SSUT
ATSAMD10D13A-MNT
ATSAMD10D13A-MUT
ATSAMD10D13A-SSNT
ATSAMD10D13A-SSUT
ATSAMD10D14A-MNT
ATSAMD10D14A-MUT
ATSAMD10D14A-MUTB5
ATSAMD10D14A-SSNT
ATSAMD10D14A-SSUT
ATSAMD10D14A-UUT
ATSAMD10D14A-UUTB5
ATSAMD10D14A-UUTBN
ATSAMD10D14A-W-NG
ATSAMD11C14A-SSNT
ATSAMD11C14A-SSUT
ATSAMD11D14A-MNT
ATSAMD11D14A-MU
ATSAMD11D14A-MUT
ATSAMD11D14A-SSNT
ATSAMD11D14A-SSUT
ATSAMD11D14A-UUT
ATSAMD11D14A-W-NG
ATSAMD20E14B-AN
ATSAMD20E14B-ANT
ATSAMD20E14B-AU
ATSAMD20E14B-AUT
ATSAMD20E14B-MN
ATSAMD20E14B-MNT
ATSAMD20E14B-MU
ATSAMD20E14B-MUT
ATSAMD20E15B-AN

ATSAMD20E15B-ANT
ATSAMD20E15B-AU
ATSAMD20E15B-AUT
ATSAMD20E15B-MN
ATSAMD20E15B-MNT
ATSAMD20E15B-MU
ATSAMD20E15B-MUT
ATSAMD20E16B-AN
ATSAMD20E16B-ANT
ATSAMD20E16B-AU
ATSAMD20E16B-AUT
ATSAMD20E16B-MN
ATSAMD20E16B-MNT
ATSAMD20E16B-MU
ATSAMD20E16B-MUT
ATSAMD20E16B-W-N01
ATSAMD20G14B-AN
ATSAMD20G14B-ANT
ATSAMD20G14B-AU
ATSAMD20G14B-AUT
ATSAMD20G14B-MN
ATSAMD20G14B-MNT
ATSAMD20G14B-MU
ATSAMD21G16B-AU
ATSAMD21G16B-AUT
ATSAMD21G16B-MF
ATSAMD21G16B-MFT
ATSAMD21G16B-MU
ATSAMD21G16B-MUT
ATSAMD21G16L-MNT
ATSAMD21G16L-MNTA7
ATSAMD21G16L-MNTP01
ATSAMD21G16L-MUT
ATSAMD21G16L-MUTN01
ATSAMD21J15B-AF
ATSAMD21J15B-AFT
ATSAMD21J15B-AU
ATSAMD21J15B-AUT
ATSAMD21J15B-MF
ATSAMD21J15B-MFT
ATSAMD21J15B-MU
ATSAMD21J15B-MUT
ATSAMD21J16B-AF
ATSAMD21J16B-AFT
ATSAMD21J16B-AU
ATSAMD21J16B-AUT
ATSAMD21J16B-MF

ATSAMD21J16B-MFT
ATSAMD21J16B-MU
ATSAMD21J16B-MUT
ATSAMDA1E14B-ABT
ATSAMDA1E14B-MBT
ATSAMDA1E15A-MBT
ATSAMDA1E15B-ABT
ATSAMDA1E15B-MBT
ATSAMDA1E16B-ABT
ATSAMDA1E16B-MBT
ATSAMDA1G14B-ABT
ATSAMDA1G14B-MBT
ATSAMDA1G15B-ABT
ATSAMDA1G15B-MBT
ATSAMDA1G16B-ABT
ATSAMDA1G16B-MBT
ATSAMDA1J14B-ABT
ATSAMDA1J15B-ABT
ATSAMDA1J16B-ABT
ATSAML21E15B-ANT
ATSAML21E15B-AUT
ATSAML21E15B-MNT
ATSAML21E15B-MUT
ATSAML21E16B-ANT
ATSAML21E16B-AUT
ATSAML21E16B-MNT
ATSAML21E16B-MUT
ATSAML21E17B-ANT
ATSAML21E17B-AUT
ATSAML21E17B-MNT
ATSAML21E17B-MUT
ATSAML21E18B-ANT
ATSAML21E18B-AUT
ATSAML21E18B-MNT
ATSAML21E18B-MUT
ATSAML21G16B-ANT
ATSAML21G16B-AUT
ATSAML21G16B-MNT
ATSAML21G16B-MUT
ATSAML21G17B-ANT
ATSAML21G17B-AUT
ATSAML21G17B-MNT
ATSAML21G17B-MUT
ATSAML21G18B-ANT
ATSAML21G18B-AUT
ATSAML21G18B-MNT
ATSAML21G18B-MUT

ATSAML21J16B-ANT
ATSAML21J16B-AUT
ATSAML21J16B-MNT
ATSAML21J16B-MUT
ATSAML21J17B-ANT
ATSAML21J17B-AUT
ATSAML21J17B-MNT
ATSAML21J17B-MUT
ATSAML21J17B-UUT
ATSAML21J18B-ANT
ATSAML21J18B-AUT
ATSAML21J18B-MNT
ATSAML21J18B-MU
ATSAML21J18B-MUT
ATSAML21J18B-UUT
ATSAML22G16A-AUT
ATSAML22G16A-MUT
ATSAML22G17A-AUT
ATSAML22G17A-MUT
ATSAML22G17A-UUT
ATSAML22G17A-UUTA0
ATSAML22G17A-UUTA1
ATSAML22G18A-AUT
ATSAML22G18A-MUT
ATSAML22G18A-UUT
ATSAML22J16A-AUT
ATSAML22J16A-MUT
ATSAML22J17A-AUT
ATSAML22J17A-MUT
ATSAML22J18A-AUT
ATSAML22J18A-MUT
ATSAML22N16A-AUT
ATSAML22N16A-CFUT
ATSAML22N17A-AUT
ATSAML22N17A-CFUT
ATSAML22N18A-AUT
ATSAML22N18A-CFUT
ATSAML22N18A-W
ATSAML22N18A-W-NG
NI32D14-MUT
NI32D14-UUTBN
ATSAMDA1E15A-ABT
ATSAMDA1E16A-ABT
ATSAMDA1E16A-MBT
ATSAMDA1G14A-ABT
ATSAMDA1G15A-ABT
ATSAMDA1G16A-ABT

ATSAMDA1G16A-MBT
ATSAMDA1J15A-ABT
ATSAMDA1J16A-ABT
ATMPS001D14A-MUT
ATMPS001D14A-MUTA01
ATMXT144UC01-MAU023
ATMXT144UC01-MAUR023
ATMXT144U-MAU025
ATMXT144U-MAU027
ATMXT144U-MAUR025
ATMXT144U-MAUR027
ATMXT144U-UUR028
ATMXT308U-MA5U023
ATMXT308U-MA5U024
ATMXT308U-MA5U025
ATMXT308U-MA5UR023
ATMXT308U-MA5UR024
ATMXT308U-MA5UR025
ATMXT308U-MAU024
ATMXT308U-MAU025
ATMXT308U-MAUR024
ATMXT308U-MAUR025
ATMXT336UL-MAU029
ATMXT336UL-MAUR029
ATMXT336U-MAU020
ATMXT336U-MAU021
ATMXT336U-MAUR020
ATMXT336U-MAUR021
ATMXT640U-C4U020
ATMXT640U-C4U023
ATMXT640U-C4U024
ATMXT640U-C4U025
ATMXT640U-C4UR020
ATMXT640U-C4UR023
ATMXT640U-C4UR024
ATMXT640U-C4UR025
ATMXT640U-CCU020
ATMXT640U-CCU021
ATMXT640U-CCU022
ATMXT640U-CCU023
ATMXT640U-CCU024
ATMXT640U-CCU025
ATMXT640U-CCUR020
ATMXT640U-CCUR021
ATMXT640U-CCUR022
ATMXT640U-CCUR023
ATMXT640U-CCUR024

ATMXT640U-CCUR025
ATMXT748U-CCU020
ATMXT748U-CCUR020
ATMXT874U-CCU020
ATMXT874U-CCU021
ATMXT874U-CCUR020
ATMXT874U-CCUR021
ATSAMC20E15A-ANT
ATSAMC20E15A-AUT
ATSAMC20E15A-MNT
ATSAMC20E15A-MUT
ATSAMC20E16A-ANT
ATSAMC20E16A-AUT
ATSAMC20E16A-MNT
ATSAMC20E16A-MUT
ATSAMC20E17A-ANT
ATSAMC20E17A-AUT
ATSAMC20E17A-MNT
ATSAMC20E17A-MUT
ATSAMC20E18A-ANT
ATSAMC20E18A-AUT
ATSAMC20E18A-MNT
ATSAMC20E18A-MUT
ATSAMC20G15A-ANT
ATSAMC20G15A-AUT
ATSAMC20G15A-MNT
ATSAMC20G15A-MUT
ATSAMC20G16A-ANT
ATSAMC20G16A-AUN01
ATSAMC20G16A-AUT
ATSAMC20G16A-MNT
ATSAMC20G16A-MUT
ATSAMC20G17A-ANT
ATSAMC20G17A-AUT
ATSAMC20G17A-MNT
ATSAMC20G17A-MUT
ATSAMC20G18A-ANT
ATSAMC20G18A-AUT
ATSAMC20G18A-MNT
ATSAMC20G18A-MUT
ATSAMC20J15A-ANT
ATSAMC20J15A-AUT
ATSAMC20J15A-MNT
ATSAMC20J15A-MUT
ATSAMC20J16A-ANT
ATSAMC20J16A-AUT
ATSAMC20J16A-MNT

ATSAMC20J16A-MUT
ATSAMC20J17A-ANT
ATSAMC20J17A-AUT
ATSAMC20J17A-MNT
ATSAMC20J17A-MUT
ATSAMC20J18A-ANT
ATSAMC20J18A-AUT
ATSAMC20J18A-MNT
ATSAMC20J18A-MUT
ATSAMC20N17A-ANT
ATSAMC20N18A-ANT
ATSAMC21E15A-ANT
ATSAMC21E15A-AUT
ATSAMD20J14B-MU
ATSAMD20J14B-MUT
ATSAMD20J15B-AN
ATSAMD20J15B-ANT
ATSAMD20J15B-AU
ATSAMD20J15B-AUT
ATSAMD20J15B-MN
ATSAMD20J15B-MNT
ATSAMD20J15B-MU
ATSAMD20J15B-MUT
ATSAMD20J16B-AN
ATSAMD20J16B-ANT
ATSAMD20J16B-AU
ATSAMD20J16B-AUT
ATSAMD20J16B-MN
ATSAMD20J16B-MNT
ATSAMD20J16B-MU
ATSAMD20J16B-MUB7
ATSAMD20J16B-MUT
ATSAMD21E15B-AF
ATSAMD21E15B-AFT
ATSAMD21E15B-AU
ATSAMD21E15B-AUT
ATSAMD21E15B-MF
ATSAMD21E15B-MFT
ATSAMD21E15B-MFTA7
ATSAMD21E15B-MU
ATSAMD21E15B-MUT
ATSAMD21E15B-UUT
ATSAMD21E15C-UUT
ATSAMD21E15L-AF
ATSAMD21E15L-AFT
ATSAMD21E15L-MF
ATSAMD21E15L-MFT

ATSAMD21E15L-MNT
ATSAMD21E16B-AF
ATSAMD21E16B-AFT
ATSAMD21E16B-AU
ATSAMD21E16B-AUT
ATSAMD20G14B-MUT
ATSAMD20G15B-AN
ATSAMD20G15B-ANT
ATSAMD20G15B-AU
ATSAMD20G15B-AUT
ATSAMD20G15B-MN
ATSAMD20G15B-MNT
ATSAMD20G15B-MU
ATSAMD20G15B-MUT
ATSAMD20G16B-AN
ATSAMD20G16B-ANT
ATSAMD20G16B-AU
ATSAMD20G16B-AUT
ATSAMD20G16B-MN
ATSAMD20G16B-MNT
ATSAMD20G16B-MU
ATSAMD20G16B-MUT
ATSAMD20J14B-AN
ATSAMD20J14B-ANT
ATSAMD20J14B-AU
ATSAMD20J14B-AUT
ATSAMD20J14B-MN
ATSAMD20J14B-MNT
ATSAMD21E16B-MF
ATSAMD21E16B-MFT
ATSAMD21E16B-MU
ATSAMD21E16B-MUT
ATSAMD21E16B-UUT
ATSAMD21E16B-UUTA5
ATSAMD21E16B-UUTB4
ATSAMD21E16C-UUT
ATSAMD21E16C-UUTB4
ATSAMD21E16L-AF
ATSAMD21E16L-AFT
ATSAMD21E16L-MF
ATSAMD21E16L-MFT
ATSAMD21E16L-MNT
ATSAMD21E16L-MNTA4
ATSAMD21E16L-MNTA7
ATSAMD21E16L-MNTB7
ATSAMD21E16L-MNTP01
ATSAMD21G15B-AF

ATSAMD21G15B-AFT
ATSAMD21G15B-AU
ATSAMD21G15B-AUT
ATSAMD21G15B-MF
ATSAMD21G15B-MFT
ATSAMD21G15B-MU
ATSAMD21G15B-MUT
ATSAMD21G16B-AF
ATSAMD21G16B-AFT

ation site for selected Atmel products manufactured with the 66.11K process technology.