



Product Change Notification - GBNG-14WQIZ459

Date:

07 Sep 2018

Product Category:

8-bit Microcontrollers; Capacitive Touch Sensors

Affected CPNs:**Notification subject:**

CCB 3370.001 Initial Notice: Qualification of MMT as a new assembly site for selected Atmel products of 19.6K, 35.4K and 35.5K wafer technologies available in 32L VQFN package using palladium coated copper wire with gold flash (CuPdAu) bond wire.

Notification text:**PCN Status:**

Initial notification.

PCN Type:

Manufacturing Change

Microchip Parts Affected:

Please open one of the icons found in the Affected CPNs section above.

NOTE: For your convenience Microchip includes identical files in two formats (.pdf and .xls)

Description of Change:

Qualification of MMT as a new assembly site for selected Atmel products of 19.6K, 35.4K and 35.5K wafer technologies available in 32L VQFN package using palladium coated copper wire with gold flash (CuPdAu) bond wire.

Pre Change:

Assembled at ANAC assembly site with punched as a singulation method, using palladium coated copper (PdCu) bond wire.

Post Change:

Assembled at MMT assembly site with sawn as a singulation method, using palladium coated copper wire with gold flash (CuPdAu) bond wire

Pre and Post Change Summary:

	Pre Change	Post Change
Assembly Site	Amkor Assembly & Test (Shanghai) Co., LTD (ANAC)	Microchip Technology Thailand (Branch)(MMT)
Wire material	PdCu	CuPdAu
Die attach material	8290	3280
Molding compound material	G700	G700
Lead frame material	C194	C194
Singulation method	Punched	Sawn

Impacts to Data Sheet:

Yes. POD change.

Change Impact:

None

Reason for Change:

To improve on-time delivery performance by qualifying MMT as a new assembly site.

Change Implementation Status:

In Progress



Estimated Qualification Completion Date:

August 2018

Note: Please be advised the qualification completion times may be extended because of unforeseen business conditions however implementation will not occur until after qualification has completed and a final PCN has been issued. The final PCN will include the qualification report and estimated first ship date. Also note that after the estimated first ship date guided in the final PCN customers may receive pre and post change parts.

Time Table Summary:

	August 2018				
Workweek	31	32	33	34	35
Initial PCN Issue Date				X	
Qual Report Availability					X
Final PCN Issue Date					X

Method to Identify Change:

Traceability code

Qualification Plan:

Please open the attachments included with this PCN labeled as PCN_#_Qual Plan.

Revision History:

August 20, 2018: Issued initial notification.

September 07, 2018: Re-issued initial notification to reflect POD change in Impacts to Data Sheet section.

The change described in this PCN does not alter Microchip's current regulatory compliance regarding the material content of the applicable products.

Attachment(s):

[PCN_GBNG-14WQIZ459_Qual Pan.pdf](#)

Please contact your local [Microchip sales office](#) with questions or concerns regarding this notification.

Terms and Conditions:

If you wish to change your product/process change notification (PCN) profile please log on to our website at <http://www.microchip.com/PCN> sign into myMICROCHIP to open the myMICROCHIP home page, then select a profile option from the left navigation bar.

To opt out of future offer or information emails (other than product change notification emails), click here to go to [microchipDIRECT](#) and login, then click on the "My account" link, click on "Update profile" and un-check the box that states "Future offers or information about Microchip's products or services."



MICROCHIP

QUALIFICATION PLAN SUMMARY

PCN #: GBNG-14WQIZ459

Date:

April 19, 2018

Qualification of MMT as a new assembly site in selected Atmel products of 19.6K, 35.4K and 35.5K wafer technologies available in 32L VQFN package using palladium coated copper wire with gold flash (CuPdAu) bond wire.

Purpose: Qualification of MMT as a new assembly site in selected Atmel products of 19.6K, 35.4K and 35.5K wafer technologies available in 32L VQFN package using palladium coated copper wire with gold flash (CuPdAu) bond wire.

CCB No.: 3370

		Qualification Report
<u>Misc.</u>	Assembly site	MMT
	BD Number	BDM-001739 rev. A
	MP Code (MPC)	35473QRXBQUL
	Part Number (CPN)	ATMEGA328P-MNR
<u>Lead-Frame</u>	Paddle size	150x150 mils
	Material	C194
	Surface	Bare Cu on paddle
	Treatment	BOT
	Process	Etched
	Lead-lock	Yes
	Part Number	10103202
	Lead Plating	Matte Tin
<u>Bond Wire</u>	Material	Au
<u>Die Attach</u>	Part Number	3280
<u>MC</u>	Part Number	G700LTD
<u>PKG</u>	PKG Type	VQFN
	Pin/Ball Count	32
	PKG width/size	5x5x0.9mm
<u>Die</u>	Die Thickness	11 mils
	Die Size	134.3 x 124.5 mils
	Fab Process (site)	35.4K/MCSO

Test Name	Conditions	Sample Size	Min. Qty of Spares per Lot (should be properly marked)	Qty of Lots	Total Units	Fail Accept Qty	Est. Dur. Days	Test Site	Special Instructions
Standard Pb-free Solderability	J-STD-002; Perform 8 hour steam aging for Matte tin finish and 1 hour steam aging for NiPdAu finish prior to testing. Standard Pb-free: Matte tin/ NiPdAu finish, SAC solder, wetting temp 245°C for both SMD & through hole packages.	22	5	1	27	> 95% lead coverage	5	MPHL	Standard Pb-free solderability is the requirement. SnPb solderability (backward solderability- SMD reflow soldering) is required for any plating related changes and highly recommended for other package BOM changes.
Backward Solderability	J-STD-002; Perform 8 hours steam aging for Matte tin finish and 1 hour steam aging for NiPdAu finish prior to testing. Backward: Matte tin/ NiPdAu finish, SnPb solder, wetting temp 215°C for SMD.	22	5	1	27	> 95% lead coverage	5	MPHL	
Wire Bond Pull - WBP	Mil. Std. 883-2011	5	0	3	15	0 fails after TC	5	MMT/MPHL	30 bonds from a minimum of 5 devices.
Wire Bond Shear - WBS	CDF-AEC-Q100-001	5	0	3	15	0	5	MMT/MPHL	30 bonds from a minimum of 5 devices.
Wire Sweep		5	0	3	15	0		MMT	Required for any reduction in wire bond thickness.
Physical Dimensions	Measure per JESD22 B100 and B108	10	0	3	30	0	5	MMT	
External Visual	Mil. Std. 883-2009/2010	All devices prior to submission for qualification testing	0	3	ALL	0	5	MMT/MPHL	

Test Name	Conditions	Sample Size	Min. Qty of Spares per Lot (should be properly marked)	Qty of Lots	Total Units	Fail Accept Qty	Est. Dur. Days	Test Site	Special Instructions
HTSL (High Temp Storage Life)	+175 C for 504 hours. Electrical test pre and post stress at +25°C and hot temp.	45	5	1	50	0	25	MPHL	
Preconditioning - Required for surface mount devices	+150°C Bake for 24 hours, moisture loading requirements per MSL level + 3X reflow at peak reflow temperature per Jedec-STD-020D for package type; Electrical test pre and post stress at +25°C. MSL1 @ 260°C	231	15	3	738	0	15	MPHL	Spares should be properly identified. 77 parts from each lot to be used for HAST, Autoclave, Temp Cycle test.
HAST	+130°C/85% RH for 96 hours. Electrical test pre and post stress at +25°C and hot temp.	77	5	3	246	0	10	MPHL	Spares should be properly identified. Use the parts which have gone through Pre-conditioning.
Unbiased HAST	+130°C/85% RH for 96 hrs. Electrical test pre and post stress at +25°C.	77	5	3	246	0	10	MPHL	Spares should be properly identified. Use the parts which have gone through Pre-conditioning.
Temp Cycle	-65°C to +150°C for 500 cycles. Electrical test pre and post stress at hot temp; 3 gram force WBP, on 5 devices from 1 lot, test following Temp Cycle stress.	77	5	3	246	0	15	MPHL	Spares should be properly identified. Use the parts which have gone through Pre-conditioning.

GBNG-14WQIZ459 - CCB 3370.001 Initial 35.4K and 35.5K wafer technologies available in 32L VQFN package u

Affected Catalog Part Numbers(CPN)

AT42QT1110-MUR
AT42QT11C12-MUR
AT42QT1244-MU
AT42QT1244-MUR
AT42QT1245-MU
AT42QT1245-MUR
AT42QT2100-MUR
AT42QT4160-MUR
ATMEGA168-20MQ
ATMEGA168-20MQR
ATMEGA168-20MU
ATMEGA168-20MUR
ATMEGA168A-MU
ATMEGA168A-MUR
ATMEGA168P-20MQ
ATMEGA168P-20MQR
ATMEGA168P-20MU
ATMEGA168P-20MUR
ATMEGA168PA-MN
ATMEGA168PA-MNR
ATMEGA168PA-MU
ATMEGA168PA-MUA1
ATMEGA168PA-MUR
ATMEGA168PA-MUR431
ATMEGA168PA-MURA1
ATMEGA168PV-10MU
ATMEGA168PV-10MUR
ATMEGA168PV-10MUR455
ATMEGA168V-10MQ
ATMEGA168V-10MQR
ATMEGA168V-10MQR610
ATMEGA168V-10MU
ATMEGA168V-10MUR
ATMEGA168V-10MUR598
ATMEGA328-MU
ATMEGA328-MUR
ATMEGA328P-MN
ATMEGA328P-MNR
ATMEGA328P-MU
ATMEGA328P-MUR
ATMEGA48-20MU
ATMEGA48-20MUR

ATMEGA48A-MU
ATMEGA48A-MUR
ATMEGA48P-20MU
ATMEGA48P-20MUR
ATMEGA48PA-MN
ATMEGA48PA-MNR
ATMEGA48PA-MU
ATMEGA48PA-MUR
ATMEGA48PA-MURA5
ATMEGA48PV-10MU
ATMEGA48PV-10MUR
ATMEGA48V-10MU
ATMEGA48V-10MUR
ATMEGA48V-10MUR173
ATMEGA48V-10MUR348
ATMEGA48V-10MURA3
ATMEGA8-16MU
ATMEGA8-16MUR
ATMEGA88-20MU
ATMEGA88-20MUR
ATMEGA88-20MURA4
ATMEGA88A-MU
ATMEGA88A-MUR
ATMEGA88P-20MU
ATMEGA88P-20MUR
ATMEGA88PA-MN
ATMEGA88PA-MNR
ATMEGA88PA-MU
ATMEGA88PA-MUR
ATMEGA88PA-MURA06
ATMEGA88PA-MURA6
ATMEGA88PV-10MU
ATMEGA88PV-10MUR
ATMEGA88V-10MU
ATMEGA88V-10MUR
ATMEGA88V-10MUR360
ATMEGA88V-10MUR378
ATMEGA88V-10MUR379
ATMEGA88V-10MURA1
ATMEGA8A-MN
ATMEGA8A-MNR
ATMEGA8A-MU
ATMEGA8A-MUR
ATMEGA8A-MURA7
ATMEGA8L-8MU
ATMEGA8L-8MUA4
ATMEGA8L-8MUR

ATMEGA8L-8MURA3
ATMEGA8L-8MURA5
ATTINY26-16MQR
ATTINY26-16MU
ATTINY26-16MUR
ATTINY261A-MF
ATTINY261A-MFR
ATTINY261A-MFRA0
ATTINY261A-MN
ATTINY261A-MNR
ATTINY261A-MU
ATTINY261A-MUR
ATTINY26L-8MU
ATTINY26L-8MUR
ATTINY28L-4MU
ATTINY28L-4MUR
ATTINY28V-1MU
ATTINY28V-1MUR
ATTINY461-20MU
ATTINY461-20MUR
ATTINY461-20MUR437
ATTINY461-20MUR553
ATTINY461A-MU
ATTINY461A-MUR
ATTINY461V-10MU
ATTINY461V-10MUR
ATTINY48-MU
ATTINY48-MUR
ATTINY48-MUR522
ATTINY48-MUR547
ATTINY861-20MU
ATTINY861-20MUR
ATTINY861-20MUR430
ATTINY861A-MU
ATTINY861A-MUR
ATTINY861V-10MU
ATTINY861V-10MUR
ATTINY88-MU
ATTINY88-MUR
ATTINY88-MURA1
QT60160-ISG
QT60240-ISG