



Product Change Notification - ASER-30EHFB658

Date:

01 Jun 2020

Product Category:

Clock and Timing - Oscillators; Others

Affected CPNs:**Notification subject:**

CCB 3960 Initial Notice: Qualification of new bill of materials (BOM) for selected Micrel products available in 4L VDFN (5.0x3.2x0.9mm) package at NSEB assembly site.

Notification text:**PCN Status:**

Initial notification.

PCN Type:

Manufacturing Change

Microchip Parts Affected:

Please open one of the icons found in the Affected CPNs section above.

NOTE: For your convenience Microchip includes identical files in two formats (.pdf and .xls).

Description of Change:

Qualification of new bill of materials (BOM) for selected Micrel products available in 4L VDFN (5.0x3.2x0.9mm) package at NSEB assembly site.

Pre Change:

Assembled at NSEB using NEX-130CT die 1 attach material, 8200T die 2 attach material, G770HCD molding compound, and Q3-6646 die coat.

Post Change:

Assembled at NSEB using HR-5104 die 1 attach material, 2200D die 2 attach material, G700LTD molding compound, and JCR6109 die coat.

Pre and Post Change Summary:

	Pre Change	Post Change
Assembly Site	UTAC Thai Limited LTD. (NSEB)	UTAC Thai Limited LTD. (NSEB)
Lead Frame Material	A194	A194
Bond Wire Material	Au	Au
Die 1 Attach Material	NEX-130CT	HR-5104
Die 2 Attach Material	8200T	2200D
Molding compound material	G770HCD	G700LTD
Die Coat	Q3-6646	JCR6109

Impacts to Data Sheet:

None.



Change Impact:

None.

Reason for Change:

To improve manufacturability by qualifying a new die attach material, molding compound, and die coat.

Change Implementation Status:

In Progress

Estimated Qualification Completion Date:

January 2020

Note: Please be advised the qualification completion times may be extended because of unforeseen business conditions however implementation will not occur until after qualification has completed and a final PCN has been issued. The final PCN will include the qualification report and estimated first ship date. Also note that after the estimated first ship date guided in the final PCN customers may receive pre and post change parts.

Time Table Summary:

	November 2019					-->	January 2020				
Workweek	44	45	46	47	48		01	02	03	04	05
Initial PCN Issue Date				X							
Qual Report Availability										X	
Final PCN Issue Date										X	

Method to Identify Change:

Traceability code.

Qualification Plan:

Please open the attachments included with this PCN labeled as PCN_#_Qual_Plan.

Revision History:

November 20, 2019: Issued initial notification.

June 1, 2020: Reissued initial notification to update qualification plan. This is a grade 2 qualification.

The change described in this PCN does not alter Microchip's current regulatory compliance regarding the material content of the applicable products.

Attachment(s):

[PCN_ASER-30EHFB658_Qual Plan.pdf](#)

Please contact your local [Microchip sales office](#) with questions or concerns regarding this notification.

Terms and Conditions:



If you wish to receive Microchip PCNs via email please register for our PCN email service at our [PCN home page](#) select register then fill in the required fields. You will find instructions about registering for Microchips PCN email service in the [PCN FAQ](#) section.

If you wish to change your PCN profile, including opt out, please go to the [PCN home page](#) select login and sign into your myMicrochip account. Select a profile option from the left navigation bar and make the applicable selections.



MICROCHIP

QUALIFICATION PLAN SUMMARY

PCN #: ASER-30EHFB658

Date:

September 24, 2019

**Qualification of new bill of materials (BOM) for selected
Micrel products available in 4L VDFN (5.0x3.2x0.9mm)
package at NSEB assembly site.
This is a Q100 grade 2 qualification.**

Purpose: _____ Qualification of new bill of materials (BOM) for selected Micrel products available in 4L VDFN (5.0x3.2x0.9mm) package at NSEB assembly site. This is a Q100 grade 2 qualification.

CCB No: _____ 3960

MP code: _____ 3610R9H6A003

Part No.: _____ D4BB-L3

BD No: _____ BDE-005830 Rev.02

Package:

Type: _____ 4L VDFN COL

Width or Size: _____ 5.0 x 3.2 x 0.9 mm

Leadframe:

Part Number: _____ FR0293

Paddle Size: _____ COL

Material: _____ A194

Pad Plating: _____ Roughen NiPdAu

Process: _____ Etched

Lead-lock (Y/N): _____ Yes

Lead Finish: _____ NiPdAu

LF Thickness: _____ 8 mils

Wire:

Material: _____ Au

Die Attach Epoxy:

Part Number: _____ HR-5104

Conductive: _____ No

Part Number: _____ 2200D

Conductive: _____ Yes

Mold Compound: _____ G700LTD

Die Coat: _____ JCR6109

Test Name	Conditions	Reliability Stress Read Point	Pre & Post Reliability Stress Test Temperature	Sample Size	Min. Qty of Spares per Lot (should be properly marked)	Qty of Lots	Total Units	Fail Accept Qty	Special Instructions
Standard Pb-free Solderability	J-STD-002D ; Perform 8 hours of steam aging for Matte tin finish and 1 hour steam aging for NiPdAu finish prior to testing. Standard Pb-free: Matte tin/ NiPdAu finish, SAC solder, wetting temp 245°C for both SMD & through hole packages.			22	5	1	27	>95% lead coverage	Standard Pb-free solderability is the requirement. SnPb solderability (backward solderability- SMD reflow soldering) is required for any plating related changes and highly recommended for other package BOM changes.
Wire Bond Pull - WBP	Mil. Std. 883-2011			5	0	1	5	0 fails after TC	30 bonds from a min. 5 devices.
Wire Bond Shear - WBS	CDF-AEC-Q100-001			5	0	1	5	0	30 bonds from a min. 5 devices.
Physical Dimensions	Measure per JESD22 B100 and B108			10	0	3	30	0	
External Visual	Mil. Std. 883-2009/2010			All devices prior to submission for qualification testing	0	3	ALL	0	
HTSL (High Temp Storage Life)	JESD22-A103 +150°C	Grade 2: 1000 hrs (150°C)	Grade 2: +25°C & +105°C	45	5	1	50	0	Spares should be properly identified.

Test Name	Conditions	Reliability Stress Read Point	Pre & Post Reliability Stress Test Temperature	Sample Size	Min. Qty of Spares per Lot (should be properly marked)	Qty of Lots	Total Units	Fail Accept Qty	Special Instructions
Preconditioning - Required for surface mount devices	J-STD-020JESD22-A113+150°C Bake for 24 hours, moisture loading requirements per MSL level + 3X reflow at peak reflow temperature per Jedec-STD-020E for package type. MSL 1@260°C		Grade 2: +25°C	231+ 45 (for devices requiring PTC)	15+ 5 (for devices requiring PTC)	3	738+ 50 (for devices requiring PTC)	0	Spares should be properly identified. 77 parts from each lot to be used for HAST, uHAST, Temp Cycle test. 45 parts from one lot to be used for PTC test (for devices requiring PTC).
HAST	JESD22-A101 or A110 +130°C/85% RH for 96 hrs	Grade 2: 96 hrs (+130°C/85% RH)	Grade 2: +25°C & +105°C	77	5	3	246	0	Spares should be properly identified. Use the parts which have gone through Pre-conditioning.
UHAST	JESD22-A102, A118, or A101 +130°C/85% RH for 96 hrs	Grade 2: 96 hrs (+130°C/85% RH)	Grade 2: +25°C	77	5	3	246	0	Spares should be properly identified. Use the parts which have gone through Pre-conditioning.
Temp Cycle	JESD22-A104 -65°C to +150°C	Grade 2: 500 cycles (-65°C to 150°C)	Grade 2: +105°C	77	5	3	246	0	Spares should be properly identified. Use the parts which have gone through Pre-conditioning.

ASER-30EHFB658 - CCB 3960 Initial Notice: Qualification of new bill of materials (BOM) for selected Mi

Affected Catalog Part Numbers(CPN)

DSC1001BL2-050.0000TVAO
DSC1000BL3-PROG
DSC1000BL5-PROG
DSC1001BC1-020.0000
DSC1001BC1-020.0000T
DSC1001BC1-024.0000
DSC1001BC1-024.0000T
DSC1001BC1-050.0000T
DSC1001BE1-001.4850
DSC1001BE1-001.4850T
DSC1001BE1-001.8432
DSC1001BE1-001.8432T
DSC1001BE1-012.0000
DSC1001BE1-012.0000T
DSC1001BE1-014.3182
DSC1001BE1-014.3182T
DSC1001BE1-014.7456
DSC1001BE1-014.7456T
DSC1001BE1-016.0000T
DSC1001BE1-024.0000
DSC1001BE1-024.0000T
DSC1001BE1-025.0000
DSC1001BE1-025.0000T
DSC1001BE1-026.0000
DSC1001BE1-026.0000T
DSC1001BE1-040.0000
DSC1001BE1-048.0000
DSC1001BE1-048.0000T
DSC1001BI1-024.0000
DSC1001BI1-024.0000T
DSC1001BI1-024.5760
DSC1001BI1-024.5760T
DSC1001BI1-025.0000
DSC1001BI1-025.0000T
DSC1001BI1-026.0000
DSC1001BI1-026.0000T
DSC1001BI1-027.0000
DSC1001BI1-027.0000T
DSC1001BI1-030.0000T
DSC1001BI1-032.0000
DSC1001BI1-032.0000T
DSC1001BI1-033.0000

DSC1001BI1-033.0000T
DSC1001BI1-033.3330
DSC1001BI1-033.3330T
DSC1001BI1-038.4000
DSC1001BI1-038.4000T
DSC1001BI1-040.0000
DSC1001BI1-040.0000T
DSC1001BI1-048.0000
DSC1001BI1-048.0000T
DSC1001BI1-050.0000
DSC1001BI1-050.0000T
DSC1001BI1-054.0000
DSC1001BI1-060.0000
DSC1001BI1-060.0000T
DSC1001BI1-066.6666
DSC1001BI1-066.6666T
DSC1001BI1-075.0000
DSC1001BI1-080.0000
DSC1001BI1-080.0000T
DSC1001BI1-099.0000
DSC1001BI1-099.0000T
DSC1001BI1-100.0000
DSC1001BI1-100.0000T
DSC1001BI1-125.0000
DSC1001BI1-125.0000T
DSC1001BI1-133.0000
DSC1001BI1-133.0000T
DSC1001BI2-001.5440
DSC1001BI2-001.5440T
DSC1001BI2-001.8432T
DSC1001BI2-002.0480T
DSC1001BI2-003.1250
DSC1001BI2-003.1250T
DSC1001BI2-003.6864
DSC1001BI2-003.6864T
DSC1001BI2-004.0000
DSC1001BI2-004.0000T
DSC1001BI2-005.5296
DSC1001BI2-005.5296T
DSC1001BI2-006.0000
DSC1001BI2-006.0000T
DSC1001BI2-007.3728
DSC1001BI2-007.3728T
DSC1001BI2-008.0000
DSC1001BI2-008.0000T
DSC1001BI2-010.0000
DSC1001BI2-010.0000T

DSC1001BI2-011.0592
DSC1001BI2-011.0592T
DSC1001BI2-012.0000
DSC1001BI2-012.0000T
DSC1001BI2-012.2880
DSC1001BI2-012.2880T
DSC1001BI2-012.2888
DSC1001BI2-012.2888T
DSC1001BI2-012.5000
DSC1001BI2-012.5000T
DSC1001BI2-013.0810
DSC1001BI2-013.0810T
DSC1001BI2-014.3181
DSC1001BI2-014.3181T
DSC1001BI2-014.7456
DSC1001BI2-014.7456T
DSC1001BI2-016.0000
DSC1001BI2-016.0000T
DSC1001BI2-016.3840
DSC1001BE1-050.0000
DSC1001BE1-050.0000T
DSC1001BE1-060.0000
DSC1001BE1-060.0000T
DSC1001BE1-066.6666
DSC1001BE1-066.6666T
DSC1001BE1-125.0000
DSC1001BE1-125.0000T
DSC1001BE1-133.0000
DSC1001BE1-133.0000T
DSC1001BE1-133.3300T
DSC1001BE2-001.6000
DSC1001BE2-010.0000
DSC1001BE2-012.0000T
DSC1001BE2-012.2880
DSC1001BE2-012.2880T
DSC1001BE2-014.7450
DSC1001BE2-014.7450T
DSC1001BE2-014.7456
DSC1001BE2-014.7456T
DSC1001BE2-024.0000
DSC1001BE2-025.0000
DSC1001BE2-027.0000
DSC1001BE2-033.3330
DSC1001BE2-048.0000
DSC1001BE2-048.0000T
DSC1001BE2-050.0000
DSC1001BE2-090.0000

DSC1001BE2-090.0000T
DSC1001BE2-100.0000
DSC1001BE2-125.0000T
DSC1001BE3-022.1184
DSC1001BE3-022.1184T
DSC1001BE3-026.0000
DSC1001BE3-026.0000T
DSC1001BE5-012.0000
DSC1001BE5-012.0000T
DSC1001BE5-016.0000
DSC1001BE5-016.0000T
DSC1001BE5-020.0000
DSC1001BE5-020.0000T
DSC1001BE5-022.5792
DSC1001BE5-022.5792T
DSC1001BE5-024.0000
DSC1001BE5-024.0000T
DSC1001BE5-030.6400
DSC1001BE5-030.6400T
DSC1001BE5-033.3330
DSC1001BE5-033.3330T
DSC1001BE5-064.0000
DSC1001BE5-064.0000T
DSC1001BI1-001.8432
DSC1001BI1-001.8432T
DSC1001BI1-003.6864
DSC1001BI1-003.6864T
DSC1001BI1-004.0000
DSC1001BI1-004.0000T
DSC1001BI1-008.0000
DSC1001BI1-008.0000T
DSC1001BI1-010.0000
DSC1001BI1-010.0000T
DSC1001BI1-011.0592
DSC1001BI1-011.0592T
DSC1001BI1-012.0000
DSC1001BI1-012.0000T
DSC1001BI1-012.2880
DSC1001BI1-012.2880T
DSC1001BI1-016.0000T
DSC1001BI1-019.6608
DSC1001BI1-019.6608T
DSC1001BI1-020.0000
DSC1001BI1-020.0000T
DSC1001BI1-022.1184
DSC1001BI1-022.1184T
DSC1001BI2-016.3840T

DSC1001BI2-016.9344
DSC1001BI2-016.9344T
DSC1001BI2-018.4320
DSC1001BI2-018.4320T
DSC1001BI2-020.0000
DSC1001BI2-020.0000T
DSC1001BI2-020.0016T
DSC1001BI2-022.5790T
DSC1001BI2-022.8000
DSC1001BI2-024.0000
DSC1001BI2-024.0000T
DSC1001BI2-024.5760
DSC1001BI2-024.5760T
DSC1001BI2-025.0000
DSC1001BI2-025.0000T
DSC1001BI2-026.0000
DSC1001BI2-026.0000T
DSC1001BI2-027.0000
DSC1001BI2-027.0000T
DSC1001BI2-028.6363
DSC1001BI2-028.6363T
DSC1001BI2-028.8000T
DSC1001BI2-029.4912
DSC1001BI2-029.4912T
DSC1001BI2-030.0000
DSC1001BI2-030.0000T
DSC1001BI2-032.0000T
DSC1001BI2-033.0000
DSC1001BI2-033.0000T
DSC1001BI2-033.3330
DSC1001BI2-033.3330T
DSC1001BI2-040.0000
DSC1001BI2-040.0000T
DSC1001BI2-040.6800
DSC1001BI2-040.6800T
DSC1001BI2-042.5000
DSC1001BI2-042.5000T
DSC1001BI2-044.0000T
DSC1001BI2-048.0000
DSC1001BI2-048.0000T
DSC1001BI2-049.0908T
DSC1001BI2-050.0000
DSC1001BI2-050.0000T
DSC1001BI2-054.0000
DSC1001BI2-054.0000T
DSC1001BI2-059.0000T
DSC1001BI2-062.5000T

DSC1001BI2-080.0000T
DSC1001BI2-099.0000
DSC1001BI2-099.0000T
DSC1001BI2-100.0000
DSC1001BI2-100.0000T
DSC1001BI2-106.2500T
DSC1001BI2-125.0000
DSC1001BI2-125.0000T
DSC1001BI2-133.0000
DSC1001BI2-133.0000T
DSC1001BI2-133.3330
DSC1001BI2-133.3330T
DSC1001BI2-148.5000
DSC1001BI2-148.5000T
DSC1001BI3-012.0000
DSC1001BI3-012.0000T
DSC1001BI3-020.0000
DSC1001BI3-020.0000T
DSC1001BL5-075.0000
DSC1001BL5-075.0000T
DSC1001BL5-080.0000
DSC1001BL5-080.0000T
DSC1001BL5-095.0000
DSC1001BL5-100.0000
DSC1001BL5-100.0000T
DSC1001BL5-106.2500
DSC1001BL5-106.2500T
DSC1001BL5-108.0000
DSC1001BL5-108.0000T
DSC1001BL5-120.0000
DSC1001BI3-024.0000
DSC1001BI3-024.0000T
DSC1001BI3-033.0000
DSC1001BI3-033.0000T
DSC1001BI3-050.0000
DSC1001BI3-050.0000T
DSC1001BI5-001.6000
DSC1001BI5-001.6000T
DSC1001BI5-003.6864T
DSC1001BI5-004.0000T
DSC1001BI5-007.3728T
DSC1001BI5-008.0000
DSC1001BI5-008.0000T
DSC1001BI5-010.0000
DSC1001BI5-010.0000T
DSC1001BI5-012.0000T
DSC1001BI5-013.5600

DSC1001BI5-013.5600T
DSC1001BI5-014.7456
DSC1001BI5-014.7456T
DSC1001BI5-016.0000
DSC1001BI5-016.0000T
DSC1001BI5-018.4320
DSC1001BI5-018.4320T
DSC1001BI5-019.6800
DSC1001BI5-019.6800T
DSC1001BI5-020.0000
DSC1001BI5-020.0000T
DSC1001BI5-024.0000
DSC1001BI5-024.0000T
DSC1001BI5-025.0000
DSC1001BI5-025.0000T
DSC1001BI5-027.0000
DSC1001BI5-027.0000T
DSC1001BI5-028.6363
DSC1001BI5-028.6363T
DSC1001BI5-030.0000T
DSC1001BI5-032.0000T
DSC1001BI5-033.0000
DSC1001BI5-033.0000T
DSC1001BI5-033.3330T
DSC1001BI5-040.0000
DSC1001BI5-040.0000T
DSC1001BI5-040.9600
DSC1001BI5-040.9600T
DSC1001BI5-048.0000T
DSC1001BI5-050.0000
DSC1001BI5-050.0000T
DSC1001BI5-066.0000T
DSC1001BI5-066.6660
DSC1001BI5-066.6660T
DSC1001BI5-066.6666T
DSC1001BI5-072.0000T
DSC1001BI5-080.0000
DSC1001BI5-080.0000T
DSC1001BI5-084.0000
DSC1001BI5-084.0000T
DSC1001BI5-090.0000
DSC1001BI5-090.0000T
DSC1001BI5-100.0000
DSC1001BI5-100.0000T
DSC1001BI5-120.0000T
DSC1001BI5-125.0000
DSC1001BI5-125.0000T

DSC1001BI5-125.0031
DSC1001BI5-125.0031T
DSC1001BI5-133.3330
DSC1001BI5-133.3330T
DSC1001BL1-002.1760
DSC1001BL1-016.0000
DSC1001BL1-016.0000T
DSC1001BL1-027.0000T
DSC1004BI2-010.0000
DSC1001BL5-120.0000T
DSC1001BL5-125.0000
DSC1001BL5-125.0000T
DSC1001BL5-133.3330T
DSC1001BL5-150.0000T
DSC1003BE1-024.0000
DSC1003BE1-024.0000T
DSC1003BE1-025.0000
DSC1003BE1-025.0000T
DSC1003BI1-008.0000
DSC1003BI1-008.0000T
DSC1003BI1-060.0000T
DSC1003BI1-100.0000
DSC1003BI1-100.0000T
DSC1003BI2-025.0000
DSC1003BI2-025.0000T
DSC1003BI5-001.6500
DSC1003BI5-001.6500T
DSC1003BI5-001.7000
DSC1003BI5-001.7000T
DSC1003BI5-040.0000
DSC1003BI5-040.0000T
DSC1003BL1-010.0000
DSC1003BL1-010.0000T
DSC1003BL3-008.1920
DSC1003BL3-008.1920T
DSC1003BL3-010.2400
DSC1003BL3-010.2400T
DSC1003BL3-013.8420
DSC1003BL3-013.8420T
DSC1003BL3-018.4320
DSC1003BL3-018.4320T
DSC1003BL3-020.0000
DSC1003BL3-020.0000T
DSC1003BL3-025.0000
DSC1003BL3-025.0000T
DSC1003BL3-030.0000
DSC1003BL3-030.0000T

DSC1003BL3-032.7680
DSC1003BL3-032.7680T
DSC1004BI2-010.0000T
DSC1004BI2-033.0000
DSC1004BI2-100.0000
DSC1004BI5-005.0000
DSC1004BI5-005.0000T
DSC1004BI5-016.0000
DSC1004BI5-016.0000T
DSC1004BI5-121.5000
DSC1004BI5-121.5000T
DSC1004BL2-024.0000
DSC1004BL2-024.0000T
DSC1004BL2-025.0000
DSC1004BL2-025.0000T
DSC8001BI2
DSC8001BI2T
DSC8001BI5
DSC8001BI5T
DSC8001BL2
DSC8001BL5
DSC8001BL5T
DSC8003BI2
DSC8003BI2T
DSC8004BI2
DSC1001BL1-048.0000T
DSC1001BL1-060.0000
DSC1001BL1-060.0000T
DSC1001BL2-020.0000
DSC1001BL2-020.0000T
DSC1001BL2-024.0000
DSC1001BL2-024.0000T
DSC1001BL2-025.0000
DSC1001BL2-025.0000T
DSC1001BL2-026.0000
DSC1001BL2-026.0000T
DSC1001BL2-027.0000T
DSC1001BL2-048.0000
DSC1001BL2-048.0000T
DSC1001BL2-050.0000
DSC1001BL2-050.0000T
DSC1001BL2-125.0000
DSC1001BL2-125.0000T
DSC1001BL5-001.1385
DSC1001BL5-001.1385T
DSC1001BL5-001.1386
DSC1001BL5-001.1386T

DSC1001BL5-001.1387
DSC1001BL5-001.1387T
DSC1001BL5-001.1388
DSC1001BL5-001.1388T
DSC1001BL5-001.1389
DSC1001BL5-001.1389T
DSC1001BL5-004.0000
DSC1001BL5-004.0000T
DSC1001BL5-008.0000T
DSC1001BL5-010.0000
DSC1001BL5-010.0000T
DSC1001BL5-012.0000T
DSC1001BL5-014.7456
DSC1001BL5-014.7456T
DSC1001BL5-016.0000
DSC1001BL5-016.0000T
DSC1001BL5-020.0000T
DSC1001BL5-024.0000T
DSC1001BL5-024.5760T
DSC1001BL5-025.0000
DSC1001BL5-025.0000T
DSC1001BL5-026.0000
DSC1001BL5-026.0000T
DSC1001BL5-026.6500
DSC1001BL5-026.6500T
DSC1001BL5-026.7000
DSC1001BL5-026.7000T
DSC1001BL5-030.0000
DSC1001BL5-030.0000T
DSC1001BL5-032.0000
DSC1001BL5-032.0000T
DSC1001BL5-033.0000
DSC1001BL5-033.0000T
DSC1001BL5-033.3330
DSC1001BL5-033.3330T
DSC1001BL5-040.0000T
DSC1001BL5-048.0000T
DSC1001BL5-049.5000
DSC1001BL5-049.5000T
DSC1001BL5-050.0000
DSC1001BL5-050.0000T
DSC1001BL5-058.9824
DSC1001BL5-058.9824T
DSC1001BL5-064.0000
DSC1001BL5-064.0000T
DSC1001BL5-066.0000
DSC1001BL5-066.0000T

DSC1001BL5-066.6666T
DSC1001BL5-072.0000
DSC1001BL5-072.0000T