



Product Change Notification / LIAL-02XWMF227

Date:

05-May-2022

Product Category:

Linear Comparators, Linear Op Amps, Power Management - System Supervisors/Voltage Detectors

PCN Type:

Manufacturing Change

Notification Subject:

CCB 5129 Initial Notice: Qualification of G700 as a new molding compound material and NiPdAuAg with roughened as a new lead frame DAP surface prep for selected MIC7300, MIC2778, MIC833, and MIC2779 device families available in 5L SOT23 package assembled at STAR assembly site.

Affected CPNs:

[LIAL-02XWMF227_Affected_CPN_05052022.pdf](#)

[LIAL-02XWMF227_Affected_CPN_05052022.csv](#)

Notification Text:

PCN Status:Initial Notification

PCN Type:Manufacturing Change

Microchip Parts Affected:Please open one of the files found in the Affected CPNs section.

Note: For your convenience Microchip includes identical files in two formats (.pdf and .xls)

Description of Change:Qualification of G700 as a new molding compound material and NiPdAuAg with roughened as a new lead frame DAP surface prep for selected MIC7300, MIC2778, MIC833, and MIC2779 device families available in 5L SOT23 package assembled at STAR assembly site.

Pre and Post Change Summary:

Method to Identify Change:Traceability code

Qualification Plan:Please open the attachments included with this PCN labeled as PCN_#_Qual_Plan.

Revision History:May 05, 2022: Issued initial notification.

The change described in this PCN does not alter Microchip's current regulatory compliance regarding the material content of the applicable products.

Attachments:

[PCN_LIAL-02XWMF227_Qual Plan.pdf](#)

[PCN_LIAL-02XWMF227_Pre and Post Change Summary.pdf](#)

Please contact your local [Microchip sales office](#) with questions or concerns regarding this notification.

Terms and Conditions:

If you wish to receive Microchip PCNs via email please register for our PCN email service at our [PCN home page](#) select register then fill in the required fields. You will find instructions about registering for Microchips PCN email service in the [PCN FAQ](#) section.

If you wish to change your PCN profile, including opt out, please go to the [PCN home page](#) select login and sign into your myMicrochip account. Select a profile option from the left navigation bar and make the applicable selections.



QUALIFICATION PLAN SUMMARY

PCN#: LIAL-02XWMF227

April 28, 2022

Qualification of G700 as a new molding compound material and NiPdAuAg with roughened as a new lead frame die attach paddle (DAP) surface prep for selected MIC7300, MIC2778, MIC833, and MIC2779 device families available in 5L SOT23 package assembled at STAR assembly site.

Purpose: Qualification of G700 as a new molding compound material and NiPdAuAg with roughened as a new lead frame die attach paddle (DAP) surface prep for selected MIC7300, MIC2778, MIC833, and MIC2779 device families available in 5L SOT23 package assembled at STAR assembly site.

<u>Misc.</u>	Assembly site	STAR
	BD Number	BD-000676 Rev01
	MP Code (MPC)	25808T6BXA03
	Part Number (CPN)	MIC2778-1YM5-TR
	MSL information	MSL-1@260C
	Assembly Shipping Media (T/R, Tube/Tray)	T/R
	Base Quantity Multiple (BQM)	3,000 units
	Reliability Site	MTAI
	CCB No.	5129
<u>Lead-Frame</u>	Paddle size	72x52 mils
	Material	C194
	DAP Surface Prep	NiPdAuAg with Roughened (Thickness: AuAg = 0.2-2.5 ulnch, Pd = 0.2-0.8 ulnch, Ni = 10-50 ulnch)
	Treatment	RT+UPG
	Process (Stamped/Etched)	STAMP
	Lead-lock Design (Locking Hole, Half Etched, Dimple, etc.)	No
	Part Number	MLEP00026MIC-T
	Lead Plating	PPF
	Strip Size	270x83 mm
Strip Density	960 units	
<u>Bond Wire</u>	Material	Au
<u>Die Attach</u>	Part Number	84-1LMISR4
	Conductive	Yes
<u>MC</u>	Part Number	G700
<u>PKG</u>	PKG Type	SOT23
	Pin/Ball Count	5L

Test Name	Conditions	Sample Size	Min. Qty of Spares per Lot (should be properly marked)	Qty of Lots	Total Units	Fail Accept Qty	Est. Dur. Days	REL Test Site	Special Instructions
Standard Pb-free Solderability	J-STD-002D ; Perform 8 hour steam aging for Matte tin finish and 1 hour steam aging for NiPdAu finish prior to testing. Standard Pb-free: Matte tin/ NiPdAu finish, SAC solder, wetting temp 245°C for both SMD & through hole packages.	22	5	1	27	> 95% lead coverage	5	MTAI	Standard Pb-free solderability is the requirement. SnPb solderability (backward solderability-SMD reflow soldering) is required for any plating related changes and highly recommended for other package BOM changes.
Backward Solderability	J-STD-002D ;Perform 8 hours steam aging for Matte tin finish and 1 hour steam aging for NiPdAu finish prior to testing. Backward: Matte tin/ NiPdAu finish, SnPb solder, wetting temp 215°C for SMD.	22	5	1	27	> 95% lead coverage	5	MTAI	
Wire Bond Pull - WBP	Mil. Std. 883-2011	5	0	1	5	0 fails after TC	5	STAR	30 bonds from a min. 5 devices.
Wire Bond Shear - WBS	CDF-AEC-Q100-001	5	0	1	5	0	5	STAR	30 bonds from a min. 5 devices.

Test Name	Conditions	Sample Size	Min. Qty of Spares per Lot (should be properly marked)	Qty of Lots	Total Units	Fail Accept Qty	Est. Dur. Days	REL Test Site	Special Instructions
Physical Dimensions	Measure per JESD22 B100 and B108	10	0	3	30	0	5	STAR	
External Visual	Mil. Std. 883-2009/2010	All devices prior to submission for qualification testing	0	3	ALL	0	5	STAR / MTAI	
Preconditioning - Required for surface mount devices	+150°C Bake for 24 hours, moisture loading requirements per MSL level + 3X reflow at peak reflow temperature per Jedec-STD-020E for package type; Electrical test pre and post stress at +25°C. MSL1@ 260C	231	15	3	738	0	15	MTAI	Spares should be properly identified. 77 parts from each lot to be used for HAST, uHAST, Temp Cycle test.
HAST	+130°C/85% RH for 96 hours Electrical test pre and post stress at +25°C	77	5	3	246	0	10	MTAI	Spares should be properly identified. Use the parts which have gone through Pre-conditioning.

Test Name	Conditions	Sample Size	Min. Qty of Spares per Lot (should be properly marked)	Qty of Lots	Total Units	Fail Accept Qty	Est. Dur. Days	REL Test Site	Special Instructions
UHAST	+130°C/85% RH for 96 hrs Electrical test pre and post stress at +25°C	77	5	3	246	0	10	MTAI	Spares should be properly identified. Use the parts which have gone through Pre-conditioning.
Temp Cycle	-65°C to +150°C for 500 cycles. Electrical test pre and post stress at +25°C. 3 gram force WBP, on 5 devices from 1 lot, test following Temp Cycle stress.	77	5	3	246	0	15	MTAI	Spares should be properly identified. Use the parts which have gone through Pre-conditioning.

CCB 5129
Pre and Post Change Summary
PCN #: LIAL-02XWMF227




A Leading Provider of Smart, Connected and Secure Embedded Control Solutions




SMART | CONNECTED | SECURE

Lead Frame Comparison

Pre Change



Post Change



LIAL-02XWMF227 - CCB 5129 Initial Notice: Qualification of G700 as a new molding compound material and NiPdAuAg with roughened as a new lead frame DAP surface prep for selected MIC7300, MIC2778, MIC833, and MIC2779 device families available in 5L SOT23 package assembled at STAR assembly site.

Affected Catalog Part Numbers (CPN)

MIC7300YM5-TR

MIC7300YM5-TX

MIC2778-1YM5-TR

MIC2778-2YM5-TR

MIC833YM5-TR

MIC2779H-1YM5-TR

MIC2779H-2YM5-TR

MIC2779L-1YM5-TR

MIC2779L-2YM5-TR