



PRODUCT CHANGE NOTIFICATION (PCN)

ISSUE DATE: 25/4/2022
MODIFICATION / REVISION DATE: 25/4/2022

DK-1611-001/BL MODULAR CABLE

CHANGE NOTIFICATION:

PCN 20220425_DK-1611-001/BL

DESCRIPTION OF CHANGES:

CHANGE OF DATA SHEET
CHANGE OF DATA SHEET
New Draw.-No. ASS_7510_CArev01

REASON FOR CHANGE:

CHANGE OF PRODUCT LOCATION
CHANGE OF PRODUCT LOCATION

KEY CHARACTERISTICS OF CHANGE:

Details see page 3

PRODUCTS AFFECTED:

DK-1611-001/BL

DATE OF CHANGE AND IMPLEMENTATION:



CHANGE: WEEK 18 / YEAR 2022
IMPLEMENTATION: 25/4/2022

RESPONSE:

NO RESPONSE TO THIS NOTIFICATION IS REQUIRED

PRODUCT CHANGE NOTIFICATION (PCN)

ISSUE DATE: 25/4/2022
MODIFICATION / REVISION DATE: 25/4/2022

DK-1611-001/BL	OLD VERSION	DK-1611-001/BL	NEW VERSION																				
Apprearence		Apprearence																					
BOM	Material: - Conductor: 24AWG 7*0.19±0.015mm - Conductor Insulation color coding: (1) White/Orange, (1) Orange, (1) White/Green, (1) Green, (1) Blue, (1) White/Blue, (1) White/Brown, (1) Brown - Cable jacket printing: DIGITUS Cat6 U-UTP PATCH CORD ISO/IEC 11801 & TIA/EIA 568-B.2-1 24AWGx4p CM(UL) C(UL) - Wiring T568B Color - P1 & P2 Contact plug: RJ45 8P8C 3μ pc UL 94V-2	BOM	<table><tr><td>①</td><td></td><td>Molding PVC</td><td>2</td><td>Molding PVC 65P</td></tr><tr><td>①</td><td></td><td>RJ45 CONN</td><td>2</td><td>RJ45 8P8C, contacts 3u" gold-plated Un-shielded PC UL94V-2</td></tr><tr><td>①</td><td></td><td>CABLE</td><td>1</td><td>CAT 5E U/UTP(24AWGx1PR)*4+PVC Jacket OD:5.6±0.3mm</td></tr><tr><td>NO.</td><td>NAME.</td><td>Q'TY</td><td colspan="2">SPECIFICATION</td></tr></table>	①		Molding PVC	2	Molding PVC 65P	①		RJ45 CONN	2	RJ45 8P8C, contacts 3u" gold-plated Un-shielded PC UL94V-2	①		CABLE	1	CAT 5E U/UTP(24AWGx1PR)*4+PVC Jacket OD:5.6±0.3mm	NO.	NAME.	Q'TY	SPECIFICATION	
①		Molding PVC	2	Molding PVC 65P																			
①		RJ45 CONN	2	RJ45 8P8C, contacts 3u" gold-plated Un-shielded PC UL94V-2																			
①		CABLE	1	CAT 5E U/UTP(24AWGx1PR)*4+PVC Jacket OD:5.6±0.3mm																			
NO.	NAME.	Q'TY	SPECIFICATION																				
FOR DETAIL, PLEASE TAKE ATTACHED NEW DRAWING: FOR REFERENCE																							

PCN REVISION HISTORY:

DATE OF REVISION: 25/4/2022

REVISION NUMBER: 00

page 3/

	1	2	3	4	5	6	7																																																											
A									A																																																									
B									B																																																									
C	Order code: DK-1611-XXX/XX color: BL (black), WH (white), B (blue), GR (green), G (grey) Length: see table ①								C																																																									
D	PIN OUT <table border="1"> <thead> <tr> <th>CN1</th> <th>WIRE COLOR</th> <th>CN2</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>ORANGE/WHITE</td> <td>1</td> </tr> <tr> <td>2</td> <td>ORANGE</td> <td>2</td> </tr> <tr> <td>3</td> <td>GREEN/WHITE</td> <td>3</td> </tr> <tr> <td>6</td> <td>GREEN</td> <td>6</td> </tr> <tr> <td>4</td> <td>BLUE</td> <td>4</td> </tr> <tr> <td>5</td> <td>BLUE/WHITE</td> <td>5</td> </tr> <tr> <td>7</td> <td>BROWN/WHITE</td> <td>7</td> </tr> <tr> <td>8</td> <td>BROWN</td> <td>8</td> </tr> </tbody> </table>								CN1	WIRE COLOR	CN2	1	ORANGE/WHITE	1	2	ORANGE	2	3	GREEN/WHITE	3	6	GREEN	6	4	BLUE	4	5	BLUE/WHITE	5	7	BROWN/WHITE	7	8	BROWN	8	D																														
CN1	WIRE COLOR	CN2																																																																
1	ORANGE/WHITE	1																																																																
2	ORANGE	2																																																																
3	GREEN/WHITE	3																																																																
6	GREEN	6																																																																
4	BLUE	4																																																																
5	BLUE/WHITE	5																																																																
7	BROWN/WHITE	7																																																																
8	BROWN	8																																																																
E	<table border="1"> <thead> <tr> <th>Length</th> <th>Feet</th> <th>mm</th> <th>tolerance (mm)</th> </tr> </thead> <tbody> <tr> <td>001</td> <td>1</td> <td>305</td> <td>+30.5/-15.3</td> </tr> <tr> <td>003</td> <td>3</td> <td>914</td> <td>+45.8/-36.6</td> </tr> <tr> <td>005</td> <td>5</td> <td>1524</td> <td>±45.8</td> </tr> <tr> <td>007</td> <td>7</td> <td>2134</td> <td>±64.1</td> </tr> <tr> <td>010</td> <td>10</td> <td>3048</td> <td>±91.5</td> </tr> <tr> <td>015</td> <td>15</td> <td>4572</td> <td>±137.3</td> </tr> <tr> <td>020</td> <td>20</td> <td>6096</td> <td>±183</td> </tr> <tr> <td>025</td> <td>25</td> <td>7620</td> <td>±228.8</td> </tr> <tr> <td>050</td> <td>50</td> <td>15240</td> <td>±457.5</td> </tr> <tr> <td>100</td> <td>100</td> <td>30480</td> <td>±915</td> </tr> </tbody> </table>								Length	Feet	mm	tolerance (mm)	001	1	305	+30.5/-15.3	003	3	914	+45.8/-36.6	005	5	1524	±45.8	007	7	2134	±64.1	010	10	3048	±91.5	015	15	4572	±137.3	020	20	6096	±183	025	25	7620	±228.8	050	50	15240	±457.5	100	100	30480	±915	E													
Length	Feet	mm	tolerance (mm)																																																															
001	1	305	+30.5/-15.3																																																															
003	3	914	+45.8/-36.6																																																															
005	5	1524	±45.8																																																															
007	7	2134	±64.1																																																															
010	10	3048	±91.5																																																															
015	15	4572	±137.3																																																															
020	20	6096	±183																																																															
025	25	7620	±228.8																																																															
050	50	15240	±457.5																																																															
100	100	30480	±915																																																															
F	Electrical Open/short/intermittence: 100% Dielectric strength: 2.5KV DC-2seconds. The operating temperature: -20°C~+60°C								F																																																									
G	RoHS compliant Unit: mm								G																																																									
H	<table border="1"> <thead> <tr> <th>Scale</th> <th>FREE</th> <th></th> <th></th> <th></th> <th></th> <th>Date</th> <th>Name</th> <th>Customer-No.</th> </tr> </thead> <tbody> <tr> <td>TOLERANCE</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>Drawn</td> <td>15.12.2015</td> <td>Joanna</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td>Approved</td> <td>12.04.2022</td> <td>Luca</td> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>DIM</td> <td>TOL</td> <td>①</td> <td>Change the plant</td> <td>12.04.2022</td> <td>Luca</td> <td colspan="3" rowspan="3"> ASSMANN WSW components </td> </tr> <tr> <td></td> <td></td> <td>②</td> <td>Drawn</td> <td>15.12.2015</td> <td>Joanna</td> </tr> <tr> <td>Angle</td> <td>TOL</td> <td>Id.</td> <td>Modification</td> <td>Date</td> <td>Name</td> </tr> </tbody> </table>								Scale	FREE					Date	Name	Customer-No.	TOLERANCE						Drawn	15.12.2015	Joanna							Approved	12.04.2022	Luca										DIM	TOL	①	Change the plant	12.04.2022	Luca	ASSMANN WSW components					②	Drawn	15.12.2015	Joanna	Angle	TOL	Id.	Modification	Date	Name	H
Scale	FREE					Date	Name	Customer-No.																																																										
TOLERANCE						Drawn	15.12.2015	Joanna																																																										
						Approved	12.04.2022	Luca																																																										
DIM	TOL	①	Change the plant	12.04.2022	Luca	ASSMANN WSW components																																																												
		②	Drawn	15.12.2015	Joanna																																																													
Angle	TOL	Id.	Modification	Date	Name																																																													
	1	2	3	4	5	6	7																																																											