



Product Change Notification / CENO-11FRYW234

Date:

27-Sep-2022

Product Category:

16-Bit - Microcontrollers and Digital Signal Controllers

PCN Type:

Manufacturing Change

Notification Subject:

CCB 5131 Initial Notice: Qualification of C194 as an additional lead frame material for selected DSPIC33EPxxxxxx, PIC24EP12xxxxxx, PIC24EP25xxxxxx, PIC24EP32xxxxx and PIC24EP64xxxxx device families available in 48L UQFN (6x6x0.5mm) package.

Affected CPNs:

[CENO-11FRYW234_Affected_CPN_09272022.pdf](#)

[CENO-11FRYW234_Affected_CPN_09272022.csv](#)

Notification Text:

PCN Status:Initial Notification

PCN Type:Manufacturing Change

Microchip Parts Affected:Please open one of the files found in the Affected CPNs section.

Note: For your convenience Microchip includes identical files in two formats (.pdf and .xls)

Description of Change:Qualification of C194 as an additional lead frame material for selected DSPIC33EPxxxxxx, PIC24EP12xxxxxx, PIC24EP25xxxxxx, PIC24EP32xxxxx and PIC24EP64xxxxx device families available in 48L UQFN (6x6x0.5mm) package.

Pre and Post Change Summary:

Final PCN Issue Date										x		
-------------------------	--	--	--	--	--	--	--	--	--	---	--	--

Method to Identify Change:Traceability code

Qualification Plan:Please open the attachments included with this PCN labeled as PCN_#_Qual_Plan.

Revision History:September 27, 2022: Issued initial notification.

The change described in this PCN does not alter Microchip’s current regulatory compliance regarding the material content of the applicable products.

Attachments:

[PCN_CENO-11FRYW234_Qualification Plan.pdf](#)

[PCN_CENO-11FRYW234_Pre and Post Change_Summary.pdf](#)

Please contact your local [Microchip sales office](#) with questions or concerns regarding this notification.

Terms and Conditions:

If you wish to receive Microchip PCNs via email please register for our PCN email service at our [PCN home page](#) select register then fill in the required fields. You will find instructions about registering for Microchips PCN email service in the [PCN FAQ](#) section.

If you wish to change your PCN profile, including opt out, please go to the [PCN home page](#) select login and sign into your myMicrochip account. Select a profile option from the left navigation bar and make the applicable selections.



MICROCHIP

QUALIFICATION PLAN SUMMARY

PCN #: CENO-11FRYW234

**Date:
September 15, 2022**

**Qualification of C194 as an additional lead frame material
for selected DSPIC33EPxxxxxxx, PIC24EP12xxxxxx,
PIC24EP25xxxxxx, PIC24EP32xxxxx and
PIC24EP64xxxxx device families available in 48L UQFN
(6x6x0.5mm) package.**

Purpose: Qualification of C194 as an additional lead frame material for selected DSPIC33EPxxxxxxx, PIC24EP12xxxxxx, PIC24EP25xxxxxx, PIC24EP32xxxxx and PIC24EP64xxxxxx device families available in 48L UQFN (6x6x0.5mm) package.

CCB No. 5131

BOMs Information:

<u>Misc.</u>	Assembly site	NSEB
	BD Number	BD-000937 rev01
	MP Code (MPC)	TLAE1JR7XNFA
	Part Number (CPN)	PIC24EP256GP204T-H/MV
	MSL information	MSL-1@260C
	Assembly Shipping Media (T/R, Tube/Tray)	Tube
	Base Quantity Multiple (BQM)	61
	Reliability Site	MTAI
<u>Lead-Frame</u>	Paddle size	193x193 mil
	Material	C194
	DAP Surface Prep	Ag on lead only
	Treatment	No
	Process (Stamped/Etched)	Etched
	Lead-lock Design (Locking Hole, Half Etched, Dimple, etc.)	Dimple
	Part Number	FU0295
	Lead frame Thickness	5 mil
	Lead Plating	Matte Tin
	Strip Size	70x250 mm
	Strip Density	315
<u>Bond Wire</u>	Material	Au
<u>Die Attach</u>	Part Number	8600
	Conductive	Yes
<u>MC</u>	Part Number	G700LTD
<u>PKG</u>	PKG Type	UQFN
	Pin/Ball Count	48
	PKG width/size	6x6x0.5 mm

Test Name	Conditions	Reliability Stress Read Point Grade 0: - 40°C to +150°C (MCHP H Temp)	Pre & Post Reliability Stress Test Temperature Grade 0: - 40°C to +150°C (MCHP H Temp)	Sample Size	Min. Qty of Spares per Lot (should be properly marked)	Qty of Lots	Total Units	Fail Accept Qty	Est. Dur. Days	REL Test Site	Special Instructions
Standard Pb-free Solderability	J-STD-002D ; Perform 8 hours of steam aging for Matte tin finish and 1 hour steam aging for NiPdAu finish prior to testing. Standard Pb-free: Matte tin/ NiPdAu finish, SAC solder, wetting temp 245°C for both SMD & through hole packages.			22	5	1	27	>95% lead coverage	5	MTAI	Standard Pb-free solderability is the requirement. SnPb solderability (backward solderability- SMD reflow soldering) is required for any plating related changes and highly recommended for other package BOM changes.
Backward Solderability	J-STD-002D ; Perform 8 hour steam aging for Matte tin finish and 1 hr steam aging for NiPdAu finish prior to testing. Backward: Matte tin/ NiPdAu finish, SnPb solder, wetting temp 215°C for SMD.			22	5	1	27	>95% lead coverage	5	MTAI	
Wire Bond Pull - WBP	Mil. Std. 883-2011			5	0	1	5	0 fails after TC	5	NSEB	30 bonds from a min. 5 devices.
Wire Bond Shear - WBS	CDF-AEC-Q100-001			5	0	1	5		5	NSEB	30 bonds from a min. 5 devices.
Physical Dimensions	Measure per JESD22 B100 and B108			10	0	3	30		5	NSEB	
External Visual	Mil. Std. 883-2009/2010			All devices prior to submission for qualification testing	0	3	ALL	0	5	NSEB / MTAI	

Test Name	Conditions	Reliability Stress Read Point Grade 0: -40°C to +150°C (MCHP H Temp)	Pre & Post Reliability Stress Test Temperature Grade 0: -40°C to +150°C (MCHP H Temp)	Sample Size	Min. Qty of Spares per Lot (should be properly marked)	Qty of Lots	Total Units	Fail Accept Qty	Est. Dur. Days	REL Test Site	Special Instructions
HTSL (High Temp Storage Life)	JESD22-A103 +125°C, +150°C or +175°C	Grade 0: 1000 hrs (+175°C)	Grade 0: +25°C, +85°C, +125°C, +150°C	45	5	1	50	0	21 - 83	MTAI	Spares should be properly identified.
Preconditioning - Required for surface mount devices	J-STD-020JESD22-A113+150°C Bake for 24 hours, moisture loading requirements per MSL level + 3X reflow at peak reflow temperature per Jedec-STD-020E for package type. MSL-1@260C		Grade 0: +25°C	231+	15+	3	738+	0	15	MTAI	Spares should be properly identified. 77 parts from each lot to be used for HAST, uHAST, Temp Cycle test.
HAST	JESD22-A101 or A110 +130°C/85% RH for 96 hrs	Grade 0: 96 hrs (+130°C/85% RH)	Grade 0: +25°C, +85°C, +125°C, +150°C	77	5	3	246	0	10 - 14	MTAI	Spares should be properly identified. Use the parts which have gone through Pre-conditioning.
UHAST	JESD22-A102, A118, or A101 +130°C/85% RH for 96 hrs	Grade 0: 96 hrs (+130°C/85% RH)	Grade 0: +25°C	77	5	3	246	0	10	MTAI	Spares should be properly identified. Use the parts which have gone through Pre-conditioning.
Temp Cycle	JESD22-A104 and Appendix 3 -55°C to +150°C	Grade 0: 2000 cycles (-55°C to +150°C)	Grade 0: +85°C, +125°C, +150°C	77	5	3	246	0	15 - 60	MTAI	Spares should be properly identified. Use the parts which have gone through Pre-conditioning.


CCB 5131

Pre and Post Change Summary

PCN #: CENO-11FRYW234




A Leading Provider of Smart, Connected and Secure Embedded Control Solutions



SMART | CONNECTED | SECURE

LEAD FRAME COMPARISON

Pre Change




Note: Not to scale

Lead frame Material

EFTEC64T

Post Change



Note: Not to scale

Lead frame Material

C194

CENO-11FRYW234 - CCB 5131 In PIC24EP12 PIC24EP25 PIC24EP32xxxxx and PIC24EP64xxxxx device families avai

Affected Catalog Part Numbers(CPN)

PIC24EP256GP204-I/MV
PIC24EP256MC204-I/MV
PIC24EP256GP204-I/MVA3
DSPIC33EP256GP504T-H/MV
DSPIC33EP256MC204T-H/MV
DSPIC33EP256MC504T-H/MV
PIC24EP256GP204T-H/MV
PIC24EP256MC204T-H/MV
DSPIC33EP256GP504-H/MV
DSPIC33EP256MC204-H/MV
DSPIC33EP256MC504-H/MV
PIC24EP256GP204-H/MV
PIC24EP256MC204-H/MV
PIC24EP256GP204T-I/MV030
DSPIC33EP256GP504T-I/MV
DSPIC33EP256MC204T-I/MV
DSPIC33EP256MC504T-I/MV
PIC24EP256GP204T-I/MV
PIC24EP256MC204T-I/MV
DSPIC33EP256GP504T-E/MV
DSPIC33EP256MC204T-E/MV
DSPIC33EP256MC504T-E/MV
PIC24EP256GP204T-E/MV
PIC24EP256MC204T-E/MV
DSPIC33EP32GP504-E/MV
DSPIC33EP32MC204-E/MV
DSPIC33EP32MC504-E/MV
PIC24EP32GP204-E/MV
PIC24EP32MC204-E/MV
DSPIC33EP32GP504-I/MV
DSPIC33EP32MC204-I/MV
DSPIC33EP32MC504-I/MV
PIC24EP32GP204-I/MV
PIC24EP32MC204-I/MV
DSPIC33EP32GP504T-H/MV
DSPIC33EP32MC204T-H/MV
DSPIC33EP32MC504T-H/MV
PIC24EP32GP204T-H/MV
PIC24EP32MC204T-H/MV
DSPIC33EP32GP504-H/MV
DSPIC33EP32MC204-H/MV
DSPIC33EP32MC504-H/MV

PIC24EP32GP204-H/MV
PIC24EP32MC204-H/MV
DSPIC33EP32GP504T-I/MV
DSPIC33EP32MC204T-I/MV
DSPIC33EP32MC504T-I/MV
PIC24EP32GP204T-I/MV
PIC24EP32MC204T-I/MV
DSPIC33EP32GP504T-E/MV
DSPIC33EP32MC204T-E/MV
DSPIC33EP32MC504T-E/MV
PIC24EP32GP204T-E/MV
PIC24EP32MC204T-E/MV
DSPIC33EP64GP504-E/MV
DSPIC33EP64MC204-E/MV
DSPIC33EP64MC504-E/MV
PIC24EP64GP204-E/MV
PIC24EP64MC204-E/MV
DSPIC33EP64GP504-I/MV
DSPIC33EP64MC204-I/MV
DSPIC33EP64MC504-I/MV
PIC24EP64GP204-I/MV
PIC24EP64MC204-I/MV
DSPIC33EP64GP504T-H/MV
DSPIC33EP64MC204T-H/MV
DSPIC33EP64MC504T-H/MV
PIC24EP64GP204T-H/MV
PIC24EP64MC204T-H/MV
DSPIC33EP64GP504-H/MV
DSPIC33EP64MC204-H/MV
DSPIC33EP64MC504-H/MV
PIC24EP64GP204-H/MV
PIC24EP64MC204-H/MV
DSPIC33EP64GP504T-I/MV
DSPIC33EP64MC204T-I/MV
DSPIC33EP64MC504T-I/MV
PIC24EP64MC204T-I/MV
DSPIC33EP64GP504T-E/MV
DSPIC33EP64MC204T-E/MV
DSPIC33EP64MC504T-E/MV
PIC24EP64GP204T-E/MV
PIC24EP64MC204T-E/MV
DSPIC33EP128GP504-E/MV
DSPIC33EP128MC204-E/MV
DSPIC33EP128MC504-E/MV
PIC24EP128GP204-E/MV
PIC24EP128MC204-E/MV
DSPIC33EP128GP504-I/MV

DSPIC33EP128MC204-I/MV
DSPIC33EP128MC504-I/MV
PIC24EP128GP204-I/MV
PIC24EP128MC204-I/MV
DSPIC33EP128GP504T-H/MV
DSPIC33EP128MC204T-H/MV
DSPIC33EP128MC504T-H/MV
PIC24EP128GP204T-H/MV
PIC24EP128MC204T-H/MV
DSPIC33EP128GP504-H/MV
DSPIC33EP128MC204-H/MV
DSPIC33EP128MC504-H/MV
PIC24EP128GP204-H/MV
PIC24EP128MC204-H/MV
DSPIC33EP128GP504T-I/MV
DSPIC33EP128MC204T-I/MV
DSPIC33EP128MC504T-I/MV
PIC24EP128GP204T-I/MV
PIC24EP128MC204T-I/MV
DSPIC33EP128GP504T-E/MV
DSPIC33EP128MC204T-E/MV
DSPIC33EP128MC504T-E/MV
PIC24EP128GP204T-E/MV
PIC24EP128MC204T-E/MV
DSPIC33EP256GP504-E/MV
DSPIC33EP256MC204-E/MV
DSPIC33EP256MC504-E/MV
PIC24EP256GP204-E/MV
PIC24EP256MC204-E/MV
DSPIC33EP256GP504-I/MV
DSPIC33EP256MC204-I/MV
DSPIC33EP256MC504-I/MV