



PRODUCT CHANGE NOTIFICATION (PCN)

ISSUE DATE: 22/8/2022
MODIFICATION / REVISION DATE: 22/8/2022

A-MCSP60100/B MODULAR CABLE

CHANGE NOTIFICATION:

PCN 20220822_A-MCSP60100/B

DESCRIPTION OF CHANGES:

CHANGE OF DATA SHEET
CHANGE OF DATA SHEET
New Draw.-No. ASS_7542_CArev06

REASON FOR CHANGE:

CHANGE OF MATERIAL PARAMETERS OR PROPERTIES
CHANGE OF MATERIAL PARAMETERS OR PROPERTIES

KEY CHARACTERISTICS OF CHANGE:

Details see page 3

PRODUCTS AFFECTED:

A-MCSP60100/B

DATE OF CHANGE AND IMPLEMENTATION:

CHANGE: WEEK 35 / YEAR 2022
IMPLEMENTATION: 22/8/2022

RESPONSE:

NO RESPONSE TO THIS NOTIFICATION IS REQUIRED

PRODUCT CHANGE NOTIFICATION (PCN)

ISSUE DATE: 22/8/2022
MODIFICATION / REVISION DATE: 22/8/2022

A-MCSP60100/B	OLD VERSION	A-MCSP60100/B	NEW VERSION																																																																																										
PIN OUT		PIN OUT																																																																																											
PIN OUT <table><thead><tr><th>CN1</th><th>④ WIRE COLOR</th><th>CN2</th></tr></thead><tbody><tr><td>1</td><td>ORANGE/WHITE</td><td>1</td></tr><tr><td>2</td><td>ORANGE</td><td>2</td></tr><tr><td>3</td><td>GREEN/WHITE</td><td>3</td></tr><tr><td>6</td><td>GREEN</td><td>6</td></tr><tr><td>4</td><td>BLUE</td><td>4</td></tr><tr><td>5</td><td>BLUE/WHITE</td><td>5</td></tr><tr><td>7</td><td>BROWN/WHITE</td><td>7</td></tr><tr><td>8</td><td>BROWN</td><td>8</td></tr><tr><td>SHELL</td><td>BRAID</td><td>SHELL</td></tr></tbody></table>		CN1	④ WIRE COLOR	CN2	1	ORANGE/WHITE	1	2	ORANGE	2	3	GREEN/WHITE	3	6	GREEN	6	4	BLUE	4	5	BLUE/WHITE	5	7	BROWN/WHITE	7	8	BROWN	8	SHELL	BRAID	SHELL	PIN OUT <table><thead><tr><th>CN1</th><th>WIRE COLOR</th><th>CN2</th></tr></thead><tbody><tr><td>1</td><td>WHITE</td><td>1</td></tr><tr><td>2</td><td>ORANGE</td><td>2</td></tr><tr><td>3</td><td>WHITE</td><td>3</td></tr><tr><td>6</td><td>GREEN</td><td>6</td></tr><tr><td>4</td><td>BLUE</td><td>4</td></tr><tr><td>5</td><td>WHITE</td><td>5</td></tr><tr><td>7</td><td>WHITE</td><td>7</td></tr><tr><td>8</td><td>BROWN</td><td>8</td></tr><tr><td>SHELL</td><td>BRAID</td><td>SHELL</td></tr></tbody></table> PIN OUT <table><thead><tr><th>CN1</th><th>WIRE COLOR</th><th>CN2</th></tr></thead><tbody><tr><td>1</td><td>ORANGE/WHITE</td><td>1</td></tr><tr><td>2</td><td>ORANGE</td><td>2</td></tr><tr><td>3</td><td>GREEN/WHITE</td><td>3</td></tr><tr><td>6</td><td>GREEN</td><td>6</td></tr><tr><td>4</td><td>BLUE</td><td>4</td></tr><tr><td>5</td><td>BLUE/WHITE</td><td>5</td></tr><tr><td>7</td><td>BROWN/WHITE</td><td>7</td></tr><tr><td>8</td><td>BROWN</td><td>8</td></tr><tr><td>SHELL</td><td>BRAID</td><td>SHELL</td></tr></tbody></table>		CN1	WIRE COLOR	CN2	1	WHITE	1	2	ORANGE	2	3	WHITE	3	6	GREEN	6	4	BLUE	4	5	WHITE	5	7	WHITE	7	8	BROWN	8	SHELL	BRAID	SHELL	CN1	WIRE COLOR	CN2	1	ORANGE/WHITE	1	2	ORANGE	2	3	GREEN/WHITE	3	6	GREEN	6	4	BLUE	4	5	BLUE/WHITE	5	7	BROWN/WHITE	7	8	BROWN	8	SHELL	BRAID	SHELL
CN1	④ WIRE COLOR	CN2																																																																																											
1	ORANGE/WHITE	1																																																																																											
2	ORANGE	2																																																																																											
3	GREEN/WHITE	3																																																																																											
6	GREEN	6																																																																																											
4	BLUE	4																																																																																											
5	BLUE/WHITE	5																																																																																											
7	BROWN/WHITE	7																																																																																											
8	BROWN	8																																																																																											
SHELL	BRAID	SHELL																																																																																											
CN1	WIRE COLOR	CN2																																																																																											
1	WHITE	1																																																																																											
2	ORANGE	2																																																																																											
3	WHITE	3																																																																																											
6	GREEN	6																																																																																											
4	BLUE	4																																																																																											
5	WHITE	5																																																																																											
7	WHITE	7																																																																																											
8	BROWN	8																																																																																											
SHELL	BRAID	SHELL																																																																																											
CN1	WIRE COLOR	CN2																																																																																											
1	ORANGE/WHITE	1																																																																																											
2	ORANGE	2																																																																																											
3	GREEN/WHITE	3																																																																																											
6	GREEN	6																																																																																											
4	BLUE	4																																																																																											
5	BLUE/WHITE	5																																																																																											
7	BROWN/WHITE	7																																																																																											
8	BROWN	8																																																																																											
SHELL	BRAID	SHELL																																																																																											
		⑥ *The PIN OUT is applied to cable length ≥10M																																																																																											
		*The PIN OUT is applied to cable length <10M																																																																																											
FOR DETAIL, PLEASE TAKE ATTACHED NEW DRAWING: FOR REFERENCE																																																																																													

	1	2	3	4	5	6	7																																																																																																		
A							A																																																																																																		
B							B																																																																																																		
C	① Order code: A-MCSP60XXX : color Grey order lengths in meter: 0.5, 1, 2, 3, 5, 7, 10, 15, 20, 30						C																																																																																																		
D	① Order code: A-MCSP60XXX/X order lengths in meter: 0.5, 1, 2, 3, 5, 7, 10, 15, 20, 30 order color: (R)Red, (Y)Yellow, (G)Green, (B)Blue						D																																																																																																		
E	② Tolerance <table border="1"> <thead> <tr> <th>Length Code</th><th>Length (meter)</th><th>Max-M</th><th>Min-M</th></tr> </thead> <tbody> <tr><td>005</td><td>0.5</td><td>+0.03</td><td>-0.025</td></tr> <tr><td>010</td><td>1</td><td>+0.04</td><td>-0.035</td></tr> <tr><td>020</td><td>2</td><td>+0.06</td><td>-0.06</td></tr> <tr><td>030</td><td>3</td><td>+0.09</td><td>-0.09</td></tr> <tr><td>050</td><td>5</td><td>+0.15</td><td>-0.15</td></tr> <tr><td>070</td><td>7</td><td>+0.21</td><td>-0.21</td></tr> <tr><td>100</td><td>10</td><td>+0.3</td><td>-0.3</td></tr> <tr><td>150</td><td>15</td><td>+0.45</td><td>-0.45</td></tr> <tr><td>200</td><td>20</td><td>+0.6</td><td>-0.6</td></tr> <tr><td>300</td><td>30</td><td>+0.9</td><td>-0.9</td></tr> </tbody> </table>						Length Code	Length (meter)	Max-M	Min-M	005	0.5	+0.03	-0.025	010	1	+0.04	-0.035	020	2	+0.06	-0.06	030	3	+0.09	-0.09	050	5	+0.15	-0.15	070	7	+0.21	-0.21	100	10	+0.3	-0.3	150	15	+0.45	-0.45	200	20	+0.6	-0.6	300	30	+0.9	-0.9	E																																																						
Length Code	Length (meter)	Max-M	Min-M																																																																																																						
005	0.5	+0.03	-0.025																																																																																																						
010	1	+0.04	-0.035																																																																																																						
020	2	+0.06	-0.06																																																																																																						
030	3	+0.09	-0.09																																																																																																						
050	5	+0.15	-0.15																																																																																																						
070	7	+0.21	-0.21																																																																																																						
100	10	+0.3	-0.3																																																																																																						
150	15	+0.45	-0.45																																																																																																						
200	20	+0.6	-0.6																																																																																																						
300	30	+0.9	-0.9																																																																																																						
F	Electrical test: Open/Short/intermittence: 100%						F																																																																																																		
G	<table border="1"> <thead> <tr> <th>NO</th><th>NAME</th><th>QTY</th><th>SPECIFICATION</th></tr> </thead> <tbody> <tr> <td>④</td><td>AL-Foil</td><td>2</td><td>Double-sided conductive aluminum foil</td></tr> <tr> <td>④</td><td>Molding PVC</td><td>2</td><td>Molding PVC 65P</td></tr> <tr> <td>④</td><td>RJ45 CONN</td><td>2</td><td>RJ45 8P8C, Two Fork gold plated contacts 3u" with metal housing</td></tr> <tr> <td>④③</td><td>CABLE</td><td>1</td><td>CAT6 S/FTP(26AWG*1PR-A)*4+B(AM)+PVC OD:5.8±0.2mm</td></tr> </tbody> </table>						NO	NAME	QTY	SPECIFICATION	④	AL-Foil	2	Double-sided conductive aluminum foil	④	Molding PVC	2	Molding PVC 65P	④	RJ45 CONN	2	RJ45 8P8C, Two Fork gold plated contacts 3u" with metal housing	④③	CABLE	1	CAT6 S/FTP(26AWG*1PR-A)*4+B(AM)+PVC OD:5.8±0.2mm	G																																																																														
NO	NAME	QTY	SPECIFICATION																																																																																																						
④	AL-Foil	2	Double-sided conductive aluminum foil																																																																																																						
④	Molding PVC	2	Molding PVC 65P																																																																																																						
④	RJ45 CONN	2	RJ45 8P8C, Two Fork gold plated contacts 3u" with metal housing																																																																																																						
④③	CABLE	1	CAT6 S/FTP(26AWG*1PR-A)*4+B(AM)+PVC OD:5.8±0.2mm																																																																																																						
H	⑥ The PIN OUT is applied to cable length ≥10M The PIN OUT is applied to cable length <10M <table border="1"> <thead> <tr> <th>CN1</th><th>PIN OUT</th><th>WIRE COLOR</th><th>CN2</th></tr> </thead> <tbody> <tr><td>1</td><td>↔</td><td>WHITE</td><td>↔</td><td>1</td></tr> <tr><td>2</td><td>↔</td><td>ORANGE</td><td>↔</td><td>2</td></tr> <tr><td>3</td><td>↔</td><td>WHITE</td><td>↔</td><td>3</td></tr> <tr><td>4</td><td>↔</td><td>BLUE</td><td>↔</td><td>4</td></tr> <tr><td>5</td><td>↔</td><td>WHITE</td><td>↔</td><td>5</td></tr> <tr><td>6</td><td>↔</td><td>BLUE</td><td>↔</td><td>6</td></tr> <tr><td>7</td><td>↔</td><td>WHITE</td><td>↔</td><td>7</td></tr> <tr><td>8</td><td>↔</td><td>BROWN</td><td>↔</td><td>8</td></tr> <tr><td>SHELL</td><td></td><td>BRAID</td><td></td><td>SHELL</td></tr> </tbody> </table> <table border="1"> <thead> <tr> <th>CN1</th><th>PIN OUT</th><th>WIRE COLOR</th><th>CN2</th></tr> </thead> <tbody> <tr><td>1</td><td>↔</td><td>ORANGE/WHITE</td><td>↔</td><td>1</td></tr> <tr><td>2</td><td>↔</td><td>ORANGE</td><td>↔</td><td>2</td></tr> <tr><td>3</td><td>↔</td><td>GREEN/WHITE</td><td>↔</td><td>3</td></tr> <tr><td>4</td><td>↔</td><td>GREEN</td><td>↔</td><td>4</td></tr> <tr><td>5</td><td>↔</td><td>BLUE/WHITE</td><td>↔</td><td>5</td></tr> <tr><td>6</td><td>↔</td><td>BLUE</td><td>↔</td><td>6</td></tr> <tr><td>7</td><td>↔</td><td>BROWN/WHITE</td><td>↔</td><td>7</td></tr> <tr><td>8</td><td>↔</td><td>BROWN</td><td>↔</td><td>8</td></tr> <tr><td>SHELL</td><td></td><td>BRAID</td><td></td><td>SHELL</td></tr> </tbody> </table>						CN1	PIN OUT	WIRE COLOR	CN2	1	↔	WHITE	↔	1	2	↔	ORANGE	↔	2	3	↔	WHITE	↔	3	4	↔	BLUE	↔	4	5	↔	WHITE	↔	5	6	↔	BLUE	↔	6	7	↔	WHITE	↔	7	8	↔	BROWN	↔	8	SHELL		BRAID		SHELL	CN1	PIN OUT	WIRE COLOR	CN2	1	↔	ORANGE/WHITE	↔	1	2	↔	ORANGE	↔	2	3	↔	GREEN/WHITE	↔	3	4	↔	GREEN	↔	4	5	↔	BLUE/WHITE	↔	5	6	↔	BLUE	↔	6	7	↔	BROWN/WHITE	↔	7	8	↔	BROWN	↔	8	SHELL		BRAID		SHELL	H
CN1	PIN OUT	WIRE COLOR	CN2																																																																																																						
1	↔	WHITE	↔	1																																																																																																					
2	↔	ORANGE	↔	2																																																																																																					
3	↔	WHITE	↔	3																																																																																																					
4	↔	BLUE	↔	4																																																																																																					
5	↔	WHITE	↔	5																																																																																																					
6	↔	BLUE	↔	6																																																																																																					
7	↔	WHITE	↔	7																																																																																																					
8	↔	BROWN	↔	8																																																																																																					
SHELL		BRAID		SHELL																																																																																																					
CN1	PIN OUT	WIRE COLOR	CN2																																																																																																						
1	↔	ORANGE/WHITE	↔	1																																																																																																					
2	↔	ORANGE	↔	2																																																																																																					
3	↔	GREEN/WHITE	↔	3																																																																																																					
4	↔	GREEN	↔	4																																																																																																					
5	↔	BLUE/WHITE	↔	5																																																																																																					
6	↔	BLUE	↔	6																																																																																																					
7	↔	BROWN/WHITE	↔	7																																																																																																					
8	↔	BROWN	↔	8																																																																																																					
SHELL		BRAID		SHELL																																																																																																					
RoHS compliant Unit: mm																																																																																																									
<table border="1"> <thead> <tr> <th>Scale</th><th>FREE</th><th>⑥</th><th>Add a PIN OUT for cable length ≥10M</th><th>19.08.2022</th><th>Luca</th><th></th><th>Date</th><th>Name</th><th>Customer-No.</th></tr> </thead> <tbody> <tr> <td>TOLERANCE</td><td></td><td>⑤</td><td>Add length code</td><td>29.06.2022</td><td>Luca</td><td>Drawn</td><td>01.02.2016</td><td>Joanna</td><td></td></tr> <tr> <td></td><td></td><td>④</td><td>Change the plant</td><td>12.04.2022</td><td>Luca</td><td>Approved</td><td>19.06.2022</td><td>Luca</td><td></td></tr> <tr> <td></td><td></td><td>③</td><td>Update the cable description</td><td>01.11.2018</td><td>Segal</td><td></td><td></td><td></td><td></td></tr> <tr> <td>DIM</td><td>TOL</td><td>②</td><td>Clarify the tolerance</td><td>23.08.2018</td><td>Segal</td><td></td><td></td><td></td><td></td></tr> <tr> <td></td><td></td><td>①</td><td>Add Grey color order code</td><td>11.08.2016</td><td>Ray</td><td></td><td></td><td></td><td></td></tr> <tr> <td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td></td><td></td><td></td><td></td></tr> </tbody> </table>							Scale	FREE	⑥	Add a PIN OUT for cable length ≥10M	19.08.2022	Luca		Date	Name	Customer-No.	TOLERANCE		⑤	Add length code	29.06.2022	Luca	Drawn	01.02.2016	Joanna				④	Change the plant	12.04.2022	Luca	Approved	19.06.2022	Luca				③	Update the cable description	01.11.2018	Segal					DIM	TOL	②	Clarify the tolerance	23.08.2018	Segal							①	Add Grey color order code	11.08.2016	Ray					Angle	TOL	Id.	Modification	Date	Name																																	
Scale	FREE	⑥	Add a PIN OUT for cable length ≥10M	19.08.2022	Luca		Date	Name	Customer-No.																																																																																																
TOLERANCE		⑤	Add length code	29.06.2022	Luca	Drawn	01.02.2016	Joanna																																																																																																	
		④	Change the plant	12.04.2022	Luca	Approved	19.06.2022	Luca																																																																																																	
		③	Update the cable description	01.11.2018	Segal																																																																																																				
DIM	TOL	②	Clarify the tolerance	23.08.2018	Segal																																																																																																				
		①	Add Grey color order code	11.08.2016	Ray																																																																																																				
Angle	TOL	Id.	Modification	Date	Name																																																																																																				
1 2 3 4 5 6 7																																																																																																									