



Product Change Notification / CENO-11FRYW234

Date:

31-May-2023

Product Category:

16-Bit - Microcontrollers and Digital Signal Controllers

PCN Type:

Manufacturing Change

Notification Subject:

CCB 5131 Final Notice: Qualification of C194 as an additional lead frame material for selected DSPIC33EPxxxxx, PIC24EP12xxxx, PIC24EP25xxxx, PIC24EP32xxx and PIC24EP64xxx device families available in 48L UQFN (6x6x0.5mm) package.

Affected CPNs:

[CENO-11FRYW234_Affected_CPN_05312023.pdf](#)

[CENO-11FRYW234_Affected_CPN_05312023.csv](#)

Notification Text:

PCN Status:Final Notification

PCN Type:Manufacturing Change

Microchip Parts Affected:Please open one of the files found in the Affected CPNs section.

Note: For your convenience Microchip includes identical files in two formats (.pdf and .xls)

Description of Change:Qualification of C194 as an additional lead frame material for selected DSPIC33EPxxxxx, PIC24EP12xxxx, PIC24EP25xxxx, PIC24EP32xxx and PIC24EP64xxx device families available in 48L UQFN (6x6x0.5mm) package.

Pre and Post Change Summary:

	Pre Change	Post Change
--	------------	-------------

Method to Identify Change:Traceability code

Qualification Report:Please open the attachments included with this PCN labeled as PCN_#_Qual_Report.

Revision History:September 27, 2022: Issued initial notification.

May 31, 2023: Issued final notification. Attached the Qualification Report. Provided estimated first ship date to be on June 30, 2023.

The change described in this PCN does not alter Microchip's current regulatory compliance regarding the material content of the applicable products.

Attachments:

[PCN_CENO-11FRYW234_Pre and Post Change_Summary.pdf](#)

[PCN_CENO-11FRYW234_Qual_Report.pdf](#)

Please contact your local [Microchip sales office](#) with questions or concerns regarding this notification.

Terms and Conditions:


If you wish to receive Microchip PCNs via email please register for our PCN email service at our [PCN home page](#) select register then fill in the required fields. You will find instructions about registering for Microchips PCN email service in the [PCN FAQ](#) section.

If you wish to change your PCN profile, including opt out, please go to the [PCN home page](#) select login and sign into your myMicrochip account. Select a profile option from the left navigation bar and make the applicable selections.

CCB 5131
Pre and Post Change Summary
PCN #: CENO-11FRYW234




A Leading Provider of Smart, Connected and Secure Embedded Control Solutions



SMART | CONNECTED | SECURE

LEAD FRAME COMPARISON

Pre Change




Note: Not to scale

Lead frame Material

EFTEC64T

Post Change



Note: Not to scale

Lead frame Material

C194

Affected Catalog Part Numbers (CPN)

PIC24EP128GP204-I/MV
PIC24EP128MC204-I/MV
DSPIC33EP128GP504T-H/MV
DSPIC33EP128MC204T-H/MV
DSPIC33EP128MC504T-H/MV
PIC24EP128GP204T-H/MV
PIC24EP128MC204T-H/MV
DSPIC33EP128GP504-H/MV
DSPIC33EP128MC204-H/MV
DSPIC33EP128MC504-H/MV
PIC24EP128GP204-H/MV
PIC24EP128MC204-H/MV
DSPIC33EP128GP504T-I/MV
DSPIC33EP128MC204T-I/MV
DSPIC33EP128MC504T-I/MV
PIC24EP128GP204T-I/MV
PIC24EP128MC204T-I/MV
DSPIC33EP128GP504T-E/MV
DSPIC33EP128MC204T-E/MV
DSPIC33EP128MC504T-E/MV
PIC24EP128GP204T-E/MV
PIC24EP128MC204T-E/MV
DSPIC33EP256GP504-E/MV
DSPIC33EP256MC204-E/MV
DSPIC33EP256MC504-E/MV
PIC24EP256GP204-E/MV
PIC24EP256MC204-E/MV
DSPIC33EP256GP504-I/MV
DSPIC33EP256MC204-I/MV
DSPIC33EP256MC504-I/MV
PIC24EP256GP204-I/MV
PIC24EP256MC204-I/MV
PIC24EP256GP204-I/MVA3
DSPIC33EP256GP504T-H/MV
DSPIC33EP256MC204T-H/MV
DSPIC33EP256MC504T-H/MV
PIC24EP256GP204T-H/MV
PIC24EP256MC204T-H/MV
DSPIC33EP256GP504-H/MV
DSPIC33EP256MC204-H/MV
DSPIC33EP256MC504-H/MV
PIC24EP256GP204-H/MV
PIC24EP256MC204-H/MV
PIC24EP256GP204T-I/MV030
DSPIC33EP256GP504T-I/MV
DSPIC33EP256MC204T-I/MV

CENO-11FRYW234 - CCB 5131 Final Notice: Qualification of C194 as an additional lead frame material for selected DSPIC33EPxxxxx, PIC24EP12xxxx, PIC24EP25xxxx, PIC24EP32xxx and PIC24EP64xxx device families available in 48L UQFN (6x6x0.5mm) package.

DSPIC33EP256MC504T-I/MV

PIC24EP256GP204T-I/MV

PIC24EP256MC204T-I/MV

DSPIC33EP256GP504T-E/MV

DSPIC33EP256MC204T-E/MV

DSPIC33EP256MC504T-E/MV

PIC24EP256GP204T-E/MV

PIC24EP256MC204T-E/MV

DSPIC33EP32GP504-E/MV

DSPIC33EP32MC204-E/MV

DSPIC33EP32MC504-E/MV

PIC24EP32GP204-E/MV

PIC24EP32MC204-E/MV

DSPIC33EP32GP504-I/MV

DSPIC33EP32MC204-I/MV

DSPIC33EP32MC504-I/MV

PIC24EP32GP204-I/MV

PIC24EP32MC204-I/MV

DSPIC33EP32GP504T-H/MV

DSPIC33EP32MC204T-H/MV

DSPIC33EP32MC504T-H/MV

PIC24EP32GP204T-H/MV

PIC24EP32MC204T-H/MV

DSPIC33EP32GP504-H/MV

DSPIC33EP32MC204-H/MV

DSPIC33EP32MC504-H/MV

PIC24EP32GP204-H/MV

PIC24EP32MC204-H/MV

DSPIC33EP32GP504T-I/MV

DSPIC33EP32MC204T-I/MV

DSPIC33EP32MC504T-I/MV

PIC24EP32GP204T-I/MV

PIC24EP32MC204T-I/MV

DSPIC33EP32GP504T-E/MV

DSPIC33EP32MC204T-E/MV

DSPIC33EP32MC504T-E/MV

PIC24EP32GP204T-E/MV

PIC24EP32MC204T-E/MV

DSPIC33EP64GP504-E/MV

DSPIC33EP64MC204-E/MV

DSPIC33EP64MC504-E/MV

PIC24EP64GP204-E/MV

PIC24EP64MC204-E/MV

DSPIC33EP64GP504-I/MV

DSPIC33EP64MC204-I/MV

DSPIC33EP64MC504-I/MV

PIC24EP64GP204-I/MV

PIC24EP64MC204-I/MV

DSPIC33EP64GP504T-H/MV

CENO-11FRYW234 - CCB 5131 Final Notice: Qualification of C194 as an additional lead frame material for selected DSPIC33EPxxxxx, PIC24EP12xxxx, PIC24EP25xxxx, PIC24EP32xxx and PIC24EP64xxx device families available in 48L UQFN (6x6x0.5mm) package.

DSPIC33EP64MC204T-H/MV

DSPIC33EP64MC504T-H/MV

PIC24EP64GP204T-H/MV

PIC24EP64MC204T-H/MV

DSPIC33EP64GP504-H/MV

DSPIC33EP64MC204-H/MV

DSPIC33EP64MC504-H/MV

PIC24EP64GP204-H/MV

PIC24EP64MC204-H/MV

DSPIC33EP64GP504T-I/MV

DSPIC33EP64MC204T-I/MV

DSPIC33EP64MC504T-I/MV

PIC24EP64MC204T-I/MV

DSPIC33EP64GP504T-E/MV

DSPIC33EP64MC204T-E/MV

DSPIC33EP64MC504T-E/MV

PIC24EP64GP204T-E/MV

PIC24EP64MC204T-E/MV

DSPIC33EP128GP504-E/MV

DSPIC33EP128MC204-E/MV

DSPIC33EP128MC504-E/MV

PIC24EP128GP204-E/MV

PIC24EP128MC204-E/MV

DSPIC33EP128GP504-I/MV

DSPIC33EP128MC204-I/MV

DSPIC33EP128MC504-I/MV



QUALIFICATION REPORT SUMMARY
RELIABILITY LABORATORY

PCN #: CENO-11FRYW234

Date:
May 17, 2023

Qualification of C194 as an additional lead frame material for selected DSPIC33EPxxxxx, PIC24EP12xxxx, PIC24EP25xxxx, PIC24EP32xxx and PIC24EP64xxx device families available in 48L UQFN (6x6x0.5mm) package.



MICROCHIP

PACKAGE QUALIFICATION REPORT

Purpose	Qualification of C194 as an additional lead frame material for selected DSPIC33EPxxxxx, PIC24EP12xxxx, PIC24EP25xxxx, PIC24EP32xxx and PIC24EP64xxx device families available in 48L UQFN (6x6x0.5mm) package.
QUAL ID	R2300317 Rev. A
MP CODE	TLAE1JR7XNFA
Part No.	PIC24EP256GP204T-H/MV
Bonding No.	BD-000937 Rev. 01
CCB No.	5131
<u>Package</u>	
Type	48L UQFN
Package size	6 x 6 x 0.5 mm
<u>Lead Frame</u>	
Paddle size	193 x 193 mils
Material	C194
Surface	Ag on lead only
Process	Etched
Lead Lock	Dimple
Part Number	FU0295
<u>Material</u>	
Epoxy	8600
Wire	Au wire
Mold Compound	G700LTD
Plating Composition	Matte Sn



MICROCHIP **PACKAGE QUALIFICATION REPORT**

Manufacturing Information

Assembly Lot No.	Wafer Lot No.	Date Code
NSEB234200565.000	TC11923335491.300	2303S72
NSEB234200566.000	TC11923335491.300	2303S7G
NSEB234200567.000	TC11923335491.300	2303S7S

Result



Pass



Fail



48L UQFN (6x6x0.5 mm) assembled by MTAI pass reliability test per QCI-39000.
This package was qualified the Moisture/Reflow Sensitivity Classification Level 1 at 260°C
reflow temperature per IPC/JEDEC J-STD-020E standard.

PACKAGE QUALIFICATION REPORT

Test Number (Reference)	Test Condition	Standard/ Method	Qty. (Acc.)	Def/SS	Result	Remarks
<u>Precondition</u> <u>Prior Perform</u> <u>Reliability Tests</u> (At MSL Level 1)	Electrical Test: +25°C, 85°C, 125°C and 150°C System: J750	JESD22-A113	693(0)	0/693		Good Devices
	Bake 150°C, 24 hrs. System: CHINEE	JIP/ IPC/JEDEC J-STD-020E		0/693		
	85°C/85%RH Moisture Soak 168 hrs. System: TABAI ESPEC Model PR-3SPH			0/693		
	3x Convection-Reflow 265°C max System: Vitronics Soltec MR1243			0/693		
	Electrical Test: +25°C, 85°C, 125°C and 150°C System: J750		693(0)	0/693	Pass	

PACKAGE QUALIFICATION REPORT

Test Number (Reference)	Test Condition	Standard/ Method	Qty. (Acc.)	Def/SS.	Result	Remarks
Temp Cycle	Stress Condition: -55°C to +150°C, 2000 Cycles System: TABAI ESPEC TSA-70H Electrical Test: +85°C, 125°C and 150°C System: J750 Bond Strength: Wire Pull (>3.00 grams)	JESD22-A104	231(0) 15(0)	0/231 0/231 0/15	Pass Pass	Parts had been pre-conditioned at 260°C 77 units / lot
UNBIASED-HAST	Stress Condition: +130°C/85%RH, 96 hrs. System: HAST 6000X Electrical Test: +25°C System: J750	JESD22-A118	231(0)	0/231 0/231	Pass	Parts had been pre-conditioned at 260°C 77 units / lot
HAST	Stress Condition: +130°C/85%RH, 96 hrs. Bias Volt: 3.6 Volts System: HAST 6000X Electrical Test: +25°C, 85°C, 125°C and 150°C System: J750	JESD22-A110	231(0)	0/231 0/231	Pass	Parts had been pre-conditioned at 260°C 77 units / lot

PACKAGE QUALIFICATION REPORT

Test Number (Reference)	Test Condition	Standard/ Method	Qty. (Acc.)	Def/SS.	Result	Remarks
High Temperature Storage Life	Stress Condition: Bake 175°C, 1000 hrs. System: SHEL LAB Electrical Test: +25°C, 85°C, 125°C and 150°C System: J750	JESD22- A103	45(0)	0/45 0/45	Pass	45 units
Solderability Temp 215°C	Steam Aging: Temp 93°C,8Hrs System: SAS-3000 Solder Dipping: Solder Temp.215°C Solder material: SnPb Sn63, Pb37 System: ERSA RA 2200D Visual Inspection: External Visual Inspection	J-STD-002	22(0)	0/22 0/22 0/22	Pass	
Solderability Temp 245°C	Steam Aging: Temp 93°C,8Hrs System: SAS-3000 Solder Dipping: Solder Temp.245°C Solder material: Pb Free Sn 95.5Ag3.9 Cu0.6 System: ERSA RA 2200D Visual Inspection: External Visual Inspection	J-STD-002	22(0)	0/22 0/22 0/22	Pass	
Physical Dimensions	Physical Dimension, 10 units / 1 lot	JESD22- B100/B108	30(0) Units	0/30	Pass	
Bond Strength Data Assembly	Wire Pull (>3.00 grams) Bond Shear (>13.00 grams)	Mil. Std. 883-2011 CDF-AEC- Q100-001	30(0) Wires 30(0) bonds	0/30 0/30	Pass Pass	