



MACRONIX
INTERNATIONAL Co., LTD.

APPLICATION NOTE

Migrating to MX25L4006E from MX25L4005A and MX25L4005C



Migrating to MX25L4006E from MX25L4005A and MX25L4005C

Contents

1. Introduction	2
2. General Features	3
2-1. Feature Comparison.....	3
Table 1: Major Feature Comparison of 4Mb Devices	3
2-2: Performance Comparison.....	4
Table 2: Performance Comparison of 4Mb Devices	4
3. Command Set Comparison	5
Table 3: Commands for the MX25L4005A/MX25L4005C and MX25L4006E Devices	5
4. Device ID Code Comparison of 4Mb Devices	6
Table 4: ID Code Comparison	6
5. References	6
REVISION HISTORY	7



Migrating to MX25L4006E from MX25L4005A and MX25L4005C

1. Introduction

This application note indicates the differences between MX25L4006E and MX25L4005A/MX25L4005C.

In Single I/O mode, MX25L4006E is identical in forms and functions with the MX25L4005A & MX25L4005C. MX25L4006E is capable of Dual Output mode (Single Input / Dual Output) but no longer supports Dual Input / Dual Output mode. The comparison and features of new products are described as below.

The information provided is based on the data available at the time. The MX25L4006E datasheet may override this application note if there is a difference description for the same in the datasheet.

Migrating to MX25L4006E from MX25L4005A and MX25L4005C

2. General Features

2-1. Feature Comparison

The Dual Output mode (1I/2O) is one of the new features of the MX25L4006E, and the most advanced technique is that this new product accepts wide range of clock rate from DC (Direct Current)~ 86MHz for frequency control from host system.

Table 1: Major Feature Comparison of 4Mb Devices

Feature		MX25L4005A/ MX25L4005C	MX25L4006E
Voltage		2.7~3.6 V	2.7~3.6 V
Interface		x1	x1, 1I/2O*
Package		8-SOP(150mil/209mil) 8-WSON(6x5mm) 8-PDIP(300mil) 8-USON(4x4)**	8-SOP(150mil/209mil) 8-WSON(6x5mm) 8-PDIP(300mil)
Operation Temperature		-40~85 °C	-40~85 °C
Sector / Block Structure		4KB / 64KB	4KB / 64KB
Clock Rate***	Fast Read	1KHz~85MHz	DC~86MHz
	Read	1KHz~33MHz	DC~33MHz
	DREAD (Dual Output)	--	DC~80MHz
Byte Program		NA	Yes
Block Protection (NVM)		BP2,BP1,BP0	BP2,BP1,BP0
HOLD#		Yes	Yes
WP#		Yes	Yes

***Note:**

* MX25L4006E 1I/2O is Dual Output mode, means Single input - Dual output

** Only MX25L4005A has 8-USON

*** 1KHz is minimum clock rate. DC = no minimum clock rate

Migrating to MX25L4006E from MX25L4005A and MX25L4005C

2-2: Performance Comparison

Table below is the comparison of new product and the former products.

Table 2: Performance Comparison of 4Mb Devices

Performance		MX25L4005A/ MX25L4005C	MX25L4006E
Clock High/ Low Time@33MHz	tCH	15ns(min.)	13ns(min.)
	tCL	15ns(min.)	13ns(min.)
Program Time	Byte	NA	9us(typ.) ; 300us(max.)
	Page	1.4ms(typ.) ; 5ms(max.)	1.4ms(typ.) ; 5ms(max.)
Erase Time	Sector(4KB)	60ms(typ.)	60ms(typ.)
	Block(64KB)	1s(typ.) ; 2s(max.)	0.7s(typ.) ; 2s(max.)
	Chip	3.5s (typ.); 7.5s(max.)	3.5s (typ.); 7.5s(max.)
Read ID	tRES1	3us(max.)	8.8us(max.)
	tRES2	1.8us(max.)	8.8us(max.)
Write Status Register	tW	5ms(typ.); 15ms(max.)	10ms(typ.); 100ms(max.)
CS# Deselect Time	tSHSL	Read/write=100ns(min.)	Read=15ns(min.) ; Write=40ns(min.)
Active Setup Time	tSLCH	5ns(min.)	7ns(min.)
Not Active Setup Time	tSHCH	5ns(min.)	7ns(min.)
Active Hold Time	tCHSH	5ns(min.)	7ns(min.)
Not Active Hold Time	tCHSL	5ns(min.)	7ns(min.)
VCC Standby	ISB1	10uA(max.)	25uA(max.)
Deep Power Down	tDP	3us(max.)	10us(max.)
	ISB2	10uA(max.)	10uA(max.)
Active Current	ICC1	12mA(max.) @85MHz	12mA(max.) @86MHz
	ICC2	15mA	20mA
	ICC3	15mA	15mA
	ICC4	15mA	15mA
	ICC5	15mA	20mA

Migrating to MX25L4006E from MX25L4005A and MX25L4005C**3. Command Set Comparison**

The new product adds new command Double Output Mode Command (DREAD) for the new feature.

Table 3: Commands for the MX25L4005A/MX25L4005C and MX25L4006E Devices

Command		MX25L4005A/ MX25L4005C	MX25L4006E
Write	WREN	06h	06h
	WRDI	04h	04h
	WRSR	01h	01h
Read	RDID	9Fh	9Fh
	RDSR	05h	05h
	READ	03h	03h
	Fast Read	0Bh	0Bh
	DREAD	-	3Bh
	RES	ABh	ABh
	REMS	90h	90h
Erase	SE	20h	20h
	BE	52h or D8h	52h or D8h
	CE	60h or C7h	60h or C7h
Program	PP	02h	02h
Deep Power Down	DP	B9h	B9h
	DRP	ABh	ABh

Migrating to MX25L4006E from MX25L4005A and MX25L4005C**4. Device ID Code Comparison of 4Mb Devices**

This table shows that Manufacturer and Device IDs have not been changed. The density (13) is defined by MXIC and also has not been changed.

Table 4: ID Code Comparison

Command Type	MX25L4005A			MX25L4005C			MX25L4006E		
RDID Command	M ID	Type	Density	M ID	Type	Density	M ID	Type	Density
	C2	20	13	C2	20	13	C2	20	13
RES Command	E ID			E ID			E ID		
	12			12			12		
REMS	M ID	Device ID		M ID	Device ID		M ID	Device ID	
	C2	12		C2	12		C2	12	

5. References

The following datasheets were used for preparing this comparison note:

Datasheet	Location	Date Issued	Versions
MX25L4005A	Macronix Website	Apr., 2009	2.0
MX25L4005C	Macronix Website	Jan., 2010	1.4
MX25L4006E	Macronix Website	May., 2010	0.01

For more functional and parametric specifications, please refer to the datasheet on the Macronix Website at <http://www.macronix.com/> and go to: Products/Flash Memory/Serial Flash.



Migrating to MX25L4006E from MX25L4005A and MX25L4005C

REVISION HISTORY

Revision No.	Description	Page	Date
1.0	1. Removed SFDP descriptions 2. Emphasizes wide range of clock rate	P2-3,5 P3	JUL/8/2010



MACRONIX
INTERNATIONAL Co., LTD.

APPLICATION NOTE

Macronix's products are not designed, manufactured, or intended for use for any high risk applications in which the failure of a single component could cause death, personal injury, severe physical damage, or other substantial harm to persons or property, such as life-support systems, high temperature automotive, medical, aircraft and military application. Macronix and its suppliers will not be liable to you and/or any third party for any claims, injuries or damages that may be incurred due to use of Macronix's products in the prohibited applications.

Copyright© Macronix International Co., Ltd. 2010. All Rights Reserved. Macronix, MXIC, MXIC Logo, MX Logo, are trademarks or registered trademarks of Macronix International Co., Ltd. The names and brands of other companies are for identification purposes only and may be claimed as the property of the respective companies.

For the contact and order information, please visit Macronix's Web site at: <http://www.macronix.com>