



Product Change Notification - KSRA-14OKGY636

Date:

19 Mar 2019

Product Category:

Memory

Affected CPNs:**Notification subject:**

CCB 3017 Cancellation Notice: Initial PCN KSRA-14OKGY636 was a duplicate PCN. Please see correct PCN No. LIAL-10CXTM831.

Notification text:**PCN Status:**

Cancellation notification

PCN Type:

Manufacturing Change

Microchip Parts Affected:

This PCN announced a change to select products of the 36.3K wafer technology of the 24AAx and 24LCxx device families available in 8L MSOP package but because this was a duplicate PCN it is no longer needed, please view the correct PCN No. [LIAL-10CXTM831](#).

Description of Change:

The notification KSRA-14OKGY636 was a duplicated PCN the correct PCN is [LIAL-10CXTM831](#). As such, we are issuing this cancellation of KSRA-14OKGY636. Please see the new notification [LIAL-10CXTM831](#) for the qualification of 36.3K process technology for selected Microchip products of the 24xx01, 24xx02, and 24xx04 device families.

Impacts to Data Sheet:

Not applicable

Change Impact:

Not applicable

Reason for Change:

Final PCN was issued under [LIAL-10CXTM831](#).

Change Implementation Status:

Not applicable

Estimated First Ship Date:

See PCN [LIAL-10CXTM831](#).

Method to Identify Change:

See PCN [LIAL-10CXTM831](#).

Revision History:

August 15, 2017: Issued initial notification.

January 29, 2019: Issued cancellation notice for the proposed qualification of 36.3K process technology for selected products of the 24AAx and 24LCxx device families available in 8L MSOP package.

March 19, 2019: Re-issued this cancellation notice to clarify in the history that only the initial PCN issued was cancelled due to the duplication and final PCN was issued under [LIAL-10CXTM831](#).

The change described in this PCN does not alter Microchip's current regulatory compliance regarding the material content of the applicable products.

Attachment(s):



Please contact your local [Microchip sales office](#) with questions or concerns regarding this notification.

Terms and Conditions:

If you wish to [receive Microchip PCNs via email](#) please register for our PCN email service at our [PCN home page](#) select register then fill in the required fields. You will find instructions about registering for Microchips PCN email service in the [PCN FAQ](#) section.

If you wish to [change your PCN profile, including opt out](#), please go to the [PCN home page](#) select login and sign into your myMicrochip account. Select a profile option from the left navigation bar and make the applicable selections.

KSRA-14OKGY636 - CCB 3017 Cancellation Notice: Initial PCN KSRA-14OKGY636 was a duplicate PCN. Please :

Affected Catalog Part Numbers(CPN)

24AA01H-I/MS
24AA01HT-I/MS
24AA01-I/MS
24AA01T-I/MS
24AA02H-I/MS
24AA02HT-I/MS
24AA02-I/MS
24AA02-I/MSB31
24AA02T-I/MS
24AA02T-I/MSB31
24AA04H-I/MS
24AA04HT-I/MS
24AA04-I/MS
24AA04T-I/MS
24LC01BH-I/MS
24LC01BHT-I/MS
24LC01B-I/MS
24LC01BT-I/MS
24LC02BH-I/MS
24LC02BHT-I/MS
24LC02B-I/MS
24LC02BT-I/MS
24LC04BH-I/MS
24LC04BHT-I/MS
24LC04B-I/MS
24LC04BT-I/MS



Product Change Notification - LIAL-10CXTM831

Date:

20 Dec 2018

Product Category:

Memory

Affected CPNs:**Notification subject:**

Memo # ML122018001Q: Final Notice: Qualification of 36.3K process technology for selected Microchip products of the 24xx01, 24xx02, and 24xx04 device families.

Notification text:**PCN Status:**

Final notification.

PCN Type:

Manufacturing Change

Microchip Parts Affected:

Please open one of the icons found in the Affected CPNs section above.

NOTE: For your convenience Microchip includes identical files in two formats (.pdf and .xls)

Description of Change:

Qualification of 36.3K process technology for selected Microchip products of the 24xx01, 24xx02, and 24xx04 device families.

Pre Change:

Available in 160K wafer technology fabricated at Microchip fabrication sites FAB2 and FAB4 (Tempe, AZ and Gresham, OR, USA) using 8 inch wafers

Post Change:

Available in 160K wafer technology fabricated at Microchip fabrication sites FAB2 and FAB4 (Tempe, AZ and Gresham, OR, USA) using 8 inch wafers or available in 36.3K wafer technology fabricated at FAB 5 (Colorado Springs, CO, USA) using 6 inch wafers.

Pre and Post Change Summary:

	Pre Change	Post Change	
Wafer Technology	160K wafer technology	160K wafer technology	36.3K wafer technology
Fabrication Location	Microchip Fabrication Sites FAB 2 and FAB4 (Tempe, AZ and Gresham, OR, USA)	Microchip Fabrication Sites FAB 2 and FAB4 (Tempe, AZ and Gresham, OR, USA)	FAB 5 (Colorado Springs, CO USA)
Wafer Diameter	8 inches (200 mm)	8 inches (200 mm)	6 inches (150 mm)
Quality certification	ISO/TS16949	ISO/TS16949	ISO9001/TS16949



--	--	--	--

Impacts to Data Sheet:

None

Change Impact:

None

Reason for Change:

To improve manufacturability by qualifying an additional fabrication site.

Change Implementation Status:

In Progress.

Estimated First Ship Date:

February 5, 2019 (date code: 1906)

NOTE: Please be advised that after the estimated first ship date customers may receive pre and post change parts.

Time Table Summary:

	December 2018					->	February 2019				
Workweek	48	49	50	51	52		5	6	7	8	9
Final PCN Issue Date				X							
Qual Report Availability				X							
Estimated Implementation Date							X				

Method to Identify Change:

Traceability code

Qualification Report:

Please open the attachments included with this PCN labeled as PCN_#_Qual Report.

Revision History:

December 20, 2018: Issued final notification. Attached the qualification report. Provided estimated first ship date to be on February 5, 2019.

The change described in this PCN does not alter Microchip's current regulatory compliance regarding the material content of the applicable products.

Attachment(s):

[PCN LIAL-10CXTM831_QUAL_REPORT.pdf](#)

Please contact your local [Microchip sales office](#) with questions or concerns regarding this notification.

Terms and Conditions:



If you wish to receive Microchip PCNs via email please register for our PCN email service at our [PCN home page](#) select register then fill in the required fields. You will find instructions about registering for Microchips PCN email service in the [PCN FAQ](#) section.

If you wish to change your PCN profile, including opt out, please go to the [PCN home page](#) select login and sign into your myMicrochip account. Select a profile option from the left navigation bar and make the applicable selections.



MICROCHIP

QUALIFICATION REPORT SUMMARY
RELIABILITY LABORATORY

PCN#: LIAL-10CXTM831

Date
November 27, 2018

**Qualification of 36.3K process technology for selected
Microchip products of the 24xx01, 24xx02, and 24xx04 device
families**



MICROCHIP

SUMMARY QUALIFICATION REPORT

Purpose: Qualification of 36.3K process technology for selected Microchip products of the 24xx01, 24xx02, and 24xx04 device families.

Document Control #: ML112018006E

Document Revision: D

Device(s): 24xx01x, 24xx02x, 24xx04x

Product: 4K, 512 X 8 1.8V SERIAL EE

Mask Identification #: 363V2

Process 36.3K

MSL: 3301



Test Conditions:

TEST	METHOD	CONDITION	SAMPLE SIZE RUN	CRITERIA
Early Life Failure Test	AEC Q100	150 °C, 24 Hrs Electrical Test at +25 °C and 125 °C	820	0/800
High Temperature Operating Life / Dynamic Life Test	MIL-STD 883 Method 1005	150°C, 408 Hrs Electrical Test at -40°C, +25°C, +85°C and/or +125°C.	620	0/600 1 Lot
Endurance Cycling and Bakes (END)	MIL-STD 883 Method 1033	100K data memory, E/W cycles, 85°C Bake 1: 150°C, 48 Hrs Bake 2: 150°C, 48 Hrs	242	0/231
High Temperature Retention Bake (RET)	MIL-STD 883 Method 1033	175°C, 504 Hrs	242	0/231
EDR HTOL(DLT)	MIL-STD 883 Method 1033	100K data memory, E/W cycles, 85 °C, 408 hours HTOL at 150 °C Electrical pre and post test at +25 °C and 125 °C.	92	0/77
ESD Human Body Model	JS-001	1.5K Ohm, 100 pF Electrical Test at +25°C, +85°C and/or +125°C.	27	2000 V 1 Lot
ESD Charged Device Model	JS-002	1 Ohm pogo pin to ground with a 50-ohm impedance matched cable, device is placed onto a charge plate separated by a dielectric material. Electrical test at +25°C, +85°C and/or +125°C.	18	500V on all pins, 750V on corner pins 1 Lot
ESD Machine Model	JESD22A115	0 Ohm, 200 pF Electrical Test at +25°C, +85°C and/or +125°C.	12	200 V 1 Lot
Latch-up Testing	JESD78	Trigger Voltage Limit = $1.5 \cdot V_{max}$ Pulse Width = 10 ms Rise/Fall Time = 500 us Test at +25°C and +125°C	6 24	1 Lot 200 mA (0/6) 105 mA (0/12)



MICROCHIP

SUMMARY QUALIFICATION REPORT

Qualification Material:

LOT	LOT 1	LOT 2	LOT 3
DEVICE	24LC04B	24LC04B	24LC04B
MASK, REV	363V2, C0	363V2, C1	363V2, C1
WAFER FAB	Colorado Springs 6 inch fabrication	Colorado Springs 6 inch fabrication	Colorado Springs 6 inch fabrication
WAFER PROCESS	36.3K 6"	36.3K 6"	36.3K 6"
WAFER LOT	MCSO519113359.000	E8U3576	MCSO519228073.000
ASSEMBLY LOT	MMT-191401703.000	Chandler	MMT-192801215.000
PACKAGE	PDIP	8L GSB	8L TSSOP
ASSEMBLY SITE	MMT	Chandler	MMT
FINAL TEST	MTAI	Chandler	MCSO
QUAL #	R18097-0x	ML092018001L ML092018006A	ML122018002C/ ML1220180048
CN #	ES212662	ES212662	ES212662
QUAL TESTS	ELFR, HTOL	ESD HBM, MM, LU	CDM, LU

Conclusion:

Pass Fail

Based on the results, the 24LC04B complies with the reliability guidelines specified in QCI-39000. Therefore, the 24xx04x, 24xx02x, and the 24xx01x are released to production

Die Level Results:

DYNAMIC LIFE TESTING AT 150°C

	24 Hours	408 Hours
Lot 1	0/820	0/620

Activation Energy	0.7 eV
Derated Temperature	55°C

	Infant Mortality	Total Life	MTBF (Years)
Device Hours	19,680	257,760	N/A
Fit Rate - 50% Confidence	136	10	10997.80
Fit Rate - 60% Confidence	180	14	8317.59
Fit Rate - 90% Confidence	452	34	3310.66

Note: One FIT is one fail in 10⁹ device hours

	Best Estimated Failure Rate (%\KHR)
Infant Mortality	0.0136
Total Life	0.0010

ENDURANCE CYCLING AT 85°C AND BAKES AT 150°C

	100,000 cycles Data Flash Memory Erase/Write Cycling	Bake 1	Bake 2
Lot 1	0/242	0/242	0/242

HIGH TEMPERATURE RETENTION BAKE AT 175°C

	96 Hours	504 Hours
Lot 1	0/242	0/242

Activation Energy	0.7 eV
Derated Temperature	55°C

	Total Life
Device Hours	116,160
FIT Rate - 50% Confidence	23
FIT Rate - 60% Confidence	30
FIT Rate - 90% Confidence	76

Note: One FIT is one fail in 10⁹ device hours

ENDURANCE CYCLING AT 85°C AND DYNAMIC LIFE TEST AT 150°C (HTOL)

	100,000 cycles Data Flash Memory Erase/Write Cycling	96 Hours (HTOL)	408 Hours (HTOL)
Lot 1	0/92	0/92	3/89 ^a

* Three devices were discounted due to test handler damage to the leads

ELECTROSTATIC DISCHARGE TESTS

	Human Body Model	Machine Model
Lot 2	Pass up to 5500V	Pass up to 400V

	Charge Device model
Lot 3	Pass up to 2000V

LATCH-UP TEST

	200mA @ 25C	105mA @ 85°C
Lot 2	Passed	Passed

	105mA @ 125C
Lot 3	Passed

LIAL-10CXTM831 - Me 24xx02 and 24xx04 device families.

Affected Catalog Part Numbers(CPN)

24AA01/SN
24AA01H-I/MS
24AA01H-I/P
24AA01H-I/SN
24AA01H-I/ST
24AA01HT-I/LT
24AA01HT-I/MNY
24AA01HT-I/MS
24AA01HT-I/OT
24AA01HT-I/SN
24AA01HT-I/ST
24AA01-I/MS
24AA01-I/P
24AA01-I/SN
24AA01-I/ST
24AA01T/SN
24AA01T-I/LT
24AA01T-I/MC
24AA01T-I/MNY
24AA01T-I/MS
24AA01T-I/OT
24AA01T-I/SN
24AA01T-I/ST
24AA02/P
24AA02/SN
24AA02/ST
24AA02H-I/MS
24AA02H-I/P
24AA02H-I/SN
24AA02H-I/ST
24AA02HT-I/LT
24AA02HT-I/MNY
24AA02HT-I/MS
24AA02HT-I/OT
24AA02HT-I/SN
24AA02HT-I/ST
24AA02-I/MS
24AA02-I/P
24AA02-I/SN
24AA02-I/ST
24AA02T/SN
24AA02T-I/LT

24AA02T-I/MC
24AA02T-I/MNY
24AA02T-I/MS
24AA02T-I/OT
24AA02T-I/SN
24AA02T-I/ST
24LC01B/P
24LC01B/SN
24LC01B/ST
24LC01BH-I/MS
24LC01BH-I/P
24LC01BH-I/SN
24LC01BH-I/ST
24LC01BHT-I/LT
24LC01BHT-I/MNY
24LC01BHT-I/MS
24LC01BHT-I/OT
24LC01BHT-I/SN
24LC01BHT-I/ST
24LC01B-I/MS
24LC01B-I/P
24LC01B-I/SN
24LC01B-I/ST
24LC01BT/OT
24LC01BT/SN
24LC01BT/ST
24LC01BT-I/LT
24LC01BT-I/MC
24LC01BT-I/MNY
24LC01BT-I/MS
24LC01BT-I/OT
24LC01BT-I/SN
24LC01BT-I/ST
24LC02B/P
24LC02B/SN
24LC02B/ST
24LC02BH-I/MS
24LC02BH-I/P
24LC02BH-I/SN
24LC02BH-I/ST
24LC02BHT-I/LT
24LC02BHT-I/MNY
24LC02BHT-I/MS
24LC02BHT-I/OT
24LC02BHT-I/SN
24LC02BHT-I/ST
24LC02B-I/MS

24LC02B-I/P
24LC02B-I/SN
24LC02B-I/ST
24LC02BT/SN
24LC02BT/ST
24LC02BT-I/LT
24LC02BT-I/MC
24LC02BT-I/MNY
24LC02BT-I/MS
24LC02BT-I/OT
24LC02BT-I/SN
24LC02BT-I/ST
24AA04/P
24AA04/SN
24AA04H-I/MS
24AA04H-I/P
24AA04H-I/SN
24AA04H-I/ST
24AA04HT-I/MNY
24AA04HT-I/MS
24AA04HT-I/OT
24AA04HT-I/SN
24AA04HT-I/ST
24AA04-I/MC
24AA04-I/MS
24AA04-I/P
24AA04-I/SN
24AA04-I/ST
24AA04T/SN
24AA04T-I/MC
24AA04T-I/MNY
24AA04T-I/MS
24AA04T-I/OT
24AA04T-I/SN
24AA04T-I/ST
24LC04B/P
24LC04B/SN
24LC04B/ST
24LC04BH-I/MS
24LC04BH-I/P
24LC04BH-I/SN
24LC04BH-I/ST
24LC04BHT-I/MNY
24LC04BHT-I/MS
24LC04BHT-I/OT
24LC04BHT-I/SN
24LC04BHT-I/ST

24LC04B-I/MC
24LC04B-I/MS
24LC04B-I/P
24LC04B-I/SN
24LC04B-I/ST
24LC04BT/SN
24LC04BT/ST
24LC04BT-I/MC
24LC04BT-I/MNY
24LC04BT-I/MS
24LC04BT-I/OT
24LC04BT-I/SN
24LC04BT-I/ST