



Dear Valued Customer

Doc. No.: 2222002
Issue date: September 1, 2022

Akihiro Hikasa
General Manager

High Power Devices Division
Power Discrete Business Headquarters
ROHM Co., Ltd.

Notification of Product/Process Change

This is an announcement of change(s) to the process of the products currently supplied by ROHM Co., Ltd.

We request your acknowledgement of the receipt of this notification within the given period.

Please provide your reply by September 1, 2023

Title of change	Wafer Diameter Change, Wafer Process Production Site Change for 3rd Generation SiC MOSFET (TO247N Package) SCT3****L Series [PCN No.2222002]		
Affected product(s)	Manufacturer part number		Customer part number
	SCT3□□□□LGC11/SCT3□□□□LHRC11		
Detailed description of change	Now		After
	<ul style="list-style-type: none"> On-board SiC chip's wafer diameter:4inch Front-end manufacturing plants : ROHM Apollo Co., Ltd. Chikugo Plant 		<ul style="list-style-type: none"> On-board SiC chip's wafer diameter:6inch Front-end manufacturing plants : Lapis Semiconductor Co., Ltd. Miyazaki Plant
Reason for change	To expand production capacity.		
Anticipated impact on quality	There is no difference in reliability and electrical characteristics.		
Identification of change	It can be identified by Lot number.		
Planned first ship date :	April 1, 2023	Sample available schedule :	Within 1.5 months from request
Attachments (data, report)	yes	4M 2222002-2_4ME	Rbl 2222002-3_Rbl
Comments			

		Reply date	
Customer reply	<input type="checkbox"/> 1. Approved. <input type="checkbox"/> 2. Accepted with conditions. <input type="checkbox"/> 3. Rejected.		
Condition for approval / reason for rejection			
Comments			
Customer company name			
Customer signature			Department
Customer signature			Department



Electronics for the Future

【Additional approval and change approval document】

Affected Manufacturing Department: HPD Division

Affected product group: SiC

SiC 6-inch factory additional approval

Document ID:2222002_PCN Details

Table of contents

PCN No.2222002



1. Background of the change	P.03
2. Summary of this approval	P.04
3. Summary of changes	P.05
4. Affected Products	P.06
5. Factory Overview	P.07-08
6. List of Changes	P.09
7. Comparison of production plants	P.10
8. 5M Change Point Verification	P.11
9. Process Change Point Verification	P.12-13
10. Product Performance Evaluation Results	P.14
11. Summary of Evaluation Results	P.15
12. Comparison of electrical characteristics	P.16-17
13. Reliability Test Results	P.18-24

1. Background of the change

PCN No.2222002



[About SiC 6inch additional approval]

In order to expand the production capacity , we are planning to **introduce larger wafer sizes , 6inch instead of 4inch.**

For the future supply , We ask for your cooperation to approve.

*Wafer manufacturing plants of new products have proven track records with SiC 4GMOSFET and other Si products.

For the 4-inch line, production is scheduled to end after the 6-inch line transition.

2. Summary of this approval

PCN No.2222002



Scope	SiC 3rd Generation MOSFET TO-247N Package
Content	<p>With regard to the above products, we will expand the wafer manufacturing process from the current ROHM Apollo Co., Ltd. Chikugo Plant to the Miyazaki Plant of Lapis Semiconductor Co., Ltd.</p> <p>The specifications and performance of the final product, including electrical characteristics and reliability, are unchanged.</p>
Reason	To expand production capacity
Verification	<ol style="list-style-type: none">1. Verification of changes between current and additional plants.2. Comparison of specifications and performance between current products and new products.
Schedule	Please respond within one year after receipt of the application.

3.Summary of changes

PCN No.2222002



Fabrication (Wafer manufacturing)		Using	Change Request
	Factory	ROHM Apollo co., Ltd. (Chikugo)	LAPIS Semiconductor Co., Ltd. (Miyazaki)
	SiC Wafers	4 inch	6 inch

Package (Assembly)		Using	Change Request
	Factory	No change(RIST)	
	Package	No change (TO-247N)	
	Dimensions	No change	
	Marking	No change	
	Tube	No change	

※RIST:ROHM INTEGRATED SYSTEMS (THAILAND) CO.,LTD.

Specification		Using	Change Request
	Datasheet (Electrical Characteristics)	Same	
	Reliability Test	OK	OK

4. Affected Products

PCN No.2222002



Please refer to PNLlist

5. Factory Overview


PCN No.2222002



- Company Name: Lapis Semiconductor Co., Ltd. Miyazaki Plant
- Representative: Kazumasa Wakuno(President and CEO)
- Location: 727 Kihara, Kiyotake, Miyazaki City, Miyazaki Prefecture
- Date of establishment: October 1, 2008
- Capital: 300 million yen (wholly owned by ROHM Corporation)
- Business: Power Devices, MEMS, WL-CSP, etc.
- Number of employees: 686 (as of October 2020)

5. Factory Overview

PCN No.2222002



※ Wafer process is only part assembly process

6.List of changes

PCN No.2222002



■ List of changes from conventional products

Item	Current products	New products	Purpose of change
Factory	ROHM Apollo co., Ltd. (Chikugo)	LAPIS Semiconductor Co., Ltd. (Miyazaki)	improve productivity
Wafer size	4inch	6inch	improve productivity
Back side metal	Ti-Ni(0.6 μ m)-Au-Ag Ti-Ni(1.2 μ m)-Au-Ag	Ti-Ni(1.2 μ m)-Au	improve productivity
Passivation	Polybenzoxazole (PBO)	Polyimide (PI)	improve productivity
Passivation structure of outer peripheral area (red frame below)			improve against passivation cracks due to thermal stress

For 6inch products ,the back metal composition and passivation structure will change.

7. Comparison of production plants

PCN No.2222002



		Conventional factory	Additional approval factory
Production plant		Rohm Apollo Chikugo	Lapis Semiconductor Miyazaki
Wafer Diameter		4inch,6inch,8inch	6inch
Clean room	Temperature	23℃	23℃
	Humidity	45%	45%
	Cleanliness* (wafer exposure area)	Class3(0.1um)	Class4(0.1um)
	Airflow method	laminar flow	laminar flow
Design Rules		0.35um	0.35um
Quality Management System		SPC System	SPC System

*Cleanliness is class according to ISO standards

There is no difference in The clean room environment of conventional factory and additional approval factory.

8.5M Change Point Verification

PCN No.2222002



		Target	Production plant		Concern	Verification	Decision
			current products	New products			
			Rohm Apollo Chikugo 4inch・6inch	Lapis Semiconductor Miyazaki 6inch			
Changes at 5M level	Man	Operator	Adoption of licensing system	Adoption of licensing system	Difference in work skills	No skill difference	No problem
	Machine	Production equipment	6inch wafer-compatible equipment (4inch combined use)	6inch wafer-compatible equipment (Mass production results)	Difference in specification	Process change point verification	No problem
	Material*	Wafer	4inch wafer	6inch wafer	Difference in specification, Reliability	Electrical characteristics	
		Passivation	Polybenzoxazole	Polyimide		Workmanship confirmation	
		Back side metal	Ti/Ni/Au/Ag	Ti/Ni/Au	Reliability		
	Method	Job method	6inch wafer process line (4inch combined use)	6inch wafer process line (Mass production results)	Difference in specification	Correlation evaluation	No problem
	Measurement	After wafer process measurement	6inch wafer-compatible equipment (4inch combined use)	6inch wafer-compatible equipment (Mass production results)	Difference in measurements between the provers		No problem

*Materials are only those that have changed.

In accordance with the 5M change point, we confirmed that there are no problems.

9. Process Change Point Verification

PCN No.2222002



No	Process operation	Equipment and methods		material		Differences and concerns	Validation results	decision ○ or ×	document
		Apollo Chikugo	Lapis Miyazaki	Apollo Chikugo	Lapis Miyazaki				
1	Fab Input	-		4inch Wafer	6inch Wafer	Difference in inch diameter	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
2	Cleaning	Same type specifications		Same type chemicals		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
3	Oxidation	Same type specifications		Same type gas		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
4	Photolithography (resist coating)	Same type specifications		Same type chemicals		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
5	Photolithography (exposure)	Same type specifications		-		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
6	Photolithography (resist development)	Same type specifications		Same type chemicals		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
7	Wet Etching	Same type specifications		Same type chemicals		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
8	Resist remove (ashing)	Same type specifications		Same type gas		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
9	SiC Trench Etching (dry)	Same type specifications		Same type gas		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
10	Implantation	Same type specifications		Same type gas		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
11	Activation annealing	Same type specifications		Same type gas		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24

We have confirmed that there are no problems with all the changes in each process.

9. Process Change Point Verification

PCN No.2222002



No	Process operation	Equipment and methods		material		Differences and concerns	Validation results	decision ○ or ×	document
		Apollo Chikugo	Lapis Miyazaki	Apollo Chikugo	Lapis Miyazaki				
12	Formation of poly-Si	Same type specifications		Same type gas		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
13	Poly-Si Etching (dry)	Same type specifications		Same type gas		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
14	Deposition inter-layer	Same type specifications		Same type gas		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
15	SiO ₂ interlayer Etching(dry)	Same type specifications		Same type gas		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
16	Forming surface electrode	Same type specifications		Same type materials		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
17	Metal Etching (Wet)	Same type specifications		Same type chemicals		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
18	Metal Etching (Dry)	Same type specifications		Same type gas		Nothing	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
19	Forming passivation layer	Same type specifications		PBO	PI	Use different materials Reliability	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
20	Back Side Grinding	Done before Fab Input	New process	Same type materials		New process	No difference in Wafer thickness No difference in specification No failure in reliability test	○	P.14 P.15-17 P.18-24
21	Forming backside electrode	Same type specifications		Ti/Ni/Au/Ag	Ti/Ni/Au	Layer structure change Reliability	No difference in specification No failure in reliability test	○	P.15-17 P.18-24
22	Electrical characteristic test	Same type specifications		-		Nothing	No difference in specification	○	P.15-17
23	Dicing	Same type specifications		Same type materials		Nothing	No difference in specification	○	-


We have confirmed that there are no problems with all the changes in each process.

10. Product Performance Evaluation Results

PCN No.2222002



■ SiC wafer thickness after Grind



*The graph on the left shows the thickness of only the board. The wafer thickness described in the data sheet contains the thickness of the metal.

*USL: Upper Specification Limit
LSL: Lower Specification Limit

Wafer	6inch
Average	326.7μm
σ	2.5μm

We confirmed that there is no problem with the process capability of the grinding process(new process).

11. Summary of Evaluation Results

PCN No.2222002



	4inch 3GMOSFET (Apollo Chikugo)	6inch 3GMOSFET (Lapis Miyazaki)
Static Characteristics (I_{DSS} , I_{GSS} , V_{th} , V_{SD} , R_{on})	Same Value	
Dynamic Characteristics (C_{iss} , C_{oss} , C_{rss} , Q_g , Q_{gs} , Q_{gd})	Same Value	
Switching Characteristics	Same Value	
Thermal Resistance	Same Value	
Electrical Static Discharge	Same Value	
Gate Oxide Reliability	Same Value*checked by TDDb test	
Reliability Test Result	AEC-Q101 qualified	AEC-Q101 qualified

There is no difference in various electrical characteristics between 4inch products and 6inch products.

12. Comparison of electrical characteristics

PCN No.2222002



■ Electrical Characteristics normal probability distribution ($T_{vj}=25^{\circ}\text{C}$)


• 4inch 3GMOSFET [SCT3040KLHRC11]

• 6inch 3GMOSFET [SCT3040KLHRC11]


*USL: Upper Specification Limit

LSL: Lower Specification Limit


Zero Gate voltage
Drain current [I_{DSS}]



Gate-Source leakage current
[$I_{GSS}(V_{GS}=22V)$]



Gate-Source leakage current
[$I_{GSS}(V_{GS}=-4V)$]



Wafer	N[pcs]	Ave[μA]	max[μA]	min[μA]	σ [μA]
4inch	100	0.00843	0.13011	0.00003	0.00679
6inch	100	0.00673	0.02534	0.00043	0.00430

Wafer	N[pcs]	Ave[nA]	max[nA]	min[nA]	σ [nA]
4inch	100	2.394	4.919	0.087	1.353
6inch	100	2.031	4.263	0.178	1.006

Wafer	N[pcs]	Ave[nA]	max[nA]	min[nA]	σ [nA]
4inch	100	0.716	1.658	0.016	0.486
6inch	100	0.713	2.015	0.015	0.512

There is no difference in various electrical characteristics between 4inch products and 6inch products.

12. Comparison of electrical characteristics

PCN No.2222002



■ Electrical Characteristics normal probability distribution ($T_{vj}=25^{\circ}\text{C}$)


• **4inch 3GMOSFET [SCT3040KLHRC11]**

• **6inch 3GMOSFET [SCT3040KLHRC11]**

*USL: Upper Specification Limit


LSL: Lower Specification Limit

Gate threshold voltage [$V_{GS(th)}$]




Wafer	N[pcs]	Ave[V]	max[V]	min[V]	σ [V]
4inch	100	4.30	4.78	3.72	0.26
6inch	100	4.31	4.87	3.82	0.25

Static Drain-Source on-state resistance [$R_{DS(on)}$]



Wafer	N[pcs]	Ave[mΩ]	max[mΩ]	min[mΩ]	σ [mΩ]
4inch	100	40.46	44.92	35.43	2.29
6inch	100	40.45	44.88	35.76	2.24

Forward voltage [V_{SD}]



Wafer	N[pcs]	Ave[V]	max[V]	min[V]	σ [V]
4inch	100	3.24	3.27	3.11	0.07
6inch	100	3.24	3.39	3.08	0.07

There is no difference in various electrical characteristics between 4inch products and 6inch products.

13. Reliability Test Results

PCN No.2222002



■ List of test results

Test items	Test conditions	Compliant standards	Exam time	Sample size n(pcs)	Failure Pn (pcs)
High Temperature Reverse Bias(HTRB)	$T_a=175^{\circ}\text{C}$, $V_{DS}=V_{DSmax}$	AEC-Q101	1000 h	77×3lot	0
High Temperature Reverse Bias(HTGB+)	$T_a=175^{\circ}\text{C}$, $V_{GS}=V_{GSmax}$	AEC-Q101	1000 h	77×3lot	0
High Temperature Reverse Bias(HTGB-)	$T_a=175^{\circ}\text{C}$, $V_{GS}=V_{GSmin}$	AEC-Q101	1000 h	77×3lot	0
Temperature humidity bias(THB)	$T_a=85^{\circ}\text{C}$, $R_h=85\%$, $V_{DS}=100\text{V}$	AEC-Q101	1000 h	77×3lot	0
Temperature cycle (TCY)	$T_a=-55^{\circ}\text{C}(30\text{min})\sim T_a=150^{\circ}\text{C}(30\text{min})$	AEC-Q101	1000 cycles	77×3lot	0
Pressure cooker(AC)	$T_a=121^{\circ}\text{C}$, 2atm, $R_h=100\%$	AEC-Q101	96 h	77×3lot	0

※Pretreatment conditions: Aging with pressure-docker equipment (105°C, 100%, 1.22×105Pa, 4h)

■ Measurement items and failure criteria

Measurement items	Conditions	Failure criteria
Gate-Source leakage current(I_{GSS})	Depends on specification conditions	Complies with AEC-Q101 standards
Zero Gate voltage Drain current (I_{DSS})	Depends on specification conditions	Complies with AEC-Q101 standards
Gate threshold voltage ($V_{GS(th)}$)	Depends on specification conditions	Complies with AEC-Q101 standards
Static Drain-Source on-state resistance ($R_{DS(on)}$)	Depends on specification conditions	Complies with AEC-Q101 standards

As a result of the reliability test, it was confirmed that there was no problem.


13. Reliability Test Results (HTRB)

PCN No.2222002



■ High Temperature Reverse Bias (HTRB) [$V_{DS}=V_{DSmax}$, $T_a=175^{\circ}C$]

Wafer:S4101MUFCZ
 Package:SCT3040KL(TO-247N)
 Sample size:77pcs×3lot



No Failure after 1000h over


13. Reliability Test Results (HTGB)

PCN No.2222002




■ High Temperature Gate Bias+ (HTGB+) [$V_{GS}=V_{GSmax}$, $T_a=175^\circ C$]

Wafer:S4101MUFCZ
 Package:SCT3040KL(TO-247N)
 Sample size:77pcs×3lot



■ High Temperature Gate Bias- (HTGB-) [$V_{GS}=V_{GSmin}$, $T_a=175^\circ C$]



No Failure after 1000h over


13. Reliability Test Results (THB)

PCN No.2222002



■ Temperature humidity bias(THB) [$V_{DS}=100V$, $T_a=85^\circ C$, $Rh=85\%$]

Wafer:S4101MUFCZ
 Package:SCT3040KL(TO-247N)
 Sample size:77pcs×3lot



No Failure after 1000h over


13. Reliability Test Results (TC)

PCN No.2222002



■ Temperature cycle (TC) [$T_a = -55^\circ\text{C}(30\text{min}) \sim 150^\circ\text{C}(30\text{min})$]

Wafer: S4101MUFCZ
 Package: SCT3040KL(TO-247N)
 Sample size: 77pcs x 3lot



No Failure after 1000cycle over



7-3. Reliability Test Results (TC)

PCN No.2222002






■ Cross sectional observation of Non-defective samples after TC 1000cyc

6inch 3GMOSFET [SCT3040KLHRC11]



4inch 3GMOSFET [SCT3040KLHRC11]



In 4inch 3GMOSFET, SiN layer in outer peripheral area may be cracked due to thermal stress such as temperature cycles. However, at the time of the TC 1050 cycle, the cracks are minor and there are no changes in characteristics, so there is no problem.

Structural changes have improved robustness against the cracking of the passivation layer(SiN).


13. Reliability Test Results (AC)

PCN No.2222002



■ Pressure cooker (AC) [$T_a=121^\circ\text{C}$, 2atm, Rh=100%]

Wafer:S4101MUFCZ
Package:SCT3040KL(TO-247N)
Sample size:77pcs×3lot



No Failure after 96h over



Electronics for the Future

ROHM Co.,Ltd. © 2022 ROHM Co., Ltd.

Public P/N (external)	Replacement P/N (external)
SCT3017ALGC11	SCT3017ALGC11
SCT3022ALGC11	SCT3022ALGC11
SCT3030ALGC11	SCT3030ALGC11
SCT3060ALGC11	SCT3060ALGC11
SCT3080ALGC11	SCT3080ALGC11
SCT3120ALGC11	SCT3120ALGC11
SCT3022KLGC11	SCT3022KLGC11
SCT3030KLGC11	SCT3030KLGC11
SCT3040KLGC11	SCT3040KLGC11
SCT3080KLGC11	SCT3080KLGC11
SCT3105KLGC11	SCT3105KLGC11
SCT3160KLGC11	SCT3160KLGC11
SCT3017ALHRC11	SCT3017ALHRC11
SCT3022ALHRC11	SCT3022ALHRC11
SCT3030ALHRC11	SCT3030ALHRC11
SCT3060ALHRC11	SCT3060ALHRC11
SCT3080ALHRC11	SCT3080ALHRC11
SCT3120ALHRC11	SCT3120ALHRC11
SCT3022KLHRC11	SCT3022KLHRC11
SCT3030KLHRC11	SCT3030KLHRC11
SCT3040KLHRC11	SCT3040KLHRC11
SCT3080KLHRC11	SCT3080KLHRC11
SCT3105KLHRC11	SCT3105KLHRC11
SCT3160KLHRC11	SCT3160KLHRC11

PCN No.2222002