



Product Change Notification / SYST-31NWXX531

Date:

01-Apr-2022

Product Category:

Clock and Timing - Clock and Data Distribution

PCN Type:

Document Change

Notification Subject:

Data Sheet - SY89832U Data Sheet

Affected CPNs:

[SYST-31NWXX531_Affected_CPN_04012022.pdf](#)

[SYST-31NWXX531_Affected_CPN_04012022.csv](#)

Notification Text:

SYST-31NWXX531

Microchip has released a new Product Documents for the SY89832U Data Sheet of devices. If you are using one of these devices please read the document located at [SY89832U Data Sheet](#).

Notification Status: Final

Description of Change:

1. Converted Micrel document SY89832U to Microchip data sheet template DS20006659A
2. Minor text changes throughout.

Impacts to Data Sheet: See above details

Reason for Change: To Improve Productivity

Change Implementation Status: Complete

Date Document Changes Effective: 01 April 2022

NOTE: Please be advised that this is a change to the document only the product has not been changed.

Markings to Distinguish Revised from Unrevised Devices: N/A

Attachments:

[SY89832U Data Sheet](#)

Please contact your local [Microchip sales office](#) with questions or concerns regarding this notification.

Terms and Conditions:

If you wish to receive Microchip PCNs via email please register for our PCN email service at our [PCN home page](#) select register then fill in the required fields. You will find instructions about registering for Microchips PCN email service in the [PCN FAQ](#) section.

If you wish to change your PCN profile, including opt out, please go to the [PCN home page](#) select login and sign into your myMicrochip account. Select a profile option from the left navigation bar and make the applicable selections.

2.5V Ultra-Precision 1:4 LVDS Fanout Buffer/ Translator with Internal Termination

Features

- Guaranteed AC Performance over Temperature and Voltage:
 - DC-to >2.0 GHz Throughput
 - <570 ps Propagation Delay (IN-to-Q)
 - <20 ps Within-Device Skew
 - <200 ps Rise/Fall Time
- Ultra-Low Jitter Design:
- 81 fs_{RMS} Phase Jitter
- Unique, Patented Input Termination and V_T Pin Accepts DC- and AC-Coupled Inputs
- High-Speed LVDS Outputs
- 2.5V Voltage Supply Operation
- Industrial Temperature Range: -40°C to +85°C
- Available in a 16-Lead 3 mm x 3 mm QFN Package

Applications

- Processor Clock Distribution
- SONET Clock Distribution
- Fibre Channel Clock Distribution
- Gigabit Ethernet Clock Distribution


General Description

The SY89832U is a 2.5V, high-speed, 2 GHz differential, low voltage differential swing (LVDS) 1:4 fanout buffer optimized for ultra-low skew applications. Within device skew is guaranteed to be less than 20 ps over supply voltage and temperature.

The differential input buffer has a unique internal termination design that allows access to the termination network through a V_T pin. This feature allows the device to easily interface to different logic standards. A VREF-AC reference output is included for AC-coupled applications.


The SY89832U is a part of the high-speed clock synchronization family. For 3.3V applications, see SY89833L or SY89833AL.

Package Type



SY89832U

Functional Block Diagram



1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings †

Supply Voltage (V_{CC})	-0.5V to +4.0V
Input Voltage (V_{IN})	-0.5V to $V_{CC} + 0.3V$
LVDS Output Current (I_{OUT})	±10 mA
Input Current (Source or Sink Current on IN, /IN) (I_{IN})	±50 mA
Termination Current (Source or Sink Current on VT) (I_{VT})	±100 mA
V_{REF-AC} Current (Source or Sink Current on V_{REF-AC}) ($I_{VREF-AC}$) (Note 1)	±1.5 mA

Operating Ratings ††

Supply Voltage Range (V_{CC})	+2.375V to +2.675V
-----------------------------------	--------------------

† **Notice:** Permanent device damage may occur if absolute maximum ratings are exceeded. This is a stress rating only and functional operation is not implied at conditions other than those detailed in the operational sections of this data sheet. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

†† **Notice:** The data sheet limits are not guaranteed if the device is operated beyond the operating ratings.

Note 1: Due to the limited drive capability, the V_{REF-AC} reference should only be used for the input of the same package device (i.e., do not use for other devices).

DC ELECTRICAL CHARACTERISTICS

Electrical Characteristics: $V_{CC} = 2.5V \pm 5\%$; $T_A = -40^\circ C$ to $+85^\circ C$, unless otherwise stated, (Note 1)						
Parameters	Symbol	Min.	Typ.	Max.	Units	Conditions
Power Supply Current	I_{CC}	—	75	100	mA	No load
Input Resistance (IN-to-VT)	R_{IN}	45	50	55	Ω	—
Differential Input Resistance (IN-to-/IN)	R_{DIFF_IN}	90	100	110	Ω	—
Input High Voltage (IN, /IN)	V_{IH}	0.1	—	$V_{CC} + 0.3$	V	—
Input Low Voltage (IN, /IN)	V_{IL}	-0.3	—	$V_{IH} - 0.1$	V	—
Input Voltage Swing	V_{IN}	0.1	—	V_{CC}	V	Note 2
Differential Input Voltage Swing	V_{DIFF_IN}	0.2	—	—	V	Note 2
Input Current (IN, /IN)	$ I_{IN} $	—	—	45	mA	Note 3
Output Reference Voltage	V_{REF-AC}	$V_{CC} - 1.525$	$V_{CC} - 1.425$	$V_{CC} - 1.325$	V	—

Note 1: Devices are designed to meet the DC specifications shown in the above table after thermal equilibration has been established.

2: See Figure 5-1 and Figure 5-2 for V_{IN} and V_{DIFF_IN} definitions.

3: Due to the internal termination the input current depends on the applied voltages at IN, /IN, and VT inputs. Do not apply a combination of voltages that causes the input current to exceed the maximum limit!

SY89832U

LVDS OUTPUTS DC ELECTRICAL CHARACTERISTICS

Electrical Characteristics: $V_{CC} = 2.5V \pm 5\%$; $T_A = -40^\circ C$ to $+85^\circ C$, $R_L = 100\Omega$ across Q and /Q, unless otherwise stated. (Note 1)

Parameter	Symbol	Min.	Typ.	Max.	Units	Conditions
Output Voltage Swing	V_{OUT}	250	325	—	mV	Note 2
Differential Voltage Output Swing	V_{DIFF_OUT}	500	650	—	mV	Note 2
Output Common Mode Voltage	V_{OCM}	1.125	—	1.275	V	Note 3
Change in Output Common Mode Voltage	ΔV_{OCM}	-50	—	50	mV	Note 3

Note 1: Devices are designed to meet the DC specifications shown in the above table after thermal equilibration has been established.

2: See Figure 5-1 and Figure 5-2 for V_{OUT} and V_{DIFF_OUT} definitions.

3: See Figure 8-2.

LVTTTL/CMOS DC ELECTRICAL CHARACTERISTICS

Electrical Characteristics: $V_{CC} = 2.5V \pm 5\%$; $T_A = -40^\circ C$ to $+85^\circ C$, unless otherwise stated. (Note 1)

Parameter	Symbol	Min.	Typ.	Max.	Units	Conditions
Input High Voltage	V_{IH}	2.0	—	V_{CC}	V	—
Input Low Voltage	V_{IL}	0	—	0.8	V	—
Input High Current	I_{IH}	-125	—	30	μA	—
Input Low Current	I_{IL}	-300	—	—	μA	—

Note 1: Devices are designed to meet the DC specifications shown in the above table after thermal equilibration has been established.

AC ELECTRICAL CHARACTERISTICS

Electrical Characteristics: $V_{CC} = 2.5V \pm 5\%$; $T_A = -40^\circ C$ to $+85^\circ C$, $R_L = 100\Omega$ across Q and /Q, unless otherwise stated. (Note 1)

Parameter	Symbol	Min.	Typ.	Max.	Units	Conditions
Maximum Frequency	f_{MAX}	2.0	2.5	—	GHz	$V_{OUT} \geq 200$ mV
Propagation Delay In-to-Q	t_{PD}	370	470	570	ps	$V_{IN} < 400$ mV
		300	410	500		$V_{IN} \geq 400$ mV
Within-Device Skew	t_{SKEW}	—	5	20	ps	Note 2
Part-to-Part Skew		—	—	200		Note 3
Set-Up Time EN to IN, /IN	t_S	0	—	—	ps	Note 4
Hold Time IN, /IN to EN	t_H	320	—	—	ps	Note 4
Additive Phase Jitter	t_{JITTER}	—	81	—	f_{SRMS}	622 MHz @ 2.5V, Integration range: 12 kHz to 20 MHz
		—	195	—		250 MHz @ 2.5V, Integration range: 12 kHz to 20 MHz
Output Rise/Fall Time Q (20% to 80%)	t_r/t_f	70	150	200	ps	At full output swing

Note 1: High-frequency AC parameters are guaranteed by design and characterization.

2: Within-device skew is measured between two different outputs under identical input transitions.

3: Part-to-part skew is defined for two parts with identical power supply voltages at the same temperature and no skew at the edges at the respective inputs.

4: Set-up and Hold times apply to synchronous applications that intend to enable/disable before the next clock cycle. For asynchronous applications, Set-up and Hold times do not apply.

TEMPERATURE SPECIFICATIONS

Parameters	Symbol	Min.	Typ.	Max.	Units	Conditions
Temperature Ranges						
Operating Temperature Range	T_A	-40	—	+85	$^\circ C$	—
Lead Temperature	T_J	—	+260	—	$^\circ C$	Soldering, 20 sec.
Storage Temperature Range	T_A	-65	—	+150	$^\circ C$	
Package Thermal Resistance (Note 1)						
Thermal Resistance, QFN-16Ld	θ_{JA}	—	60	—	$^\circ C/W$	Junction-to-Ambient, Still-Air
	Ψ_{JB}	—	32	—	$^\circ C/W$	Junction-to-Board

Note 1: Package thermal resistance assumes exposed pad is soldered (or equivalent) to the device's most negative potential; on the PCB. θ_{JA} and Ψ_{JB} values are determined for a 4-layer board in still-air number, unless otherwise stated.

SY89832U

2.0 TYPICAL OPERATING CHARACTERISTICS

Note: $V_{CC} = 2.5V$, $GND = 0V$, $V_{IN} = 400\text{ mV}$, $R_L = 100\Omega$ across the outputs; $T_A = 25^\circ\text{C}$, unless otherwise stated.




FIGURE 2-1: Output Swing vs. Frequency.




FIGURE 2-4: 622 MHz Output.




FIGURE 2-2: Propagation Delay vs. Input Voltage Swing.




FIGURE 2-5: 1 GHz Output.




FIGURE 2-3: 155 MHz Output.

$V_{CC} = 2.5V$, $GND = 0$, $T_A = +25^{\circ}C$.




FIGURE 2-6: Typical Additive Phase Jitter (622 MHz Carrier).




FIGURE 2-7: Typical Additive Phase Jitter (250 MHz Carrier).

SY89832U

3.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in [Table 3-1](#).

TABLE 3-1: PIN FUNCTION TABLE

Pin Number	Pin Name	Pin Function
15, 16 1, 2 3, 4 5, 6	Q0, /Q0 Q1, /Q1 Q2, /Q2 Q3, /Q3	LVDS Differential (Outputs): Normally terminated with 100Ω across the pair (Q, /Q). See LVDS Outputs section for more details. Unused outputs should be terminated with a 100Ω resistor across each pair.
8	EN	The single-ended, TTL/CMOS-compatible input functions as a synchronous output enable. The synchronous enable ensures that enable/disable will only occur when the Q outputs are in a logic LOW state. Note that this input is internally connected to a 25 kΩ pull-up resistor and will default to logic HIGH state (enabled) if left open.
9, 12	/IN, IN	Differential Input: This input is the differential signal input to the device. Input accepts AC- or DC-Coupled differential signs as small as 100 mV. Each pin internally terminates to the V _T pin through 50Ω. Note that this input will default to an intermediate state if left open. See Input Interface Applications section for more details.
10	VREF-AC	Reference Voltage: This output biases to approximately V _{CC} – 1.4V. It is used when AC coupling the input (IN, /IN). For AC-Coupled applications, connect VREF-AC to VT pin and bypass with a 0.01 μF low-ESR capacitor to VCC. See Input Interface Applications section for more details. Maximum sink/source current is ±1.5 mA. Due to the limited drive capability, the VREF-AC pin is only intended to drive the VT pin.
11	VT	Input Termination Center-Tap: Each side of the differential input pair terminates to the VT pin. The VT pin provides a center-tap to a termination network for maximum interface flexibility. See Input Interface Applications section for more details.
13	GND	Ground. GND pin and exposed pad must be connected to the most negative potential of the device ground.
7, 14	VCC	Positive Power Supply: Bypass with 0.1 μF//0.01 μF low ESR capacitors and place as close to each VCC pin as possible.

TABLE 3-2: TRUTH TABLE

IN	/IN	EN	Q	/Q
0	1	1	0	1
1	0	1	1	0
X	X	0	0	1

4.0 TIMING DIAGRAMS




FIGURE 4-1: *Timing Diagram Disable.*




FIGURE 4-2: *Timing Diagram Enable.*

5.0 SINGLE-ENDED AND DIFFERENTIAL SWINGS




FIGURE 5-1: *Single-Ended Swing.*




FIGURE 5-2: *Differential Swing.*

6.0 INPUT STAGE




FIGURE 6-1: Simplified Differential Input Buffer.

SY89832U

7.0 INPUT INTERFACE APPLICATIONS




FIGURE 7-1: DC-Coupled CML Input Interface.




FIGURE 7-4: AC-Coupled LVPECL Input Interface.




FIGURE 7-2: AC-Coupled CML Input Interface.




FIGURE 7-5: LVDS Input Interface.




FIGURE 7-3: DC-Coupled LVPECL Input Interface (*Bypass with 0.01 µF to GND).




FIGURE 7-6: HSTL Input Interface.

8.0 LVDS OUTPUTS

LVDS specifies a small swing of 325 mV typical, on a nominal 1.2V common-mode above ground.

The common-mode voltage has tight limits to permit large variations in ground noise between an LVDS driver and receiver.




FIGURE 8-1: LVDS Differential Measurement.





FIGURE 8-2: LVDS Common Mode Measurement.

SY89832U


9.0 PACKAGING INFORMATION

9.1 Package Marking Information

16-Lead QFN*



Example




Legend:	XX...X	Product code or customer-specific information
	Y	Year code (last digit of calendar year)
	YY	Year code (last 2 digits of calendar year)
	WW	Week code (week of January 1 is week '01')
	NNN	Alphanumeric traceability code
	(e3)	Pb-free JEDEC® designator for Matte Tin (Sn)
	*	This package is Pb-free. The Pb-free JEDEC designator (e3) can be found on the outer packaging for this package.
	•, ▲, ▼	Pin one index is identified by a dot, delta up, or delta down (triangle mark).
Note:	In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information. Package may or may not include the corporate logo.	
	Underbar (¯) and/or Overbar (˘) symbol may not be to scale.	


TITLE

16 LEAD QFN 3x3mm PACKAGE OUTLINE & RECOMMENDED LAND PATTERN


DRAWING #	QFN33-16LD-PL-3	UNIT	MM
Lead Frame	NiPdAu	Lead Finish	NiPdAu




TOP VIEW
NOTE: 1, 2, 3



BOTTOM VIEW
NOTE: 1, 2, 3



SIDE VIEW
NOTE: 1, 2, 3



RECOMMENDED LAND PATTERN
NOTE: 4, 5

NOTE:

1. MAX PACKAGE WARPAGE IS 0.05mm.
2. MAX ALLOWABLE BURR IS 0.076mm IN ALL DIRECTIONS
3. PIN #1 IS ON TOP WILL BE LASER MARKED.
4. RED CIRCLE IN LAND PATTERN INDICATES THERMAL VIA. SIZE SHOULD BE 0.30-0.35mm IN DIAMETER AND SHOULD BE CONNECTED TO GND FOR MAX THERMAL PERFORMANCE.
5. GREEN RECTANGLES (SHADED AREA) INDICATE SOLDER STENCIL OPENING ON EXPOSED PAD AREA. SIZE SHOULD BE 0.60x0.60mm IN SIZE, 0.20mm SPACING.

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>.

SY89832U

NOTES:

APPENDIX A: REVISION HISTORY

Revision A (March 2022)

- Converted Micrel document SY89832U to Microchip data sheet template DS20006659A.
- Minor text changes throughout.

SY89832U

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

<u>PART NO.</u>	X	X	X	-XX	Examples:	
Device	Voltage Option	Package	Temperature Range	Special Processing		
Device:	SY89832:	2.5V Ultra-Precision 1:4 LVDS Fanout Buffer/Translator with Internal Termination			a) SY89832UMG:	2.5V Ultra-Precision 1:4 LVDS Fanout Buffer/Translator with Internal Termination, 2.5V, 16-Lead Industrial QFN, -40°C to 85°C (NiPdAu Lead Free), 100/Tube
Voltage Option:	U	=	2.5V		b) SY89832UMG-TR:	2.5V Ultra-Precision 1:4 LVDS Fanout Buffer/Translator with Internal Termination, 2.5V, 16-Lead Industrial QFN, -40°C to 85°C (NiPdAu Lead Free), 1,000/Reel
Package:	M	=	16-Lead Industrial QFN			
Temperature Range:	G	=	-40°C to 85°C (NiPdAu Lead Free)			
Special Processing:	<blank>	=	100/Tube			
	TR	=	1,000/Reel			

SY89832U

NOTES:

Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is “unbreakable”. Code protection is constantly evolving. Microchip is committed to continuously improving the code protection features of our products.

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at <https://www.microchip.com/en-us/support/design-help/client-support-services>.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSEQUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPIC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Klear, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, QuietWire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, TrueTime, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, GridTime, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, NVM Express, NVMe, Omniscient Code Generation, PICDEM, PICDEM.net, PICKit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SmartHLS, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, Symmcom, and Trusted Time are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2022, Microchip Technology Incorporated and its subsidiaries.

All Rights Reserved.

ISBN: 978-1-6683-0159-3



MICROCHIP

Worldwide Sales and Service

AMERICAS

Corporate Office
2355 West Chandler Blvd.
Chandler, AZ 85224-6199
Tel: 480-792-7200
Fax: 480-792-7277
Technical Support:
<http://www.microchip.com/support>
Web Address:
www.microchip.com

Atlanta
Duluth, GA
Tel: 678-957-9614
Fax: 678-957-1455

Austin, TX
Tel: 512-257-3370

Boston
Westborough, MA
Tel: 774-760-0087
Fax: 774-760-0088

Chicago
Itasca, IL
Tel: 630-285-0071
Fax: 630-285-0075

Dallas
Addison, TX
Tel: 972-818-7423
Fax: 972-818-2924

Detroit
Novi, MI
Tel: 248-848-4000

Houston, TX
Tel: 281-894-5983

Indianapolis
Noblesville, IN
Tel: 317-773-8323
Fax: 317-773-5453
Tel: 317-536-2380

Los Angeles
Mission Viejo, CA
Tel: 949-462-9523
Fax: 949-462-9608
Tel: 951-273-7800

Raleigh, NC
Tel: 919-844-7510

New York, NY
Tel: 631-435-6000

San Jose, CA
Tel: 408-735-9110
Tel: 408-436-4270

Canada - Toronto
Tel: 905-695-1980
Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney
Tel: 61-2-9868-6733

China - Beijing
Tel: 86-10-8569-7000

China - Chengdu
Tel: 86-28-8665-5511

China - Chongqing
Tel: 86-23-8980-9588

China - Dongguan
Tel: 86-769-8702-9880

China - Guangzhou
Tel: 86-20-8755-8029

China - Hangzhou
Tel: 86-571-8792-8115

China - Hong Kong SAR
Tel: 852-2943-5100

China - Nanjing
Tel: 86-25-8473-2460

China - Qingdao
Tel: 86-532-8502-7355

China - Shanghai
Tel: 86-21-3326-8000

China - Shenyang
Tel: 86-24-2334-2829

China - Shenzhen
Tel: 86-755-8864-2200

China - Suzhou
Tel: 86-186-6233-1526

China - Wuhan
Tel: 86-27-5980-5300

China - Xian
Tel: 86-29-8833-7252

China - Xiamen
Tel: 86-592-2388138

China - Zhuhai
Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore
Tel: 91-80-3090-4444

India - New Delhi
Tel: 91-11-4160-8631

India - Pune
Tel: 91-20-4121-0141

Japan - Osaka
Tel: 81-6-6152-7160

Japan - Tokyo
Tel: 81-3-6880-3770

Korea - Daegu
Tel: 82-53-744-4301

Korea - Seoul
Tel: 82-2-554-7200

Malaysia - Kuala Lumpur
Tel: 60-3-7651-7906

Malaysia - Penang
Tel: 60-4-227-8870

Philippines - Manila
Tel: 63-2-634-9065

Singapore
Tel: 65-6334-8870

Taiwan - Hsin Chu
Tel: 886-3-577-8366

Taiwan - Kaohsiung
Tel: 886-7-213-7830

Taiwan - Taipei
Tel: 886-2-2508-8600

Thailand - Bangkok
Tel: 66-2-694-1351

Vietnam - Ho Chi Minh
Tel: 84-28-5448-2100

EUROPE

Austria - Wels
Tel: 43-7242-2244-39
Fax: 43-7242-2244-393

Denmark - Copenhagen
Tel: 45-4485-5910
Fax: 45-4485-2829

Finland - Espoo
Tel: 358-9-4520-820

France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79

Germany - Garching
Tel: 49-8931-9700

Germany - Haan
Tel: 49-2129-3766400

Germany - Heilbronn
Tel: 49-7131-72400

Germany - Karlsruhe
Tel: 49-721-625370

Germany - Munich
Tel: 49-89-627-144-0
Fax: 49-89-627-144-44

Germany - Rosenheim
Tel: 49-8031-354-560

Israel - Ra'anana
Tel: 972-9-744-7705

Italy - Milan
Tel: 39-0331-742611
Fax: 39-0331-466781

Italy - Padova
Tel: 39-049-7625286

Netherlands - Drunen
Tel: 31-416-690399
Fax: 31-416-690340

Norway - Trondheim
Tel: 47-7288-4388

Poland - Warsaw
Tel: 48-22-3325737

Romania - Bucharest
Tel: 40-21-407-87-50

Spain - Madrid
Tel: 34-91-708-08-90
Fax: 34-91-708-08-91

Sweden - Gothenberg
Tel: 46-31-704-60-40

Sweden - Stockholm
Tel: 46-8-5090-4654

UK - Wokingham
Tel: 44-118-921-5800
Fax: 44-118-921-5820

SYST-31NWXK531 - Data Sheet - SY89832U Data Sheet

Affected Catalog Part Numbers(CPN)

SY89832UMG

SY89832UMG-TR